

Pipe Tools

Wrenches

Hex Wrenches

Hex jaw design gives multi-sided, secure grip on all hex nuts, square nuts, unions, and valve packing nuts. The extra-wide opening offset model is ideal for securing drain nuts on sinks and tubs.

Catalog No.	Model No.	Description	Length		Capacity		Weight		Std. Pack
			in.	mm	in.	mm	lb.	kg	
31305	E-110	Offset Hex Wrench	9½	240	1⅛-2⅝	29-67	1½	0,6	6
31275	17	Straight Hex Wrench	14½	362	⅝-1¼	16-30	4½	2,0	6
31280	25	Straight Hex Wrench	20	500	1-2	25-50	8¾	4,0	6



Spud Wrench

12" Spud Wrench features narrow jaws to fit into tight places. Smooth, toothless jaws ideal for square or rectangular stock.

Catalog No.	Model No.	Description	Length		Capacity		Weight		Std. Pack
			in.	mm	in.	mm	lb.	kg	
31400	-	Spud Wrench	12	300	⅜-2⅝	10-67	2½	1,1	1

Adjustable Wrenches

- New ergonomic cushioned grips on 6", 8", 10" and 12".
- High grade Chrome-Vandium alloy steel.
- Forged and Heat-treated for durability.
- Cobalt plated finish to reduce rust and corrosion.
- Jaw scales in SAE and metric for quick adjustment
- Cushioned grips are designed for comfort only. They are **NOT** intended as insulation against electric shock.

Catalog No.	Model No.	Description	Length		Capacity		Weight		Std. Pack
			in.	mm	in.	mm	lb.	kg	
86902	756	Adjustable Wrench (Cushioned Grip)	6	150	¾	20	¼	0,1	1
86907	758	Adjustable Wrench (Cushioned Grip)	8	200	⅞	25	½	0,2	1
86912	760	Adjustable Wrench (Cushioned Grip)	10	250	1⅛	30	¾	0,3	1
86917	762	Adjustable Wrench (Cushioned Grip)	12	300	1⅝	35	1½	0,6	1
86922	765	Adjustable Wrench	15	375	1⅞	40	3	1,3	1
86927	768	Adjustable Wrench	18	450	2⅞	50	5⅛	2,3	1
86932	774	Adjustable Wrench	24	600	2⅞	60	9¼	4,2	1

