



Buy it for looks. Buy it for life.®

FAUCET DESCRIPTION

- Metal construction with various finishes identified by suffix
- 1/2" IPS connections will accept standard ball nose connection for 3/8" tubing
- Includes matching traditional side spray

OPERATION

- Lever style handle
- Temperature controlled by 130° arc of handle travel
- Will operate with less than 5 lbs. of force

FLOW


- Aerator is limited to 2.2 gpm (8.3 L/min).

CARTRIDGE

- 1225 cartridge design
- Nonmetallic, nonferrous and stainless steel material

STANDARDS


- Third party certified to CSA B125.1, ASME A112.18.1, ICC A117.1 and all applicable requirements referenced therein
- Certified to ANSI/NSF 61/9
- Complies with California Proposition 65 and with the Federal Safe Drinking Water Act

- ADA  for lever handle

WARRANTY

- Lifetime limited warranty against leaks, drips and finish defects to the original consumer purchaser
- 5 year warranty if used in commercial installations


Specifications



Vestige™ Single-Handle Kitchen Faucet with Side Spray

Model: 7065 series

Spout, Handle, & Hose Spray install
through deck holes a minimum of
1-1/4" (32mm) in diameter.



CRITICAL DIMENSIONS

(DO NOT SCALE)