

GENERAL

Highest quality sink formed of #18 (1.2mm) gauge, type 304 (18-8) nickel bearing stainless steel. Undermount.

DESIGN FEATURES

Bowl Depth: 6" (152mm).

Finish: Exposed surfaces are hand blended to a lustrous satin finish.

Underside: Underside of sink is fully protected by heavy duty Sound Guard $^{\text{\tiny TM}}$ undercoating to prevent condensation and dampen sound.

OTHER

Drain Opening: 1-5/8" (41mm).

Overflow: Sink comes with LKF293 overflow assembly.

Note: All Elkay undermount sinks are designed to affix to the underside of any solid surface countertop.

These sinks comply with Standards ASME A112.19.3 and CSA B45.4



These sinks are listed by the International Association of Plumbing and Mechanical Officials as meeting the requirements of the Uniform Plumbing Code.

OPTIONAL ACCESSORIES


Drains: LK174, LK175.


SINK DIMENSIONS*


Model	Overall		Inside Bowl			Cutout in	Minimum Cabinet
Number	L	W	L	W	D	Countertop	Size
ELU1511	17 (432mm)	13 (330mm)	15 ¹ / ₂ (394mm)	11 ³ / ₈ (289mm)	6 (152mm)	Template**	21 (533mm)
ELUH1511	18 (457mm)	14 (356mm)	15 ¹ / ₂ (394mm)	11 ³ / ₈ (289mm)	6 (152mm)		21 (533mm)


^{*}Length is left to right. Width is front to back.

^{**}Template and countertop mounting clips are packed with every sink.









Installation Profile of ELU and ELUH Single Bowl Models

The template provided with each ELU/ELUH sink provides the only type of installation recommended by Elkay.

1/8" (3mm) Overhang (ELU Sink) COUNTERTOP MOUNTING BRACKET FASTENER (NOT FURNISHED) 1-3/8" (35mm) 1/8 (APPROX.) OVERHANG

In keeping with our policy of continuing product improvement, Elkay reserves the right to change product specifications without notice. Please visit elkayusa.com for most current version of Elkay product specification sheets.

COUNTERTOP

MOUNTING
BRACKET

FASTENER
(NOT FURNISHED)

1-1/8"

SILICONE
CAULK
(NOT
FURNISHED)


SINK

1/2" (13mm) Reveal (ELUH Sink)

This specification describes an Elkay product with design, quality and functional benefits to the user. When making a comparison of other producers' offerings, be certain these features are not overlooked.

15-1/2

(394mm)



14"

(356mm)

11-3/81

(289mm)