

SPECIFICATIONS

Input

- **Voltage:** 24, 120 or 240 VAC
- **Frequency:** 50-60 Hz
- **Power Consumption:** 1 watt maximum

Time Delays

- **Defrost:** Fixed at 10 minutes (+/- 10%)
- **Interval Between Defrost:**
 - Pin selectable (30/45/90 minutes)
- **Test Time:** Short across "DEF" terminals before startup to reduce time by 256x


Output

- **Rating:**
 - **N.O.:** 20 amps @ 240 VAC
 - **N.C.:** 10 amps @ 240 VAC
- **Type:** Relay
- **Form:** SPDT

Mechanical

- **Dimensions:** 4.2" x 4.2"
- **Mounting:** Surface mount using (4) #6 or #8 screws, or plastic stand offs

WIRING DIAGRAM



Note: Use only one input voltage at a time.