

digital fade dimmers



- press on to favorite level; press off
- press twice for full on
- press, hold and release for gradual fade-to-off
- touch buttons to adjust light level
- provides true dimming from each location (with companion dimmers)

incandescent/halogen†

single pole/	600 W	AB-600M-
multi-location		
single pole	1000 W	AB-1000M-
multi-location		

magnetic low-voltage†

single pole/	600 VA	ABLV-600M-
multi-location	(450 W)	
single pole/	1000 VA	ABLV-1000M-
multi-location	(800 W)	

Suggested maximum lighting load for magnetic low-voltage dimming is 450 W for 600 VA products and 800 W for 1000 VA products, to allow for transformer losses.

† minimum load is 40 W/VA

companion dimmer



- **for use with multi-location dimmers only**
use up to **nine** companion dimmers with only one Abella® multi-location dimmer
- provides true dimming from each location
- no derating if ganged

companion dimmer

AB-AD-

Use standard single-pole and 3-way wiring for easy installation.

See page 89 for available colors.

To order, add color suffix to model number.

Example: **AB-600M- WH**