

Terminations

R C Y1 Y2 W2 O B G E L

7-Day, 5-2-Day & 5-1-1-Day Programmable

2-STAGE HEAT PUMP

Simple control for year-round comfort. This easy-to-operate comfort command center allows you to match temperature to your family's lifestyle. Attractive, extra-rugged, highly reliable and accurate, this thermostat's elegant design will look and perform like new for years to come.





- Two-stage heat pump
- New ICM patented Thermal Intrusion
- New SimpleSet™ Target Programming technology
- Large display with backlight
- Accuracy: ±1°F
- Adjustable temperature differentials
- Hardwired
- Manual changeover
- Easy access terminal block
- Field adjustable calibration
- Vacation hold
- Selectable °F or °C
- Keypad lockout
- Zoning system compatible
- Soft-touch controls
- Status LEDs






- · Two-stage heat pump
- Manual changeover


SC3211L




Programmable 7-Day, 5-2-Day & 5-1-1-Day Two-Stage Heat Pump Hardwired

Dimensions







Specifications

Electrical Rating:

- 24 VAC (18-30 VAC)
- 1 amp maximum per terminal
- 4 amp maximum total load
- · Easy access terminal block

Temperature Control Ranges:

• 45°F to 90°F, Accuracy: ±1°F

System Configurations:

· 2-stage heat pump

Terminations:

• SC3211L: R, C, Y1, Y2, W2, O, B, G, E, L

Specifications subject to change without notice.

NEWThermal Intrusion Barrier

Exclusive, patented insulation technology eliminates thermal drift caused by wall effect.



NEW SimpleSet[™] Target Programming

Patent-pending technology lets you transfer the program and configuration from one thermostat to another in seconds.



Need more wall coverage? Order the ICM insulated wall plate for a polished installation.

Eliminate the wall effect. ICM's insulated wall plate provides a fast, easy solution for hiding wall problems.

- · Foam gasket prevents drafts through wall opening
- Rugged, flexible construction
- Hidden mounting screws for a sleek appearance
- Universal fit with all SimpleComfort® thermostats
- Order: **ACC-WP03** 5.7"H x 7.5"W



SC5812 Thermostat shown with **ACC-WP03** insulated wall plate.

