



Shown actual size: Rotary dimmer
and 1-gang Fassada® wallplate in ivory (IV)

available models

source type

- 💡 incandescent/halogen lighting
- ✂️ quiet 3-speed fan controls
- 🌀 fully variable fan controls

control locations

- 🔌 single pole (one location)
- 🔌🔌 3-way (two locations)

available colors (see page 12 for color swatches)

colors (gloss finish)

- WH** white
- IV** ivory

Rotary dimmers

product family features

- easy-turn knob adjusts light to your favorite level
- coordinating Fassada® wallplates available separately (including matte, gloss, and stainless steel finishes)
- **eco-dim**® model available

Questions on installation or selection?
Call Lutron® 24 hours/7 days a week at
1.800.523.9466 or visit www.lutron.com

dimmers with push on/off knob



- push on/off, rotate to adjust light level
- eco-dim® model guarantees at least 15% energy savings compared to a standard switch

incandescent/halogen

single pole	600 W	D-600P-	
3-way	600 W	D-603P-	

dimmer with rotate on/off knob



- rotate on/off, rotate to adjust light level

incandescent/halogen

single pole	600 W	D-600R-	
-------------	-------	----------------	--

incandescent/halogen — eco-dim®†

NEW

single pole/3-way	600 W	D-603PG-	
-------------------	-------	-----------------	--

dimmers with push on/off knob & locator light



- push on/off, rotate to adjust light level
- includes locator light

incandescent/halogen

single pole	600 W	DNG-600P-	
3-way	600 W	DNG-603P-	

† available in white, ivory, almond, and light almond

See page 101 for available colors.

To order, add color suffix to model number.

Example: **D-600P- WH**

fan control with rotate on/off knob



- rotate on/off, rotate to adjust fan speed
- 3 quiet fan speeds for increased comfort
- designed to reduce motor hum
- for use with only one ceiling paddle fan

quiet 3-speed control

single pole	1.5A	FSQ-2F-
-------------	------	----------------

replacement knobs



- standard knob



- quiet, 3-speed fan control knobs

knobs

standard knob	RK-
3-speed fan control knob, white	280-324-01
3-speed fan control knob, ivory	280-324-06

fan controls with rotate on/off knob



- rotate on/off, rotate to adjust fan speed
- for use with multiple ceiling paddle fans or exhaust fans

fully variable control

single pole fan control	5A	FS-5F-
factory set minimum speed		
single pole fan control	5A	FS-5E-
user adjustable minimum speed		

See page 101 for available colors.
To order, add color suffix to model number.
Example: **FSQ-2F- WH**