



Shown actual size: Diva® preset dimmer and 1-gang Claro® wallplate in light almond (LA)

DIVA® contemporary dimmers

product family features

- matches existing decorator-style switches
- paddle switch returns light to your favorite level
- slide adjusts light to suit any activity
- soft locator light illuminated in off position
- coordinating Claro® and Satin Colors® wallplates available separately (including stainless steel)
- **eco-dim®** model available

available models

source type

- incandescent/halogen lighting
- magnetic low-voltage lighting
- electronic low-voltage lighting
- fluorescent lighting
- LED lighting
- dimmable compact fluorescent
- quiet 3-speed fan controls

control locations

- single pole (one location)
- 3-way (two locations)

available colors (see pages 12-13 for color swatches)

colors (gloss finish)

- | | |
|------------------------|-----------------|
| WH white | GR gray |
| IV ivory | BR brown |
| AL almond | BL black |
| LA light almond | |

colors (satin finish)

- | | |
|-----------------------|------------------------|
| HT hot | ES eggshell |
| MR merlot | BI biscuit |
| PL plum | GS goldstone |
| TQ turquoise | DS desert stone |
| TC terracotta | ST stone |
| GB greenbriar | LS limestone |
| BG bluestone | SW snow |
| MS mocha stone | PD palladium |
| SG sea glass | MN midnight |
| TP taupe | SI sienna |

colors & finishes key

- available in gloss finish
- available in satin finish
- available in all gloss and satin finishes

CAD file downloads available at www.lutron.com/cad

Questions on installation or selection?
Call Lutron® 24 hours/7 days a week at
1.800.523.9466 or visit www.lutron.com

dimmers with locator light



- paddle turns on/off
- slide up to brighten, down to dim
- includes locator light
- **eco-dim®** model guarantees at least 15% energy savings compared to a standard switch

incandescent/halogen

single pole	600W	DV-600P-	
		DVSC-600P-	
single pole	1000W	DV-10P-	
		DVSC-10P-	
3-way	600W	DV-603P-	
		DVSC-603P-	
3-way	1000W	DV-103P-	
		DVSC-103P-	

incandescent/halogen – eco-dim®† NEW

single pole/3-way	600W	DV-603PG-	
-------------------	------	------------------	--

magnetic low-voltage

single pole	600VA (450W)	DVLV-600P-	
		DVSCLV-600P-	
single pole	1000VA (800W)	DVLV-10P-	
		DVSCLV-10P-	
3-way	600VA (450W)	DVLV-603P-	
		DVSCLV-603P-	
3-way	1000VA (800W)	DVLV-103P-	
		DVSCLV-103P-	

Suggested maximum lighting load for magnetic low-voltage dimming is 450W for 600VA products and 800W for 1000VA products, to allow for transformer losses.

electronic low-voltage*

single pole	300W	DVELV-300P-	
		DVSCELV-300P-	
3-way	300W	DVELV-303P-	
		DVSCELV-303P-	

* requires neutral wire connection

† available in white, ivory, almond, and light almond

screw base compact fluorescent dimming with Philips® DIMMABLE Energy Saver CFL NEW



- use **only** with **PHILIPS®** models:
EL/A
R30 DIM
R40 DIM
PAR38 DIM
- includes locator light
- no derating if ganged
- always turn on, regardless of slider setting
- isolates bulb from unstable line voltage

screw base dimmable compact fluorescent

single pole/3-way	200W	DVPDC-203P-	
-------------------	------	--------------------	--

Standard incandescent/halogen dimmers are not UL listed for screw base dimmable compact fluorescent (CFL) lamps.

colors & finishes key

- available in gloss finish
- available in satin finish
- available in all gloss and satin finishes

See page 69 for available colors.

To order, add color suffix to model number.

Example: **DVSC-600P- HT**

fluorescent dimming with Hi-lume®, Compact SE™, Eco-10®, EcoSystem® ballasts, and Hi-lume® LED



- use with Lutron® 3-wire line-voltage control electronic dimming ballasts
- please refer to the Lutron® Fluorescent Dimming Systems Selection Guide (P/N 366-002) for more information
- includes locator light
- no derating if ganged

fluorescent*

single pole/3-way 8A 120V	DVF-103P- 
single pole/3-way 8A 120V	DVSCF-103P- 
single pole/3-way 6A 277V	DVF-103P-277- 
single pole/3-way 6A 277V	DVSCF-103P-277- 

LED with Hi-lume® LED driver only* NEW

single pole/3-way 8A 120V	DVF-103P- 
single pole/3-way 8A 120V	DVSCF-103P- 
single pole/3-way 6A 277V	DVF-103P-277- 
single pole/3-way 6A 277V	DVSCF-103P-277- 

LED with GRX-TVI (0-10 VDC sink control)* NEW

single pole/3-way 16 A load 30 mA control 120/277V	DVF-103P- 
single pole/3-way 16 A load 30 mA control 120/277V	DVSCF-103P- 

* requires neutral wire connection

fluorescent dimming with Tu-Wire® ballasts



- use with Lutron® Tu-Wire® line-voltage control electronic dimming ballasts
- includes locator light
- for information on using Lutron® dimmers to control Advance® Mark 10® dimming ballasts, visit the Lutron® website at www.lutron.com/advance
- must be derated if ganged

fluorescent Tu-Wire®

single pole/3-way 5A	DVFTU-5A3P- 
	DVSCFTU-5A3P- 

colors & finishes key

-  available in gloss finish
-  available in satin finish
-  available in all gloss and satin finishes

See page 69 for available colors.

To order, add color suffix to model number.

Example: **DVFTU-5A3P- WH**

fan controls



- paddle turns on/off
- slide up to increase, down to decrease
- 3 quiet fan speeds for increased comfort
- no derating if ganged
- for use with only one ceiling paddle fan
- does not include locator light

quiet 3-speed control

single pole/3-way	1.5A	DVFSQ-F-	
		DVSCFSQ-F-	

quiet 3-speed control

(for use with specific fans such as Hunter Original Series)

single pole/3-way	2.0A	DVFSQ-F-HO-	
-------------------	------	--------------------	---

coordinating switches



- paddle turns on/off
- use with any 15A load
- general purpose switching of all sources and motor loads
- no derating if ganged

general purpose switches (120/277 V)

single pole	15A	CA-1PSH-	
		SC-1PS-	
3-way	15A	CA-3PSH-	
		SC-3PS-	
4-way	15A	CA-4PSH-	
		SC-4PS-	

general purpose switch with locator light

(120 V only)

single pole	15A	CA-1PSNL-	
		SC-1PSNL-	
3-way	15A	CA-3PSNL-	
		SC-3PSNL-	
4-way	15A	CA-4PSNL-	
		SC-4PSNL-	

colors & finishes key

-  available in gloss finish
-  available in satin finish
-  available in all gloss and satin finishes

See page 53 for available colors.
To order, add color suffix to model number.
Example: **DVFSQ-F- WH**