





4700 W. 160th St.  
Cleveland, OH 44135  
PH:800-321-9532  
FX:800-321-9535  
www.oatey.com

**ACCESS ABLE®  
ACCESS PANELS**



**TECHNICAL SPECIFICATION**

**TECHNICAL SPECIFICATION:** Oatey Access Able Access Panels are designed to allow access to service areas. Access Panels can be used for access to plumbing, electrical, security systems, telephone, computer cables, and sprinkler systems. Reversible feature allows for flush mounting or surface mounting.



**PHYSICAL/CHEMICAL PROPERTIES**

Material High Impact ABS  
Color White

**DIRECTIONS FOR USE**

**Surface Mount Installation:** Cut appropriate size opening using frame as a template. Check for level. Apply construction adhesive to backside of frame flange. Fit frame into opening. Press flange against wall to ensure flat installation. After adhesive is set, snap door into place.

**Flush Mount Installation:** Nail or screw frame into place at desired location with flange flat against the stud. Check for level. Drywall or plaster to the top of the flange. Snap on door after wall covering is complete.

**COMMON APPLICATIONS**

Oatey Access Panels provide access to service areas, while allowing an easy installation into wall surface. Patented clips on panel door and frame eliminate sagging or bowing of door in ceiling applications.

✓	PRODUCT NUMBER	DESCRIPTION	Actual Door Size		Frame Size to Outer Flange		Wall Opening		PACK
			A	B	C	D	E	F	
	34054	4" x 6" Access Panel	4"	6"	5-1/4"	7-1/4"	4 1/4"	6-1/4"	12
	34055	6" x 9" Access Panel	6"	9"	8-1/4"	11-1/4"	6-3/8"	9-3/8"	6
	34045	8" x 8" Access Panel	8"	8"	10-1/4"	10-1/4"	8-3/8"	8-3/8"	6
	34056	14" x 14" Access Panel	13-3/4"	13-3/4"	17"	17"	14"	14"	6
	34044	14" x 29" Access Panel	13-3/4"	29"	17"	32-1/4"	14"	29-1/2"	6

Data is subject to manufacturing tolerances.