

PRODUCT SPECIFICATION DRAWING **HOLDRITE® QUICK FLEX™ Connectors**



HOLDRITE® QUICK FLEX™ Connectors are designed to provide fast and easy connections for water heaters and other equipment, such as boilers, water softeners, etc. They are made of large-ID corrugated stainless steel tube, which has higher flow rates than standard copper or braided connectors and isolates against electrolysis. These connectors are more flexible than standard copper flex connectors and are less likely to kink. Available in several sizes from 3/4" to 2" FIP connectors and from 12" - 24" lengths. For water use ONLY.

Product Information:

- Material: 304 Stainless Steel
- Chrome Plated Brass Nut (FIP x FIP swivel nuts)
- Meets ASME A112.18.6
- IAPMO Listed
- Meets UPC and IPC Codes
- Pressure rating: 125 Service/200 Max PSI
- Temperature rating: 190 Degrees
- Full Flow Connector - no Restrictions
- EPDM washer for chemical compatibility
- Easy Installation
- Complies with CA Lead Law



Product Submittal	
Job Name:	
Date:	
Part Number:	Qty:
Architect / Owner:	
Contractor:	
Notes:	