


### **SPECIFICATION SHEET**

## **E661 RANGE HOOD**



The Broan Elite E661 model is part of our new generation of range hoods: stylish, powerful, and most of all, quieter than ever.

#### **FEATURES**

- Sleek, classic smooth shell design makes cleaning easy
- Created to work over high BTU residential grade cooking equipment
- Colors available: White or Black durable powder-coated paint finishes for 30" and 36" widths, and Stainless Steel for 30". 36" or 42" widths
- Dishwasher safe aluminum filters with metal latch
- Dual 50-Watt halogen lights focus toward the center for brilliant full cooktop lighting (MR16 GU10 bulbs not included)
- New High Flow centrifugal blower wheel provides greater performance and quieter operation
- Flush-mounted electro-mechanical controls with Amber-Yellow LED status lights
- 5-minute off delay
- Broan Heat Sentry automatically turns blower to third speed when excess cooking heat is detected
- Versatile design allows for a 3¼"x 14" horizontal or vertical discharge

#### **SPECIFICATIONS**

Volts		120	
HZ		60	
Amps		2.4	
CFM (high)		300*	
Sones (norm.	)	<0.3	
Sones (high)		3.0*	
Controls	3-speed	electronic with memory, plus boos	t mode.
Halogen Flood Light		MR16 GU10 <sup>†</sup>	
Broan Heat Sentry		Yes	
+==0 ( 0.0			

<sup>\* 550</sup> cfm & 8.5 sones in boost mode.

#### **TYPICAL SPECIFICATION**

Range hood shall be Broan Elite E661.

Unit shall be for indoor use only.


Unit will have all over smooth design, with no sharp edges. Finish to be powder-coated paint (brushed finish stainless steel). It must have a fully enclosed stainless steel bottom and full aluminum filters.

Hood discharge to be 31/4" x 14", horizontal or vertical.

Range hood to have a centrifugal blower and twin, 50-watt (max.) halogen flood max. Blower and light shall be operated using a specially-designed, 3-speed control with boost, memorizes last setting, with 5-minute delayed "off".

Air delivery shall be no less than 550 cfm. Sound level to be no greater than 0.3 sones/110 cfm - 3.0 sones/300 cfm - 8.5 sones/550 cfm (boost mode).

Air and sound ratings to be certified by HVI. Unit shall be U.L. and cU.L. listed.





HVI-2100 CERTIFIED RATINGS comply with the new testing technologies and procedures prescribed by the Home Ventilation Institute, for off-the-shelf products, as they are available to consumers. Product performance is rated at 0.1 in. static pressure, based on tests conducted in a state-of-the-art laboratory. Sones are a measure of humanly produced loudness, based on laboratory measurements.

Broan-NuTone LLC Hartford, Wisconsin www.broan.com 800-558-1711 Broan-NuTone Canada Mississauga, Ontario www.broan.ca 877-896-1119

REFERENCE	QTY.	REMARKS	Project
			Location
			Architect
			Engineer
			Contractor
			Submitted by Date

90M 99043668C

<sup>&</sup>lt;sup>†</sup>2 bulbs req. (not included).

# BROAN ELITE E661 HOOD SYSTEM

