

# Peerless Boilers SERIES 63

**Residential Gas Fired,  
Packaged or Knockdown, Hot Water or Steam Boilers**  
7 Sizes ■ 3-6 Sections ■ 88.5 to 287.5 MBH Input ■ Up to 83.5% AFUE

## Features:

### Natural or LP Gas

### Standing Pilot or Spark Ignition

### Natural Draft (Chimney) Venting

- Single Vent Draft Hood

### Factory Assembled Sections on Knockdown Boilers

- Reduces Installation Time

### Large Water Content

- Ideal for Steam and Large Volume Hot Water Applications
- 3" Supply and 2½" Return

### Skim Tapping

- For Cleaning Steam Boilers

### Low Profile Design

- Horizontal to Vertical Draft Diverter
- Ideal for Installations with Low Ceilings

### Steel Push Nipples

- Provide a Permanent Water Tight Seal Between Sections
- Unaffected by Petroleum and Other Contaminants

### Deluxe Insulated Enameled Steel Jacket

- Reduces Boiler Heat Loss
- Completely Encloses Gas Valve and Burners

### Slide-in, Preassembled Burner Tray

### Preassembled Wiring Harness for KD

### Safety Controls

- Low Water Cut-Off on Steam Boilers
- Flame Roll-Out Shut-Off Switch
- Blocked Vent Shut-Off Switch



## Standard Equipment:

- Honeywell Operating Controls
- Vent Damper
- Probe Type LWCO on Steam Boilers

## Optional Equipment:

- Circulator on Hot Water Boilers



We are pleased to offer one of the most comprehensive warranty programs in the industry. All residential cast iron boilers include a full one-year warranty. A limited, lifetime warranty is provided for the cast iron sections of Peerless residential hot water boilers. We also provide a limited, ten-year warranty on the cast iron sections of its residential steam boilers. Five and ten-year extended warranties on parts and labor are now available. Please consult us for complete warranty information.



Printed on  
Recycled Paper

PeerlessBoilers.com



PeerlessBoilers.com

FAB-63 R2 (11/09-2M)  
Printed in U.S.A.