

Peerless Boilers SERIES MI/MIH

Packaged Residential Gas Fired, Hot Water Boilers

7 Sizes ■ 3-9 Sections ■ 65.0 to 260.0 MBH CSA Input ■ Up to 83% AFUE

Features:

MI Model Available for Natural or LP Gas

- Standing Pilot (3-9 section) with 80% AFUE
- Honeywell SmartValve® Intermittent Ignition (3-9 section) with 82% AFUE

MIH Mid-Efficiency Model Available in 3-6 Sections for Natural Gas

- Honeywell SmartValve® Intermittent Ignition with 83% AFUE
- Qualifies for Utility Company Energy Rebates in Some Areas

Natural Draft (Chimney) Venting

Low Profile Design

- Internal Horizontal to Vertical Draft Diverter
- Ideal for Installations with Low Ceilings

Steel Push Nipples

- Provide a Permanent Water Tight Seal Between Sections
- Unaffected by Petroleum and Other Contaminants

Deluxe Insulated Enameled Steel Jacket

- Reduces Boiler Heat Loss
- Completely Encloses Gas Valve and Burners

Safety Controls

- Vent Safety Shutoff Switch
- Flame Rollout Safety Shutoff Switch



Standard Equipment:

- Standing Pilot or Honeywell SmartValve® Intermittent Ignition
- Honeywell Operating Controls
- Taco Circulator
- Elec. Operated Automatic Vent Damper

Optional Equipment:

- Grundfos Circulator
- 50 PSI Safety Relief Valve
- Non-Combustible Floor Pan

®SmartValve is a registered trademark of Honeywell Corporation.



We are pleased to offer one of the most comprehensive warranty programs in the industry. All residential cast iron boilers include a full one-year warranty. A limited, lifetime warranty is provided for the cast iron sections of Peerless residential hot water boilers. We also provide a limited, ten-year warranty on the cast iron sections of its residential steam boilers. Five and ten-year extended warranties on parts and labor are now available. Please consult us for complete warranty information.



PeerlessBoilers.com



PeerlessBoilers.com

FAB-MI R4 (3/08-5M)
Printed in U.S.A.