

# Copper Pipe Dimensions

| Nominal or Standard Size, inches | Nominal Dimensions, inches |                 |
|----------------------------------|----------------------------|-----------------|
|                                  | Outside Diameter           | Inside Diameter |
| 1/4                              | .375                       | .305            |
| 3/8                              | .500                       | .402            |
| 1/2                              | .625                       | .527            |
| 5/8                              | .750                       | .652            |
| 3/4                              | .875                       | .745            |
| 1                                | 1.125                      | .995            |
| 1 1/4                            | 1.375                      | 1.245           |
| 1 1/2                            | 1.625                      | 1.481           |
| 2                                | 2.125                      | 1.959           |
| 2 1/2                            | 2.625                      | 2.435           |
| 3                                | 3.125                      | 2.907           |
| 3 1/2                            | 3.625                      | 3.385           |
| 4                                | 4.125                      | 3.857           |
| 5                                | 5.125                      | 4.805           |
| 6                                | 6.125                      | 5.741           |
| 8                                | 8.125                      | 7.583           |
| 10                               | 10.125                     | 9.449           |
| 12                               | 12.125                     | 11.315          |

| Nominal or Standard Size, inches | Nominal Dimensions, inches |                 |
|----------------------------------|----------------------------|-----------------|
|                                  | Outside Diameter           | Inside Diameter |
| 1/4                              | .375                       | .315            |
| 3/8                              | .500                       | .430            |
| 1/2                              | .625                       | .545            |
| 5/8                              | .750                       | .666            |
| 3/4                              | .875                       | .785            |
| 1                                | 1.125                      | 1.025           |
| 1 1/4                            | 1.375                      | 1.265           |
| 1 1/2                            | 1.625                      | 1.505           |
| 2                                | 2.125                      | 1.985           |
| 2 1/2                            | 2.625                      | 2.465           |
| 3                                | 3.125                      | 2.945           |
| 3 1/2                            | 3.625                      | 3.425           |
| 4                                | 4.125                      | 3.905           |
| 5                                | 5.125                      | 4.875           |
| 6                                | 6.125                      | 5.845           |
| 8                                | 8.125                      | 7.725           |
| 10                               | 10.125                     | 9.625           |
| 12                               | 12.125                     | 11.565          |

| Nominal or Standard Size, inches | Nominal Dimensions, inches |                 |
|----------------------------------|----------------------------|-----------------|
|                                  | Outside Diameter           | Inside Diameter |
| 3/8                              | .500                       | .450            |
| 1/2                              | .625                       | .569            |
| 3/4                              | .875                       | .811            |
| 1                                | 1.125                      | 1.055           |
| 1 1/4                            | 1.375                      | 1.291           |
| 1 1/2                            | 1.625                      | 1.527           |
| 2                                | 2.125                      | 2.009           |
| 2 1/2                            | 2.625                      | 2.495           |
| 3                                | 3.125                      | 2.981           |
| 3 1/2                            | 3.625                      | 3.459           |
| 4                                | 4.125                      | 3.935           |
| 5                                | 5.125                      | 4.907           |
| 6                                | 6.125                      | 5.881           |
| 8                                | 8.125                      | 7.785           |
| 10                               | 10.125                     | 9.701           |
| 12                               | 12.125                     | 11.617          |

| Nominal or Standard Size, inches | Nominal Dimensions, inches |                 |
|----------------------------------|----------------------------|-----------------|
|                                  | Outside Diameter           | Inside Diameter |
| 1 1/4                            | 1.375                      | 1.295           |
| 1 1/2                            | 1.625                      | 1.541           |
| 2                                | 2.125                      | 2.041           |
| 3                                | 3.125                      | 3.030           |
| 4                                | 4.125                      | 4.009           |
| 5                                | 5.125                      | 4.981           |
| 6                                | 6.125                      | 5.959           |
| 8                                | 8.125                      | 7.907           |



**PexSupply.com**