

Dielectric Nipples • Spec Sheet



Thread X Thread



Grove X Grove



Thread X Grove

FEATURES & BENEFITS

- 300 PSI
- Rated up to 230° F
- Approvals - ASTM A53, ANSI B1.20.1 & ASTM F492-95
- Sizes 3/4" - 4"

MATERIAL SPECIFICATIONS

- Galvanized Dielectric Nipples
- Pex Liner
- Metal to Metal design

Thread X Thread

Part #	Size
DNTT04212	3/4" x 2-1/2"
DNTT043	3/4" x 3
DNTT044	3/4" x 4
DNTT054	1" x 4
DNTT064	1-1/4" x 4
DNTT074	1-1/2" x 4
DNTT084	2" x 4
DNTT096	2-1/2" x 6"
DNTT106	3" x 6"
DNTT116	4" x 6"

Grove X Grove

Part #	Size
DNTG084	2" x 4"
DNTG096	2-1/2" x 6"
DNTG106	3" x 6"
DNTG116	4" x 6"

Thread X Grove

Part #	Size
DNGG084	2" x 4"
DNGG096	2-1/2" x 6"
DNGG106	3" x 6"
DNGG116	4" x 6"

 **MATCO-NORCA**
Global sourcing. National compliance. Local service.

CALIFORNIA 5593 Fresca Dr., La Palma CA 90623 • Toll Free: 866-532-8306 • Fax: 866-532-8307
TEXAS 1150 Silber Rd., Houston TX 77055 • Toll Free: 800-935-5456 • Fax: 713-680-2999
NEW YORK PO Box 27, Rt. 22, Brewster NY 10509 • Toll Free: 800-431-2082 • Fax: 845-278-9056
 WEB: www.matco-norca.com EMAIL: mail@matco-norca.com