Ready, Set, Go Programming

High Output Digital Wall Heater



green wizard



- ► READY, SET, GO PROGRAMMING
 - SMARTSERIES® DIGITAL THERMOSTAT
- **▶** CONTROL YOUR COMFORT
 - EASY-TO-USE CUSTOMIZABLE CONTROL
- ► SAVE ENERGY WITH ZONAL HEATING
- ► SAVE TIME AND MONEY ON INSTALLATION
 'OUT OF THE BOX' SET-UP
- ► APPLICATIONS INCLUDE:
 - RESTAURANTS
 - HOTELS
 - CONFERENCE ROOMS
 - ATRIUM
 - ... AND MUCH MORE









OUTSMART THE COMPETITION

SELECTION CHART


CATALOG					
NUMBER	UPC	VOLTS	WATTS	AMPS	BTUHR
SSH04008	6 85360 15669 9	208	1800 - 4000	8.7 - 19.2	13,650
SSH04004	6 85360 15671 2	240	1800 - 4000	7.5 - 16.7	13,650
SSH04007	6 85360 15673 6	277	1800 - 4000	6.5 - 14.4	13,650
SURFACE MOUNTING	FRAMES				
HTWHSM	6 85360 15545 6	Surface Mounting Frame 16-1/4" W x 19-3/8" H x 3-7/8" D			
HTWHS1	6 85360 15548 7	1" Semi-Recess Mounting Frame 16-1/4" W x 19-3/8" H x 1" D			

Note: Standard grille color is Northern White, Add NV (Navajo White) or SB (Stat Bronze) suffix to catalog number. Example: SSHO4008NV Allow two weeks delivery for models with special color. See Color Selection Chart for custom colors.

6 85360 15551 7

THERMOSTAT DISPLAY

HTWHS2



AVAILABLE COLOR OPTIONS

Grilles are available in three colors:







Navajo White Statuary Bronze

MOUNTING LIMITATIONS

Do not install heater closer than 12" to the floor, 12" to an adjacent wall, 36" to the ceiling. Do not install heater behind towel rack or door, upside down or sideways, in the floor, in the ceiling, or in closets.

FEATURES

- Heat where you are, not where you aren't . Instant response when you want it. Save energy by heating only the areas you occupy.
- Precise heat within 1.5 degree of set temperature (as compared to five degrees with conventional bi-metal thermostats.)
- ▶ 5 day / 2 day programmability (5 weekdays and 2 day weekend, 4 program periods per day).
- SmartSeries provides only the amount of heat needed at any given moment by continually calculating heat output and fan speed of the proportional difference between room temperature and the set temperature.
- ► Hold mode maintains constant set temperature which can be used for freeze protection or vacation setting for when you are not there.
- ▶ BMS compatible Connects to Building Management Systems for optimum control.
- ► Lockout Feature Securely maintain comfort levels.

2" Semi-Recess Mounting Frame 16-1/4" W x 19-3/8" H x 2" D

- Remote control to make adjustments anywhere in the room Catch a chill? Raise the temperature from the comfort of your bed or easy chair.
- Quick set up 'right out of the box' 3 piece construction Includes back box, Element/Fan Deck and Grille
- Fits recessed between standard studs walls or use with optional surface mounting frame (ideal for block or plaster walls).
- No ducting or plumbing needed means no heat loss before the heat enters the room.

DIMENSIONS

