

Gutter Outlet



Catalog Number	Description	Frame Dimensions in. (cm.)	Net Wt. lbs. (kg)
GOT	Tool Frame	19x10 (48x25)	6.70 (3.04)
	PUNCH AND DIE ASSEMBLIES		
	2.2" x 3.2" (56 x 81 mm) OVERSIZE Rectangular Hole (See descriptions above.)	_	_
GOP23LUK	Punch and Die Assy - Upgrade Kit	_	2.20 (1.00)
	2" x 3" (51 x 76 mm) Standard Rectangular Hole	_	_
GOP23UK	Punch and Die Assy - Upgrade Kit	_	2.20 (1.00)
	3" x 4" (76 x 102 mm) Standard Rectangular Hole	_	_
GOP34UK	Punch and Die Assy - Upgrade Kit	=	2.50 (1.13)
	2" x 3" (51 x 76 mm) X-Style (No drop required. Fasten downspout securely to ears created by X.)	_	_
GOP23XUK	Punch and Die Assy - Upgrade Kit	=	1.90 (0.86)
	REPLACEMENT BLADES AND CHOCKS		
GOTRC	Replacement Chocks for (GOT)	_	_
GOP23LRB	Replacement Blade for (GOP23LUK)	_	1.30 (0.60)
GOPRB	Replacement Blade for (GOP23UK)	=	1.30 (0.60)
GOP34RB	Replacement Blade for (GOP34UK)	=	1.80 (0.82)
GOP23XRB	Replacement Blade for (GOP23XUK)	=	_

OVERSIZED DROPS Larger nominal 2"x 3" (56x81 mm) drops compatible with the GOP23LUK include: Amerimax | Berger Brothers | Buchner Mfg. | Clendenon | Gutter Suppliers | Lynch Aluminum | MetalTech | Matteo luminum | Petit | Raytec | US Aluminum



Works anywhere to attach gutter to fascia with ease.

Use the Malco Gutter Nail Driver with hidden hangers and 8D galvanized nails to hang aluminum or steel gutters. A non-slip ergonomic grip provides multiple positions for grasping tool and working from above or below roof overhang. Durable 2-piece steel construction plus weather resistant zinc and nickel plating assure long service life of this professional quality tool.



Ideal for end caps on gutter.

Slide adjustment for throat depth allows settings from 1/4" to 5/8" (6 to 16 mm) depth. Also used to crimp end caps on gutter. Nickel plate and black oxide finish. Formed metal cutting jaws. Ergonomic Redline Handles with unique one-hand operation latch offer maximum compound leverage performance and natural fit and feel.



Produces a double crimp that downsizes without deforming down-spout; walls stay square for a tight fitting, leakproof connection.

Tool also features rust resistant plating. Ergonomic Redline Handles with unique one-hand operation latch offer maximum compound leverage performance and natural fit and feel.



Light Duty tool without grips.

Makes a single crimp for downsizing aluminum downspouts.

Specifications

Catalog				Variable Le	verage Ratio			Length	Net Wt.	
Number	Description		Throat Depth in. (mm) (High / Low) throughout stroke	Jaws		in. (mm)	oz. (g)	
GND	Gutter Nail Driver		_					7-5/8 (194)	7 (199)	
SL2R	One-Inch Hand Note	her	1/4 to 5/8 (6.4 to	15.9) —				8 (203)	16 (454)	
C4R	5 Blade Crimper		1-1/4 (31.8)	7.1 to 1.0 -	9.8 to 1.0	Carbo	on Steel	9 (229)	16 (454)	
SC2	Snap Lock Punch		1-1/8 (28.6)	_				8 (203)	8 (227)	
CAPACITIES	Material	Aluminum	Copper	Stainless Steel 26 Gauge	Galvanized Steel 24 G	auge	Mild Steel 24	Gauge		
C4R	inches (mm)	0.35 (0.89)	0.23 (0.58)	0.18 (046)	0.28 (0.71)		0.24 (0.61)			

Replacement Spring for Hand Tools

5018 Fits C4R, SL2R