Liberty Pumps[®]



Builders Series Submersible Sump Pump

1/3 hp 1/4" Solids Handling 1-1/2" Discharge

Features:

- Quiet running, heavy-duty
 1/3 hp motor
 - Dual ball bearings
- Cast iron motor plate
- High suction ports to reduce potential jamming
 - High capacity flow rates
 - 10' standard power cord



100000000000

innovate.

Vertical Float

Model S37

ewolwe.

Year Warranty

S30-Series

Builders Series Submersible Sump Pump

The S30-Series from Liberty was designed to handle the problem areas of sump pumps in new home construction. Powered by a durable 1/3 hp motor, the S30-Series offers larger clearances around the impeller for better solids and debris handling.

BASIC CONSTRUCTION AND FEATURES:

- Rugged and quiet 1/3 hp motor. Oil filled, thermally protected.
- Permanently lubricated upper and lower ball bearings.
- · Stainless steel rotor shaft.
- 1/4" solids-handling with higher intake screening helps reduce debris from entering the pump compared to bottom suction designs.
- Bi-directional dual lip shaft seal.
- 1-1/2" NPT discharge.
- Thermoplastic vortex style impeller with improved clearances for better debris handling.
- 10' power cord.
- Water directed flow in cast motor plate allows for improved cooling of motor.
- · Stainless steel fasteners.
- High head 25' shut off.

MOTOR SPECIFICATIONS:

1/3 hp 115 volt 6.5 amps 60 Hz. 3450 RPM

Thermally protected

Maximum fluid temperature 140° F

Model S37


Height: 13" Width: 9%" Length: 9%" Weight: 14 lbs. Turn-on level 8.25" Turn-off level 2.75"

Model S38

Height: 10.5" Width: 9¾" Length: 9¾" Weight: 14 lbs. Turn-on level 12" Turn-off level 3.5"

Help eliminate jamming from debris. Use "The Brick" sump pump platform for a professional installation. Part #4445000

S30-SERIES PERFORMANCE 60 hz





Certified Specifications are subject to change without notice.