

**HOSES & HOSE
SPECIALTIES**

CLEAR VINYL TUBING

W-R#	I.D.	O.D.	Length
0809000	1/8"	3/16"	100'
0809001	1/8"	1/4"	100'
0809002	1/4"	3/8"	100'
0809004	5/16"	7/16"	100'
0809006	3/8"	1/2"	100'
0809008	1/2"	5/8"	100'
0809010	5/8"	7/8"	100'
0809012	3/4"	1"	50'
0809014	1"	1 1/4"	50'

ICE-MAKER TUBING

W-R#	I.D.	O.D.	Length
0809020	1/8"	1/4"	100'

- Bulk ice-maker tubing


**BRASS INSERT
STIFFENER
- LEAD FREE -**


W-R#	SIZE	Min	Box
4A00119	1/4" Insert	25	25
4022002	3/8" Insert	25	25
4022004	1/2" Insert	25	25


HOSE CLAMPS


CARBON	STAINLESS	SAE	Min.	Max.
2208004	2209004	#4	1/4"	5/8"
2208006	2209006	#6	3/8"	7/8"
2208008	2209008	#8	7/16"	1"
2208010	2209010	#10	1/2"	1 1/16"
2208012	2209012	#12	1/2"	1 1/4"
2208016	2209016	#16	3/4"	1 1/2"
2208020	2209020	#20	3/4"	1 3/4"
2208024	2209024	#24	1"	2"
2208028	2209028	#28	1 5/16"	2 1/4"
2208032	2209032	#32	1 9/16"	2 1/2"
2208036	2209036	#36	7/8"	2 3/4"
2208040	2209040	#40	1 1/8"	3"
2208052	-	#52	1 7/8"	3 3/4"
2208072	-	#72	3 1/8"	5"
2208088	-	#88	5 1/8"	6"

- 10 per box

HOSES & HOSE SPECIALTIES

3/4" FHT HOSE CAP

W-R#		Min	Box
2607002	Brass	12	12
4607002	Lead-Free Brass	12	12
2606002	Brass Plated	12	12
2605002	Plastic	12	12
- Brass hose caps furnished with washer			


3/4" FHT HOSE CAP WITH CHAIN

W-R#		Min	Box
2607004	Brass	1	12
4607004	Lead-Free Brass	1	12

- Furnished with washer and 6" chain


HOSE NIPPLES

SIZE	Lead Free#	Non-potable#
3/4" MH x 3/4" MIP	4610002	2610002
3/4" MH x 1/2" MIP	4610004	2610004
3/4" MH x 3/4" MH	4610006	2610006
3/4" MH x 1/2" MIP x 1/2" SWT	4610008	2610008
3/4" MH x 3/4" MIP x 1/2" FIP	4610010	2610010



SIZE	Lead Free#	Non-potable#
3/4" MH x 3/4" FIP	4610012	2610012
3/4" MH x 1/2" FIP	4610014	2610014



Call 800-221-1157 to check availability for "261-" series brass hose nipples for non-potable use only.

SIZE	Lead Free#	Non-potable#
3/4" FH x 3/4" FIP	4610016	2610016
3/4" FH x 1/2" FIP	4610018	2610018
3/4" FH x 3/4" FH	4610020	2610020



SIZE	Lead Free#	Non-potable#
3/4" FH x 1/2" MIP	4610028	2610028
3/4" FH x 3/4" MIP	4610030	2610030
3/4" FH x 1/2" MIP x 1/2" SWT	4610032	2610032


SWIVEL HOSE NIPPLES

SIZE	Lead Free#	Non-potable#
3/4" FH x 3/4" FIP	4610022	2610022
3/4" FH x 1/2" FIP	4610024	2610024
3/4" FH x 3/4" FH	4610026	2610026

- All hose nipples are 12 per bag

HOSES & HOSE SPECIALTIES

**RUBBER
HOSE WASHERS**

W-R#		Min	Box
2724002	Bulk	100	100
2724004	10 to clip	36 clips/box	


**INLET HOSE FILTER
SCREEN**

W-R#		Min	Box
0533002		25	25


**SIAMESE 3/4" HOSE
CONNECTION WITH
SHUT OFF**

W-R#		Min	Box
2601002	Die Cast	1	12
2603003	All Brass	1	12

- For outdoor watering use


**3/4" SIAMESE
CONNECTION**

W-R#		Min	Box
2602002	Die Cast	1	12
2603002	Brass	1	12

- For outdoor watering use


**FROST PROOF
SILLCOCK**

W-R#		Min	Box
0407502	6"	1	12
0407504	8"	1	12
0407506	12"	1	12

- For outdoor watering use


**HOSE BIBB MOUNTING
PLATE**


W-R#		Min	Box
0623602	Mounting Plate	1	12

- Zinc-plated steel plate to cover annular space around hose bibbs and sillcocks.
- Mounting hardware included


**3/4" HOSE VACUUM
BREAKER
- LEAD FREE-**


W-R#		Min	Box
4418000	3/4"	1	12

- With break-off set screw
- FH x MH connection

HOSES & HOSE SPECIALTIES

**VANDAL-PROOF
QUARTER-TURN
SILLCOCKS**

W-R#		Min	Box
0404002	1/2" IPS	1	12
0404006	1/2" SWT	1	12

- For outdoor watering use


**"HOSE-MATE"
SILLCOCK RETROFIT
VALVE -LEAD FREE -**


W-R#		Box
RV900LF	3/4 FH Swivel x MH	6

The **RV900 "Hose-Mate"** is a rugged, machined-brass solution for frozen sillcocks or other hose connections.


**DIE CAST
VALVE HANDLE**

W-R#		Min	Box
0420002	Square	1	12
0420004	Round	1	12

- 12 pt


SILLCOCK KEY

W-R#		Min	Box
0421002	5/16"	1	12
0421000	1/4"	1	12


4-WAY SILLCOCK KEY

W-R#		Min	Box
0421004		1	12

- Fits stems 1/4", 9/32", 5/16" and 11/32"


**STOP AND WASTE
CAPS**

With washer

W-R#		Min	Box
0419006	5/16"	10	10
0419008	3/8"	10	10


**FIRE HYDRANT TO
3/4"MH ADAPTER**

W-R#		Min	Box
2604002	2 1/2" Hydrant	1	-


**"BIBBLOCK" HOSE
BIBB LOCKOUT**

W-R#		Min	Box
2607500	"Bibblock"	1	-

- Eliminates unauthorized use of water!
- Vandal-proof design!
- Lock sold separately.

HOSES & HOSE SPECIALTIES

5/8" GARDEN HOSES


W-R#		Min	Box
1803000	50' Tire Cord	1	5
1803002	50' Rubber/Vinyl	1	5
1803006	50' Premium	1	5
1803008	25' Premium	1	5

- **Premium** Rubber Hoses 1803006 & 8 rated for temperatures up to 180°


9-SPRAY PISTOL GRIP HOSE NOZZLE

W-R#	
2609502	7" 9-Pattern Spray

- Durable Metal Construction
- Insulated Handle Grip for hot & cold applications
- Soft Cushioned Grip


INSULATED PISTOL GRIP HOSE NOZZLE

W-R#	
2609702	Heavy-Duty Insulated

- Solid Metal Body
- Insulated Handle Grip for hot & cold applications
- Nylon Handle


BRASS TWIST HOSE NOZZLE

W-R#	
2609602	7" Brass Twist Nozzle

- Durable Metal Construction
- Insulated Handle Grip for hot & cold applications
- Soft Cushioned Grip


C.P. ECONOMY PISTOL GRIP HOSE NOZZLE

W-R#	Min	Box
2609002	1	12


4" BRASS HOSE NOZZLE

W-R#	Min	Box
2608002	1	12

**HOSES & HOSE
SPECIALTIES**


**WATER HAMMER
ARRESTERS**
- LEAD FREE -

LEAD-FREE

NEW!

W-R#		Min	Box
4320002	1/2" MIP	1	12
4320004	1/2" Sweat	1	12

- rated to 200 psi



**WATER HAMMER
ARRESTER TEES**
- LEAD FREE -

LEAD-FREE

NEW!

W-R#	Description	Min
4320010	1/4" OD X 1/4" OD	1
4320012	3/8" OD X 3/8" OD	1
4320014	5/8" OD X 5/8" OD	1

W-R#	Description	Min
4320016	1/2" PEX x 1/2" PEX	1



**WATER HAMMER
COMPRESSION
RETROFIT TEES**
- LEAD FREE -

LEAD-FREE

NEW!

W-R#	Description	Min
4320020	3/8" OD X 3/8" Female Compression	1



3/8" OD Female connection to fit
existing stops



3/4" MH

**WATER HAMMER
ARRESTER FOR
WASHING MACHINE**
- LEAD FREE -

LEAD-FREE

NEW!

W-R#	Description	Min
4320030	3/4" FH X 3/4" MH	1

3/4" FH

**HOSES & HOSE
SPECIALTIES**
**SEWAGE EJECTOR
CHECK VALVE**


W-R#		Min	Box
0414204	1½" I.P.S.	1	24
0414206	2" I.P.S.	1	24
0414208	1 1/2" x 1 1/4"	1	24
0414210	3" w/Cast Iron Body	1	24


**COMPRESSION
SEWAGE EJECTOR
CHECK VALVE**

W-R#		Min
0414606	2" Compression	1


**"SILENT-CHECK"
SEWAGE EJECTOR
CHECK VALVE**

W-R#		Min
0414302	1 1/2" Silent Check	1
0414304	2" Silent Check	1


NEW!

W-R#		Min
0414706	2" Silent Check -Compression-	1



W-R#		Min
0414806	2" Silent Check -True Union-	1



W-R#		Min
0414812	2" Silent Check -True Union- with Ball Valve	1

HOSES & HOSE SPECIALTIES

SUMP PUMP DRAIN HOSE KIT


W-R#		Min	Box
0810002	1 1/4" X 24'	1	8
0810004	1 1/2" X 24'	1	6
0810010	1 1/2" MIP X 1 1/4" Adapter	1	12

• Included in kit are 24' corrugated plastic hose. 1 1/4" plastic male adapter and stainless clamp, individually packaged.


GAS RANGE CONNECTOR ADAPTER


W-R#		Min	Box
0814102	5/8" Flare x 1/2" FIP		25
0814104	5/8" Flare x 3/4" FIP		25
0814106	5/8" Flare x 1/2" MIP		25
0814108	5/8" Flare x 3/4" MIP		25


STAINLESS STEEL GAS RANGE CONNECTOR

Yellow Epoxy Coated



W-R#		Min	Box
0813004	1/2" x 24"	1	12
0813008	1/2" x 36"	1	12
0813012	1/2" x 48"	1	12
0813014	1/2" x 60"	1	12
0813016	1/2" x 72"	1	12


CSA GAS BALL VALVES


W-R#	Description	Min	Box
0400120	1/2"	12	12
0400122	3/4"	12	12