Braeburn.

2 Zone Panel 140202 for Residential and Light Commercial Applications

Braeburn Zone Control Panels feature the latest in zone controls. Our economical two zone panels deliver maximum value for all two zone applications. Equipment and status can be determined at a glance with the monitoring LEDs built into the panel. User economy is improved with built in features such as last zone purge and economical opposite mode calling.

Quick and Easy Installation

Braeburn zone panels are designed with the features that customers demand: easy installation, at-a-glance status, quick and reliable wiring terminals—all in an attractive six inch by six inch panel. Braeburn, your best source for zoning.

Specifications

Panel Power	4 VA maximum (3.5 VA typical) for panel	
System Power	4 VA (Zone Panel) + 1.0 VA per thermostat plus damper requirements, not to exceed 35 VA	
Protection	Electronic self resetting current limiting	
Equipment	Relay driven 2A at 24 VAC	
Zone Damper Control	Compatible with power open/power close, spring open/power close and spring close/power open dampers	
Indicators (6)	Power OK, status, equipment Rh, Rc, Damper 1 PO, PC; Damper 2 PO, PC	
Switches	Non HP/HP, dual fuel no/yes, reversing valve B active/0 active, fan control plenum/system, opposite mode call timer 20/15, 2nd stage lockout none/active, priority all/zone 1	
Terminals	Rh, Rc, Y1, G, W1/E/W3, W2/O-B, C, E-Heat; panel power (2) and R, Y, G, W, C, PO, C, PC for each zone	

Braeburn Zone Control Systems



Product Features and Benefits

- Compact 6" x 6" foot print maintains system appearance
- Suitable for residential and light commercial applications
- · Can be used with conventional four or five wire thermostats
- Quick connect terminals speed installation and reliability
- Compatible with electric, gas, oil and heat pump equipment
- · Controls 2 heating and 1 cooling stage
- Emergency heat switch with remote terminals for total heat pump control
- Fan purge into last calling zone for improved energy efficiency
- The value choice in 2 zone panels

The brighter choice®

Braeburn.

Braeburn Zone Control Systems2 Zone Panel 140202, for Residential and Light Commercial Applications

Architectural Specifications

The fully automatic zone panel shall be Braeburn model number 140202 6.00" high x 6.00" wide x 1.25" deep, powered from 24 Volts AC. In the event of a power failure, the unit shall retain all configuration settings. The zone panel shall be compatible with low voltage 4 or 5 wire mechanical or electronic thermostats and be capable of controlling up to two stages of heating and one stage of cooling. Wiring blocks with terminals R, Y, G, W, and C shall be included for two thermostat and one emergency heat position. Equipment terminals Rh, Rc, Y, G, W1/E, W2/O-B, and C shall be present along with two sets of damper terminals PO, C, and PC. Configuration options shall be available for System Type- Heat Pump / Non-Heat Pump, Dual Fuel- Yes / No, Reversing Valve- B Active / O Active, Fan Control- Plenum / System, Opposite Mode Timer- 20 / 15 minutes, 2nd stage Lockout- None / Active, and Zone Priority- All / Zone 1. LEDs (Light Emitting Diodes) shall be present to monitor Panel Power (1), Panel Processor (1), HVAC equipment power (2), and outputs for two dampers (2). Provisions shall be available to disable short cycle protection. The panel shall have an operating temperature of 0 to 50° C, and a storage temperature of -10 to 60° C with an operating humidity range of 5 to 95% RH non-condensing.

Specifications		
Power	24 VAC	
Indicators	6 LED Indicators	
Construction	PC Board in High Impact Housing	
Mounting	Wall or Return Air Plenum Mount	
Environmental	Storage - 40° F to 150° F (-40° to 65° C) Operating - 20° F to 125° F (-30° F to 50° C)	

Zone Panel Selection		
Description	Item No.	
2 Zone 2H / 1C	140202	
3 Zone 3H / 2C	140303	

The Braeburn Advantage

The Best Value in Zoning Today™

- Suitable for light commercial and residential installation
- Designed for years of trouble free operation
- Fully compatible with Braeburn and other zoning system components

Braeburn Thermostats and Accessories

From our Premier Series to our economical Builder Series, Braeburn has the products you need to lower energy costs and increase comfort in any home or business environment.

Call Us Toll-Free 866.268.5599 (U.S.) **+1.630.844.1968** (Outside the U.S.) **www.braeburnonline.com**