

# Series 1510 Centrifugal Pump Kits

**PUMP KITS INCLUDE:**

1. Full Size Bronze Impeller
2. Cast Iron Volute
3. Volute Cover Plate and Gasket

4. Nameplate
5. Impeller Cap Screw and Washer

**ACCESSORY KITS INCLUDE:**

1. Support Foot
2. Motor Saddle (if required)
3. Pump Riser (if required)

**BRONZE FITTED PUMPS**

PUMP SIZE	MOTOR FRAME	PUMP KIT PART NO.	COUPLER PART NO.	BEARING ASSY. PART NO.	SEAL KIT PART NO.	BASE PART NO.	ACCESSORY KIT
1¼ AC	56	191310	186868	185011	186862	P85285	191970
	143 - 145T		186869			P85285	191970
	182 - 184T		186870			P85286	191972
	213 - 215T		186871			P85287	191975
1½ AC	56	191602	186868	185011	186862	P85285	191970
	143 - 145T		186869			P85285	191970
	182 - 184T		186870			P85286	191972
	213 - 215T		186871			P85287	191975
2 AC	56	191312	186868	185011	186862	P85285	191970
	143 - 145T		186869			P85285	191970
	182 - 184T		186870			P85286	191972
	213 - 215T		186871			P85287	191975
254T	186873	P85288	191979				
2½ AB	56	191314	186868	185011	186862	P85285	191970
	143 - 145T		186869			P85285	191970
	182 - 184T		186870			P85286	191972
	213 - 215T		186871			P85287	191975
254T	186873	P85288	191979				
3 AC	143 - 145T	191600	186869	185011	186862	P85285	191970
	182 - 184T		186870			P85286	191972
4 AC	143 - 145T	191552	186869	185011	186862	P85286	191971
	182 - 184T		186870			P85286	191973
	213T		186871			P85287	191976
5 A	182 - 184T	191554	186870	185011	186862	P85286	191993
	213 - 215T		186871			P85287	191978
1¼ BC	143 - 145T	191311	186869	185011	186862	P85286	191971
	182 - 184T		186870			P85286	191973
1½ BC	143 - 145T	191470	186869	185011	186862	P85286	191971
	182 - 184T		186870			P85286	191973
	213 - 215T		186871			P85287	191976
2 BC	143 - 145T	191313	186869	185011	186862	P85286	191971
	182 - 184T		186870			P85286	191973
	213 - 215T		186871			P85287	191976
2½ BB	182 - 184T	191315	186870	185011	186862	P85286	191973
	213 - 215T		186871			P85287	191976
3 BC	182 - 184T	191603	186870	185011	186862	P85286	191973
	213 - 215T		186871			P85287	191976
	254T		186873			P85288	191979
4 BC	213 - 215T	191316	186871	185011	186862	P85287	191978
	254T		186873			P85288	191981

PUMP SIZE	MOTOR FRAME	PUMP KIT PART NO.	COUPLER PART NO.	BEARING ASSY. PART NO.	SEAL KIT PART NO.	BASE PART NO.	ACCESSORY KIT
5 BC	213 - 215T	191576	186871	185011	186862	P85289	191994
	254T		186873			P85289	191995
5 BC	256T	191568	186874	185014	186543	P85289	191990
	284T		P63242			P85290	191984
6 BC	254T	191584	P63239	185014	186543	P85289	191990
	256T		186874			P85289	191990
	284T		P63242			P85290	191984
2E	184T	191299	186870	185011	186862	P85298	191993
	213 - 215T		186871			P85298	191978
	254T		186873			P85298	191981
3E	213 - 215T	191300	186871	185011	186862	P85298	191978
	254T		186873			P85298	191981
3E	256T	191301	186874	185014	186543	P85289	191989
4E	215T	191302	186871	185011	186862	P85298	191978
	254T		186873			P85298	191981
4E	256T	191303	186874	185014	186543	P85289	191989
	284T		P63242			P85290	191985
5E	254T	191304	P63239	185014	186543	P85289	191990
	256T		186874			P85289	191990
	284T		P63242			P85290	191984
	286T		P63244			P85290	191984
	324T		P63245			P85290	191996
6E	284T	191305	P63242	185014	186543	P85291	191986
	286T		P63244			P85291	191986
	324T		P63245			P85291	191987
	326T		P63247			P85291	191987
	364T		P63248			P85291	191988
2 G	213 - 215T	191325	186872	185014	186543	P85289	191982
	254T		P63239			P85289	191989
	256T		186874			P85289	191989
3 G	213 - 215T	191326	186872	185014	186543	P85289	191982
	254T		P63239			P85289	191989
	256T		186874			P85289	191989
	284T		P63242			P85290	191985
4 GB	213 - 215T	191605	186872	185014	186543	P85289	191983
	254T		P63239			P85289	191990
	256T		186874			P85289	191990
	284T		P63242			P85290	191984
	286T		P63244			P85290	191984
5 G	254T	191328	P63239	185014	186543	P85291	191991
	256T		186874			P85291	191991
	284T		P63243			P85291	191986
	286T		P63244			P85291	191986
	324T		P63245			P85291	191987
	326T		P63247			P85291	191987
6 G*	256T	191329	186874	185014	186543	P85291	191991
	284T		P63243			P85291	191986
	286T		P63244			P85291	191986
	324T		P63245			P85291	191987
	326T		P63247			P85291	191987
	364T		P63248			P85291	191988
	365T		P63250			P85291	191988
	404TS		P63253			P85291	191992

\* Large Bearing Frame Only, maximum impeller diameter 12 1/2".



## Bell & Gossett

**USA**  
 Bell & Gossett  
 8200 N. Austin Avenue  
 Morton Grove, IL 60053  
 Phone: (847) 966-3700  
 Facsimile: (847) 966-9052  
 www.bellgossett.com



**INTL.**  
 Bell & Gossett / Export Dept.  
 8200 N. Austin Avenue  
 Morton Grove, IL 60053  
 Phone: (847) 966-3700  
 Facsimile: (847) 966-8366  
 www.bellgossett.com

**CANADA**  
 Fluid Products Canada  
 55 Royal Road  
 Guelph, Ontario,  
 N1H 1T1, Canada  
 Phone: (519) 821-1900  
 www.itfpc.ca