

## LEAKATOR® 10

**Combustible Gas Leak Detector** 

**Leak Detection** 





## **Bacharach Makes Leak Detection Easy**

Bacharach's Leakator 10 is a low maintenance combustible gas leak detection unit, small enough to be operated with just one hand, yet loaded with the kind of advanced features and technology professionals demand.

Powered for up to 30 hours of continuous operation by alkaline C-cell batteries, Leakator 10 comes complete with a flexible 20-inch long probe for hard-to-reach areas and a solid state sensor that will last for up to five years. Leakator 10 allows you to pinpoint large and small leaks quickly, while checking a relatively large area in a short amount of time.

\*Only available by ordering P/N 19-7063

Headquarters: 621 Hunt Valley Circle, New Kensington, PA 15068 U.S.A.

Phone: 1-800-736-4666 Canada: 1-800-328-5217 E-Mail: help@bacharach-inc.com Website: www.bacharach-inc.com



## Features & Benefits

- Visual Indicator 10 Ultra-bright LEDs
- Audible Indicator Loud audible ticking rate
- 30 Hour Battery Life Easily replaced C-cells
- Sensitivity Thumb-Wheel Aids pinpointing leak detection
- Operational Status LEDs English and international systems
- Solid State Sensor
  Plug-in sensor, five year typical life

- 20 Inch Flexible Probe For hard to reach locations
- Tough ABS Plastic Housing Durable and rugged
- Carrying Strap Easy to use
- **UL Listed** Intrinsically safe
- **CE Mark** Electronic performance standard



SPECIFICATIO	
Housing	Molded, three piece ABS plastic in bright yellow color, includes carrying strap
Power	Five alkaline C-cells, not provided 30 hours typical life for continuous operation
Warm-up Time	Automatic, self check, about ten seconds to operational condition
Sensor	Semiconductor type. Five year typical life. Plug-in replacement
Probe	Self storing 20 inch flexible probe. Accommodates integral sensor
Sensitivity	20 ppm useable sensitivity (methane)
Status indicators	Visual: 10 ultra-bright red LED's. Audible: Variable speed ticking sound. Earphone available for use in noisy environments. Power-On ultra-bright green LED, Fail ultra-bright yellow LED. Low Battery ultra-bright yellow LED
Environments	23° to 130°F (-5° to 54°C), 10% to 90% relative humidity, non-condensing
Dimensions / Weight	Leakator: 18 oz. (0.51Kg.), 8.5" x 2.25" x 1.75" (21.6 cm x 5.7 cm x 4.4 cm) Case: Black HDPE, 17 oz. (.48Kg), 10.5" x 7" x 3" (26.7 cm x 17.8 cm x 7.6 cm)
Safety Approvals	UL listed, intrinsically safe, for use in Class I, Division 1, Groups A, B, C, and D classified areas
Warranty	One year limited warranty. See warranty card for more information

ORDERING INFORMATION	
PART NO.	DESCRIPTION
19-7051	LEAKATOR 10, in custom carrying case, UL Listed, flexible 20 inch probe for combustible gases and vapors, with instruction manual (batteries not included)
19-7063	Leakator ETO - For detection of Ethylene Oxide
19-0398	Replacement sensor and matching resistor
19-0397	Replacement rigid carrying case
19-3091	Replacement flexible probe assembly
51-2529	Optional Earphone

## **Distributed By:**





Leakator and Bacharach are registered trademarks of Bacharach Inc.

©August, 2002, Bacharach, Inc., all rights reserved. All information herein is subject to verification.

Product Bulletin-4098 08/02 10M DXC

Printed in U.S.A.