

Emerson™ Builder's Series Filter Driers

- Economical System Protection for Air Conditioning Applications
- ODF - Solid Copper Connections for Easy Installation
- Solid Core Construction
- 40 Micron Filtration
- Maximum Working Pressure = 680 psig



Liquid Line Service

PCN	Model	Water Capacity drops R-22 @ 125 °F	Flow Capacity Tons *	
			R-22	R-410A
066122	BSL-053S	36	4.9	4.8
066123	BSL-083S	51	4.6	4.5
066125	BSL-084S	51	7.6	7.4
066098	BSL-163S	70	5.3	5.2
066099	BSL-164S	70	9.3	9.1

Suction Line Service

PCN	Model	Water Capacity drops R-22 @ 125 °F	Flow Capacity Tons *	
			R-22	R-410A
066126	BSS-165S	72	3.4	3.5
066127	BSS-166S	72	4.1	4.2
066128	BSS-167S	72	4.1	4.2
066100	BSS-305S	111	3.4	3.5
066101	BSS-306S	111	5.4	5.5
066129	BSS-307S	111	5.9	6.0
066102	BSS-309S	111	6.1	6.2

Bi-Flow Service

PCN	Model	Water Capacity drops R-22 @ 125 °F	Flow Capacity Tons *	
			R-22	R-410A
066130	BSB-083S	154	5.1	5.1
066131	BSB-163S	223	5.2	5.1

* Ratings in accordance with AHRI Standard 710

† Ratings in accordance with AHRI Standard 730



2008ECT-165 R3 (01/14) Emerson is a trademark of Emerson Electric Co.
©2014 Emerson Climate Technologies, Inc. All rights reserved. Printed in the USA.

EMERSON. CONSIDER IT SOLVED.™