"JUALITY FUMPS SINCE 1939"

Product information presented here reflects conditions at time of publication. Consult factory regarding discrepancies or inconsistencies.



MAIL TO: P.O. BOX 16347 • Louisville, KY 40256-0347 SHIP TO: 3649 Cane Run Road • Louisville, KY 40211-1961 (502) 778-2731 • 1 (800) 928-PUMP • FAX (502) 774-3624

SECTION: 4.10.100 FM0217 0705 Supersedes 1104

visit our web site: www.zoeller.com



THE "FULL-FLOW" UNICHECKS

- 30-0163 30-0152 2" CAST IRON NPT 1¹/₄" CAST IRON NPT · Vertical or horizontal installation. Full flow design - no restrictions. 30-0164 30-0160 1¹/₂" CAST IRON NPT **3" CAST IRON NPT** · Stops backflow of water. • Standard, 11/4", 11/2", 2", 3" female NPT pipe. Neoprene polyester reinforced flapper - smooth edge design, with cast iron and noncorrosive metal backing plates & stainless steel fastener. COATED TOUGH · Corrosion resistant powder coated epoxy finish. Rated at 50 PSI (115 feet of head) at 130°F Stainless steel bolts. 1 per carton. Weight: 30-0163, 7.5 lbs.; 30-0164, 7.5 lbs.; 30-0152, 10 lbs.; 30-0160, 18 lbs. Outside dimensions Outside dimensions 30-0163 30-0160 · Suitable for installation below basin cover. Pictured 6 5/8" W x 6 5/8" W x 8" H 5 1/16" W x 4" W x 6 1/4" H Pictured 30-0021 2" PLASTIC SLIP X SLIP UNIONS 30-0151 Hinnin 2" CAST IRON SLIP X SLIP UNIONS Full 2" flow design - meets BOCA (P.604.2) stainless steel clamps for low pressure systems. 2" Full Flow Pump Code. Avoid more than 10 ft. static head above the check valve, 4.3 PSI at 130°F. Checks backflow of water and sewer gas. Simple to install (no threading of pipe Stainless steel screws. required). Save time & material costs. Extra wide hinge to reduce hinge stress. · Plastic check has PVC body and can be Neoprene gasket and flapper, weighted with heavy stainless steel metal backing plates and installed with solvent welded couplings for stainless steel rivet. pressure systems to 25 PSI (57 ft. of Head). (P/N 30-0023) Can be installed on vertical or horizontal line. Slips over ABS, PVC, steel pipe or copper Model 30-0151 has corrosion resistant IL IIII (TO) powder coated epoxy finish. piping. Reduces motor and pump noise from plumbing Stainless Steel sleeves available to meet Illinois plumbing code. C.I. 30-0201 / PVC 30-0202. system. Meets requirements of Wisconsin Uniform Plastic check individual rack pack Model Plumbing Code. 30-0021 30-0022. 30-0151 PVC PLASTIC CAST IRON Flexible neoprene slip x slip union includes 6 per carton. 30-0181 / 30-0200 11/2" or 11/4" SLIP X SLIP UNION

 - Flapper bends over a radius, no sharp 90° edges—lengthens life of flapper hinge.
 - PVC plastic check body, ultrasonically welded and can be solvent welded for rigid pressure rated piping systems to 25 PSI - (57 ft. of Head) at 130°F. (30-0182).
 - Vertical or horizontal installation.
 - Available in individual packages for pegboard display (30-0191).
- All stainless steel screws, nuts and clamps on model 30-0200 only.
- Slip x Slip for 4.3 PSI (10 ft. of Head) at 130°F. Avoid more than 10 ft. static head above the check valve.
- Designed to reduce water hammer.
- 10 per carton.



HIGH TEMPERATURE "FULL-FLOW" UNICHECKS



- Use with 2000 & 3000 Series High Temperature Pumps.
- Vertical or horizontal installation.
- Full flow design no restrictions.
- Stops backflow of water.
- Standard, 11/4", 11/2", 2" female NPT pipe.
- EPDM strand reinforced flapper smooth edge design, with cast iron and noncorrosive metal backing plates & stainless steel fastener.
- Corrosion resistant powder coated epoxy finish.
- Rated at 50 PSI (115 feet of head) at 200°F
 - Stainless steel bolts.
- 1 per carton.
- Weight: 30-0214, 7.5 lbs.; 30-0215, 7.5 lbs.; 30-0216, 10 lbs.

<u>/Tri-Check</u>

30-0100

1½" PVC CHECK VALVE / BALL VALVE / UNION COMBINATION 30-0101

2" PVC CHECK VALVE / BALL VALVE / UNION COMBINATION

FEATURES:

- Full flow check valve design.
- Threaded union allows pump to be removed without disrupting discharge piping.
- · Saves time and money Easy to install.
- · Neoprene gasket and flapper, weighted with stainless steel backing plates and stainless steel rivet.
- · Can be installed on vertical or horizontal pipe.
- Meets plumbing codes requiring a ball valve installed in conjunction with a check valve.
- · All stainless steel screws.
- Replaceable flapper in the check valve.
- Extra wide hinge to reduce stress.
- Rated for 25 psi (58 ft. of head).
- 6 Per carton (30-0100 & 30-0101).
- 9 Per carton (30-0102 & 30-0103).



www.zoeller.com

© Copyright 2005 Zoeller Co. All rights reserved.

The "Combo"



30-0102 1½" PVC CHECK VALVE / UNION COMBINATION 30-0103 2" PVC CHECK VALVE / UNION COMBINATION

Manufacturers of . .

"Quality Pumps Since 1939"