THIS SPACE FOR DESIGNER/ENGINEER APPROVAL					
Job/Customer	Date	Contractor			
Model Specified	Qty	Approved By			
Designer/Engineer	Date	Contractor's PO#			
Submitted by	Date	Other			

4067 Series

T-Drain™
Full Port Forged Brass Fitting
w/ Hi-Flow Hose Drain
IPS
600 WOG
ISO 9001






ITEM #	SIZE	CTN	CASE	Α	В	С	D
40672	1/2"	10	80	1/2	1 15/16	1/2	2 15/16
40673	3/4"	8	48	3/4	2 5/16	1/2	3 7/16
40674	1"	8	48	1	2 5/16	1/2	3 13/16
40675	1 1/4"	6	24	1 1/4	2 7/8	3/4	4 1/4
40676	1 1/2"	4	24	1 1/2	2 7/8	3/4	4 5/8
40677	2"	2	20	2	3	3/4	5 3/16



NO.	DESCRIPTION	MATERIAL
1	BODY	BRASS
2	END CAP	BRASS
3	SEAT	PTFE
4	BALL	BRASS HCP
5	STEM	BRASS
6	STEM SEAL	PTFE
7	PACKING GLAND	BRASS
8	HANDLE	ENAMEL COATED ALUMINUM
9	HANDLE SCREW	BRASS
10	CAP & STRAP	BRASS W/ EPDM STRAP
11	WASHER	EPDM



TEMP °F	PSI
100	600
150	490
200	470
250	439
300	411
350	294
366	N/A

Specifications: Designed for residential, commercial or industrial use with water, oil or gas. This approved Webstone valve is actuated by a blowout proof stem and features an adjustable packing gland. Threaded ends comply with ANSI B1.20.1.



Quality and Commitment Since 1954