

tekmar® - User Brochure

Thermostat 507

U 507

05/07

Congratulations on the installation of your tekmar Control Systems' thermostat. This thermostat has been designed with state of the art technology and packaged in a compact and attractive enclosure. The large display and easy to use buttons make this thermostat extremely user friendly. This tekmar Control Systems' thermostat is designed to increase the comfort level of your home. At the same time these thermostats have been designed to be simple to use.

Table of Contents

Display / Keypad Operation.....	pg 1
Setting the Temperatures	pg 2
Units of Display.....	pg 2
Setting the Mode of Operation	pg 3
Warranty	pg 4

Display / Keypad Operation

The thermostat's display has four distinct fields. These fields are the **Menu** field, the **Item** field, the **Number** field and the **Status** field. The four buttons on the face of the thermostat are used to navigate through the menus and items to view and/or adjust the desired settings.

Menu Field


Displays the current menu

Item Field

Displays an abbreviated name of the selected item

Status Field

Displays the current status of the thermostat's inputs, outputs and operation



Number Field

Displays the current value of the selected item

Buttons

Selects Menus, Items and adjusts settings

Display Symbols



Warning

Displays when an error exists.

H1

Heat One

Displays when the heat contact is on.

SETTING THE TEMPERATURE(S) ——————

Use the following procedure to set the desired air temperature.

- Step One:** Press and release the **Menu** button until the Adjust Menu is reached.
- Step Two:** Press and release the **Item** button until the desired item is displayed.
- Step Three:** Use the **^** or **<** button to set the desired temperature.



UNITS OF DISPLAY ——————

To select between Fahrenheit and Celsius, use the following procedure.


- Step One:** Press and release the **Menu** button until the Adjust Menu is reached.
- Step Two:** Press and release the **Item** button until the current temperature unit begins to flash.
- Step Three:** Use the **^** or **<** button to select between Fahrenheit and Celsius.



SETTING THE MODE OF OPERATION

Use the following procedure to select the mode of operation.

- Step One:** Press and release the **Menu** button until the Adjust Menu is reached.
- Step Two:** Use the **^** or **▼** button to select between the Off and Heat setting.
- Off:** In the Off mode, the thermostat does not operate the heating device.
- Heat:** In the Heat mode, the thermostat operates to maintain the room at the required heating temperature.



Limited Warranty and Product Return Procedure

Limited Warranty *The liability of tekmar under this warranty is limited. The Purchaser, by taking receipt of any tekmar product ("Product"), acknowledges the terms of the Limited Warranty in effect at the time of such Product sale and acknowledges that it has read and understands same.*

The tekmar Limited Warranty to the Purchaser on the Products sold hereunder is a manufacturer's pass-through warranty which the Purchaser is authorized to pass through to its customers. Under the Limited Warranty, each tekmar Product is warranted against defects in workmanship and materials if the Product is installed and used in compliance with tekmar's instructions, ordinary wear and tear excepted. The pass-through warranty period is for a period of twenty-four (24) months from the production date if the Product is not installed during that period, or twelve (12) months from the documented date of installation if installed within twenty-four (24) months from the production date.

The liability of tekmar under the Limited Warranty shall be limited to, at tekmar's sole discretion: the cost of parts and labor provided by tekmar to repair defects in materials and / or workmanship of the defective product; or to the exchange of the defective product for a warranty replacement product; or to the granting of credit limited to the original cost of the defective product, and such repair, exchange or credit shall be the sole remedy available from tekmar, and, without limiting the foregoing in any way, tekmar is not responsible, in contract, tort or strict product liability, for any other losses, costs, expenses, inconveniences, or damages, whether direct, indirect, special, secondary, incidental or consequential, arising from ownership or use of the product, or from defects in workmanship or materials, including any liability for fundamental breach of contract.

The pass-through Limited Warranty applies only to those defective Products returned to tekmar during the warranty period. This Limited Warranty does not cover the cost of the parts or labor to remove or transport the defective Product, or to reinstall the repaired or replacement Product, all such costs and expenses being subject to Purchaser's agreement and warranty with its customers.

Any representations or warranties about the Products made by Purchaser to its customers which are different from or in excess of the tekmar Limited Warranty are the Purchaser's sole responsibility and obligation. Purchaser shall indemnify and hold tekmar harmless from and against any and all claims, liabilities and damages of any kind or nature which arise out of or are related to any such representations or warranties by Purchaser to its customers.

The pass-through Limited Warranty does not apply if the returned Product has been damaged by negligence by persons other than tekmar, accident, fire, Act of God, abuse or misuse; or has been damaged by modifications, alterations or attachments made subsequent to purchase which have not been authorized by tekmar; or if the Product was not installed in compliance with tekmar's instructions and / or the local codes and ordinances; or if due to defective installation of the Product; or if the Product was not used in compliance with tekmar's instructions.

THIS WARRANTY IS IN LIEU OF ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, WHICH THE GOVERNING LAW ALLOWS PARTIES TO CONTRACTUALLY EXCLUDE, INCLUDING, WITHOUT LIMITATION, IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, DURABILITY OR DESCRIPTION OF THE PRODUCT, ITS NON-INFRINGEMENT OF ANY RELEVANT PATENTS OR TRADEMARKS, AND ITS COMPLIANCE WITH OR NON-VIOLATION OF ANY APPLICABLE ENVIRONMENTAL, HEALTH OR SAFETY LEGISLATION; THE TERM OF ANY OTHER WARRANTY NOT HEREBY CONTRACTUALLY EXCLUDED IS LIMITED SUCH THAT IT SHALL NOT EXTEND BEYOND TWENTY-FOUR (24) MONTHS FROM THE PRODUCTION DATE, TO THE EXTENT THAT SUCH LIMITATION IS ALLOWED BY THE GOVERNING LAW.

Product Warranty Return Procedure All Products that are believed to have defects in workmanship or materials must be returned, together with a written description of the defect, to the tekmar Representative assigned to the territory in which such Product is located. If tekmar receives an inquiry from someone other than a tekmar Representative, including an inquiry from Purchaser (if not a tekmar Representative) or Purchaser's customers, regarding a potential warranty claim, tekmar's sole obligation shall be to provide the address and other contact



tekmar Control Systems Ltd., Canada
tekmar Control Systems, Inc., U.S.A.
Head Office: 5100 Silver Star Road
Vernon, B.C. Canada V1B 3K4
(250) 545-7749 Fax. (250) 545-0650
Web Site: www.tekmarcontrols.com

Product design, software and literature
are Copyright © 2007 by:
tekmar Control Systems Ltd. and tekmar
Control Systems, Inc.

