

QUICK RESPONSE AUTOMATIC SPRINKLERS GL SERIES UPRIGHT • PENDENT VERTICAL SIDEWALL HORIZONTAL SIDEWALL CONVENTIONAL (OLD STYLE)

DESCRIPTION AND OPERATION

The Globe Quick Response GL Series Sprinklers are a low profile yet durable design which utilizes a 3mm frangible glass ampule as the thermosensitive element. This provides sprinkler operation approximately six times faster than ordinary sprinklers. While the Quick Response Sprinkler provides an aesthetically pleasing appearance, it can be installed wherever standard spray sprinklers are specified when allowed by the applicable standards. It offers the additional feature of greatly increased safety to life and is available in various styles, orifices, temperature ratings and finishes to meet many varying design requirements. Quick Response Sprinklers should be used advisedly and under the direction of approving authorities having jurisdiction.

The heart of Globe's GL Series sprinkler proven actuating assembly is a hermetically sealed frangible glass ampule that contains a precisely measured amount of fluid. When heat is absorbed, the liquid within the bulb expands increasing the internal pressure. At the prescribed temperature the internal pressure within the ampule exceeds the strength of the glass causing the glass to shatter. This results in water discharge which is distributed in an approved pattern depending upon the deflector style used.



UPRIGHT



CONVENTIONAL

QUICK RESPONSE

QUICK RESPONSE

PENDENT

VERTICAL SIDEWALL

TECHNICAL DATA

- See reverse side for Approvals and Specifications.
- •Temperature Ratings 135°F (57°C), 155°F (68°C), 175°F (79°C), 200°F (93°C), 286°F (141°C)
- •Water Working Pressure Rating 175 psi (12 Bars)
- Factory tested hydrostatically to 500 psi (34 Bars)
- •Maximum low temperature glass bulb rating is -67°F (-55°C)
- •Frame bronze Deflector brass Screw brass
- •Bulb seat copper Spring nickel alloy Seal teflon
- •Bulb glass with alcohol based solution, 3mm size



QUICK RESPONSE
HORIZONTAL SIDEWALL

SPRINKLER TEMPERATURE RATING/CLASSIFICATION and COLOR CODING

CLASSIFICATION	AVAILABLE TEMPER		BULB COLOR		MAXIMUM MPERATURE
ORDINARY	135°F/155°F	57°C/68°C	ORANGE/RED	100°F	38°C
INTERMEDIATE	175°F/200°F	79°C/93°C	YELLOW/GREEN	150°F	66°C
HIGH	286°F	141°C	BLUE	225°F	107°C

4077 AIRPARK DRIVE, STANDISH, MICHIGAN 48658

989-846-4583 • FAX 989-846-9231

QUICK RESPONSE

AUTOMATIC SPRINKLERS GL SERIES

Upright • Pendent • Vertical Sidewall Horizontal Sidewall • Conventional (Old Style)

SPECIFICATIONS

NOMINAL "K" FACTOR		THREAD SIZE	LENGTH 1	FINISHES		
2.8	(39 metric)	1/2" NPT	2 1/4" (5.7 cm)	Factory Bronze		
4.2	(59 metric)	1/2" NPT	2 1/4" (5.7 cm)	Bright Chrome Satin Chrome ²		
5.6	(80 metric)	1/2" NPT	2 1/4" (5.7 cm)	White Polyester ³		
7.8	(111 metric)	1/2" NPT	2 1/4" (5.7 cm)	Black Polyester 2,3		
8.1	(116 metric)	3/4" NPT	2 7/16" (6.2 cm)	Lead Coated ^{2,3}		

NOTE: METRIC CONVERSIONS ARE APPROXIMATE.

¹ HORIZONTAL SIDEWALL IS 2 9/16". ² FINISHES AVAILABLE ON SPECIAL ORDER. ³ AVAILABLE AS cULus LISTED CORROSION RESISTANT WHEN SPECIFIED ON ORDER.

APPROVALS

71111011120												
STYLE	SIN MODEL	K FACTOR	135°F 57°C	155°F 68°C	175°F 79°C	200°F 93°C	286°F 141°C	cULus	F.M.	LPC	CE	NYC - DOB MEA 101-92-E
UPRIGHT	GL2815	2.8	Х	Х	Х	Х	Х	Х				Х
	GL4215	4.2	X	Х	Х	Х	Х	Х				X
	GL5615	5.6	X	Х	Х	Х	Х	Х	Χ	Х	X	X
	GL8115	7.8*	X	Х	Х	Х	Х	Х				X
	GL8118	8.1	Χ	Х	Х	Х	Х	Х	Χ	Χ	Х	X
PENDENT	GL2801	2.8	X	Х	Х	Х	Х	Х				X
	GL4201	4.2	X	Х	Х	Х	Х	Х				X
	GL5601	5.6	Χ	Х	Х	Х	Х	Х	Χ	Х	Х	X
	GL8101	7.8*	Χ	Х	Х	Х	Х	Х	Χ			X
	GL8106	8.1	Χ	Х	Х	Χ	Х	Х	Χ	X	X	X
VERTICAL SIDEWALL†	GL5632	5.6	Х	Х	Х	Х	Х	Х	Х			
	GL8133	8.1	X	Х	Х	Х	Х	Х				
HORIZONTAL SIDEWALL §	GL2826	2.8	X	Х	Х	Х	Х	Х				Х
	GL4226	4.2	Х	Х	Х	Х	Х	Х				X
	GL5626	5.6	X	Х	Х	Х	Х	Х	X			X
	GL8127	8.1	X	Х	Х	Χ	Х	Х				
CONVENTIONAL (OLD STYLE)	GL5624	5.6	Х	Х	Х	Х	Х			Х	Х	
	GL8125	8.1	X	Х	X	Х	X			Х	Χ	

ORDERING INFORMATION SPECIFY

- QuantityModel NumberStyle
- Orifice Thread Sizes Temperature
- Finishes desired
- Quantity Wrenches P/N 325390 (1/2");
 P/N 312366 (L.O.)



*1/2" NPT

- † VERTICAL SIDEWALL SPRINKLER cULus LISTED FOR LIGHT HAZARD ONLY. PENDENT VERTICAL SIDEWALL cULus LISTED FOR 6' MIN. SPACING. UPRIGHT VERTICAL SIDEWALL cULus LISTED FOR 9' MIN. SPACING.
- § HORIZONTAL SIDEWALL cULus LISTED FOR DEFLECTOR 4" TO 12" BELOW THE CEILING, FM APPROVED 4" TO 6".

GLOBE® PRODUCT WARRANTY

Globe agrees to repair or replace any of its own manufactured products found to be defective in material or workmanship for a period of one year from date of shipment.

For specific details of our warranty please refer to Price List Terms and Conditions of Sale (Our Price List).

4077 AIRPARK DRIVE, STANDISH, MICHIGAN 48658 989-846-4583 FAX 989-846-9231 1-800-248-0278 www.globesprinkler.com