



For Commercial & Residential Applications

Job Name _____
 Job Location _____
 Engineer _____
 Approval _____

Contractor _____
 Approval _____
 Contractor's P.O. No. _____
 Representative _____

Metal Elbows



| MODEL | ✓ TO SUBMIT | DESCRIPTION | DIMENSIONS | | | | FINISH |
|------------------------------|-------------|--------------|------------|-----|-------|-----|--------------------|
| | | | A | | B | | |
| | | | in. | mm. | in. | mm. | |
| Low Down Flush Elbows | | | | | | | |
| 605 103 | | 2" x 4" x 6" | 6 | 152 | 4 | 102 | 20 GA. Chrome |
| 606 103 | | 2" x 5" x 7" | 7 | 178 | 5 | 127 | 20 GA. Chrome |
| 607 103 | | 2" x 6" x 8" | 8 | 203 | 6 | 152 | 20 GA. Chrome |
| Slip Joint Elbows | | | | | | | |
| 624 061 | | 1 1/4" x 6" | 6 | 152 | 2 1/2 | 64 | 22 GA. Rough Brass |
| 624 063 | | 1 1/4" x 6" | 6 | 152 | 2 1/2 | 64 | 22 GA. Chrome |
| 625 081 | | 1 1/4" x 8" | 8 | 203 | 2 1/2 | 64 | 22 GA. Rough Brass |
| 625 083 | | 1 1/4" x 8" | 8 | 203 | 2 1/2 | 64 | 22 GA. Chrome |
| 627 121 | | 1 1/4" x 12" | 12 | 305 | 2 1/2 | 64 | 22 GA. Rough Brass |
| 627 123 | | 1 1/4" x 12" | 12 | 305 | 2 1/2 | 64 | 22 GA. Chrome |
| 627 221 | | 1 1/2" x 12" | 12 | 305 | 2 1/2 | 64 | 22 GA. Rough Brass |
| 627 223 | | 1 1/2" x 12" | 12 | 305 | 2 1/2 | 64 | 22 GA. Chrome |

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.



Brass & Tubular Products

USA: 815 Chestnut St., No. Andover, MA 01845-6098; www.watts.com
Canada: 5435 North Service Rd., Burlington, ONT. L7L 5H7; www.wattscanada.ca
 ES-WB&T-Mtl-Elbows 0752