

ProPress for Stainless 304



ProPress for Stainless 304

viega

Viega ProPress for Stainless 304

Viega ProPress for Stainless is the total system solution where optimum corrosion protection or chemical resistance is required. All fittings offer Viega's patented Smart Connect feature, the quick and easy way to identify unpressed connections.

FEATURES and BENEFITS

- Connections are made in four to seven seconds
- Same tool used on all Viega press systems
- Ensures a consistent, strong, reliable seal for liquids or gases
- Reduces system installation time and job site clean up
- Requires less pipe preparation than other joining methods
- Eliminates costly downtime
- Reduced maintenance problems
- No hot work, burn permits or fire watches needed

CODES and STANDARDS

- ASTM A312: Standard Specification for Seamless Welded and Heavily Cold Worked Austenitic Stainless Steel Pipe
- ASTM A403: Standard Specification for Austenitic Stainless Steel Piping Fittings
- ASTM A554: Standard Specification for Welded Stainless Steel Mechanical Tubing
- ASTM A999: Standard Specification for Alloy and Stainless Steel Pipe
- ASME B31.1: Power Piping
- ASME B31.3: Process Piping
- ASME B31.9: Building Service Piping
- ABS: America Bureau of Shipping
- CRN 13492.5: Canadian Registration Number

ABBREVIATIONS

- FTG – Fitting
- NPT – National Pipe Thread
- P – ProPress Connection

Smart Connect feature

Orange Dot = EPDM sealing element
White Dot = FKM sealing element

Table of Contents

Pipe	52
Elbows	53
Tees	56
Threaded Adapters, Couplings and Reducers	58
Couplings	60
Reducers	62
Caps	63
Unions and Flanges	64

	Stock Code	Dimension	Qty	Approx. wt./lb. Each	
 Pipe ProPress Stainless Pipe 304 Stainless Steel DISCOUNT 9 <u>model 0103</u>		in x ft			
	87000	1/2 x 20	5/100	7.48	
	87005	3/4 x 20	5/100	10.80	
	87010	1 x 20	5/100	14.12	
	87015	1 1/4 x 20	5/100	17.46	
	87020	1 1/2 x 20	5/100	20.74	
	87025	2 x 20	5/100	27.38	
 ProPress Stainless XL-S Pipe DISCOUNT 9 <u>model 0107XL</u>		in x ft			
	87095	2 1/2 x 20		2.179	
	87100	3 x 20	5/100	2.606	
	87105	4 x 20	5/100	3.462	
 ProPress Stainless ECO Pipe 304 Stainless Steel DISCOUNT 9 <u>model 0108</u>		in x ft			
	87050	1/2 x 20	5/100	5.30	
	87055	3/4 x 20	5/100	9.00	
	87060	1 x 20	5/100	11.72	
	87065	1 1/4 x 20	5/100	17.92	
	87070	1 1/2 x 20	5/100	21.28	
	87075	2 x 20	5/100	28.08	
 ProPress Stainless XL-S ECO Pipe 304 Stainless Steel DISCOUNT 9 <u>model 0108XL</u>		in x ft			
	87080	2 1/2	5/100	46.12	
	87085	3	5/100	52.12	
	87090	4	5/100	68.54	

	Stock Code	Dimension	Qty	Approx. wt./lb. Each	
Elbows					
 ProPress Stainless Elbow - 90° 304 Stainless Steel Smart Connect feature DISCOUNT 9 <u>model 0116</u>		P x P			
	85400	1/2	10	0.106	
	85405	3/4	10	0.239	
	85410	1	5	0.308	
	85415	1 1/4	1	0.468	
	85420	1 1/2	1	0.771	
	85425	2	1	1.047	
 ProPress Stainless Elbow - 90° 304 Stainless Steel w/FKM Seal Smart Connect feature DISCOUNT 9 <u>model 6016</u>		P x P			
	85402	1/2	10	0.112	
	85407	3/4	10	0.237	
	85412	1	5	0.314	
	85417	1 1/4	1	0.364	
	85422	1 1/2	1	0.771	
	85427	2	1	1.038	
 ProPress Stainless XL-S Elbow - 90° 304 Stainless Steel Smart Connect feature DISCOUNT 9 <u>model 0116XL</u>		P x P			
	85430	2 1/2	1	1.814	
	85435	3	1	2.468	
	85440	4	1	4.044	
 ProPress Stainless XL-S Elbow - 90° 304 Stainless Steel w/FKM Seal Smart Connect feature DISCOUNT 9 <u>model 6016XL</u>		P x P			
	85432	2 1/2	1	1.843	
	85437	3	1	2.499	
	85442	4	1	4.086	
 ProPress Stainless Elbow - 45° 304 Stainless Steel Smart Connect feature DISCOUNT 9 <u>model 0126</u>		P x P			
	85445	1/2	10	0.093	
	85450	3/4	10	0.184	
	85455	1	5	0.231	
	85460	1 1/4	1	0.351	
	85465	1 1/2	1	0.509	
	85470	2	1	0.932	

		Stock Code	Dimension	Qty	Approx. wt./lb. Each	
	ProPress Stainless Elbow - 45° 304 Stainless Steel w/FKM Seal Smart Connect feature DISCOUNT 9 <u>model 6026</u>		P x P			
		85447	1/2	10	0.091	
		85452	3/4	10	0.185	
		85457	1	5	0.233	
		85462	1 1/4	1	0.298	
		85467	1 1/2	1	0.54	
		85472	2	1	0.774	
	ProPress Stainless XL-S Elbow - 45° 304 Stainless Steel Smart Connect feature DISCOUNT 9 <u>model 0126XL</u>		P x P			
		85475	2 1/2	1	1.40	
		85480	3	1	1.876	
		85485	4	1	3.035	
	ProPress Stainless XL-S Elbow - 45° 304 Stainless Steel w/FKM Seal Smart Connect feature DISCOUNT 9 <u>model 6026XL</u>		P x P			
		85477	2 1/2	1	1.446	
		85482	3	1	1.913	
		85487	4	1	2.969	
	ProPress Stainless Elbow - 90° 304 Stainless Steel Smart Connect feature DISCOUNT 9 <u>model 0116.1</u>		FTG x P			
		85490	1/2	10	0.104	
		85495	3/4	10	0.218	
		85500	1	5	0.311	
		85505	1 1/4	1	0.469	
		85510	1 1/2	1	0.64	
		85515	2	1	1.234	
	ProPress Stainless Elbow - 90° 304 Stainless Steel w/FKM Seal Smart Connect feature DISCOUNT 9 <u>model 6016.1</u>		FTG x P			
		85492	1/2	10	0.115	
		85497	3/4	10	0.219	
		85502	1	5	0.315	
		85512	1 1/2	1	0.782	
		85517	2	1	0.985	

	Stock Code	Dimension	Qty	Approx. wt./lb. Each	
 ProPress Stainless XL-S Elbow - 90° 304 Stainless Steel Smart Connect feature DISCOUNT 9 <u>model 0116.1XL</u>		FTG x P			
	85520	2 1/2	1	1.73	
	85525	3	1	2.319	
	85530	4	1	3.859	
 ProPress Stainless XL-S Elbow - 90° 304 Stainless Steel w/FKM Seal DISCOUNT 9 <u>model 6016.1XL</u>		FTG x P			
	85522	2 1/2	1	1.688	
	85527	3	1	2.332	
	85532	4	1	3.828	
 ProPress Stainless Elbow - 45° 304 Stainless Steel Smart Connect feature DISCOUNT 9 <u>model 0126.1</u>		FTG x P			
	85535	1/2	10	0.085	
	85540	3/4	10	0.183	
	85545	1	5	0.229	
	85550	1 1/4	1	0.356	
	85555	1 1/2	1	0.465	
	85560	2	1	0.93	
 ProPress Stainless Elbow - 45° 304 Stainless Steel w/FKM Seal Smart Connect feature DISCOUNT 9 <u>model 6026.1</u>		FTG x P			
	85537	1/2	10	0.087	
	85542	3/4	10	0.187	
	85547	1	5	0.235	
	85557	1 1/2	1	0.60	
	85562	2	1	0.925	
 ProPress Stainless XL-S Elbow - 45° 304 Stainless Steel Smart Connect feature DISCOUNT 9 <u>model 0126.1XL</u>		FTG x P			
	85565	2 1/2	1	1.333	
	85570	3	1	1.746	
	85575	4	1	2.797	

	Stock Code	Dimension	Qty	Approx. wt./lb. Each	
 ProPress Stainless XL-S Elbow - 45° 304 Stainless Steel w/FKM Seal Smart Connect feature DISCOUNT 9 <u>model 6026.1XL</u>		FTG x P			
	85567	2 1/2	1	1.34	
	85572	3	1	1.785	
	85577	4	1	2.848	
Tees					
 ProPress Stainless Tee 304 Stainless Steel Smart Connect feature DISCOUNT 9 <u>model 0118</u>		P x P x P			
	85580	1/2	10	0.143	
	85585	3/4	10	0.268	
	85630	3/4 x 3/4 x 1/2	10	0.237	
	85590	1	5	0.358	
	85640	1 x 1 x 1/2	5	0.31	
	85650	1 x 1 x 3/4	5	0.341	
	85595	1 1/4	1	0.462	
	85660	1 1/4 x 1 1/4 x 1/2	1	0.355	
	85670	1 1/4 x 1 1/4 x 3/4	1	0.429	
	85680	1 1/4 x 1 1/4 x 1	1	0.453	
	85600	1 1/2	1	0.81	
	85690	1 1/2 x 1 1/2 x 1/2	1	0.666	
	85700	1 1/2 x 1 1/2 x 3/4	1	0.689	
	85710	1 1/2 x 1 1/2 x 1	1	0.706	
	85605	2	1	1.113	
	85720	2 x 2 x 1/2	1	0.952	
	85730	2 x 2 x 3/4	1	0.758	
	85740	2 x 2 x 1	1	0.796	
	85750	2 x 2 x 1 1/2	1	1.093	
 ProPress Stainless Tee 304 Stainless Steel w/FKM Seal Smart Connect feature DISCOUNT 9 <u>model 6018</u>		P x P x P			
	85582	1/2	10	0.156	
	85587	3/4	10	0.264	
	85632	3/4 x 3/4 x 1/2	10	0.242	
	85592	1	5	0.364	
	85642	1 x 1 x 1/2	5	0.316	
	85652	1 x 1 x 3/4	5	0.34	
	85597	1 1/4	1	0.452	
	85662	1 1/4 x 1 1/4 x 1/2	1	0.359	
	85672	1 1/4 x 1 1/4 x 3/4	1	0.403	
	85682	1 1/4 x 1 1/4 x 1	1	0.445	
	85598	1 1/2	1	0.765	
	85692	1 1/2 x 1 1/2 x 1/2	1	0.641	
	85702	1 1/2 x 1 1/2 x 3/4	1	0.655	
	85712	1 1/2 x 1 1/2 x 1	1	0.683	
	85607	2	1	1.181	
	85722	2 x 2 x 1/2	1	0.753	
	85732	2 x 2 x 3/4	1	0.976	
	85742	2 x 2 x 1	1	0.824	
	85752	2 x 2 x 1 1/2	1	1.095	

		Stock Code	Dimension	Qty	Approx. wt./lb. Each	
 ProPress Stainless XL-S Tee 304 Stainless Steel Smart Connect feature DISCOUNT 9 <u>model 0118XL</u>			P x P x P			
		85610	2 1/2	1	2.023	
		85763	2 1/2 x 2 x 1 1/2	1	1.516	
		85762	2 1/2 x 2 x 2	1	1.679	
		85761	2 1/2 x 2 1/2 x 1 1/2	1	1.547	
		85760	2 1/2 x 2 1/2 x 2	1	1.701	
		85615	3	1	2.658	
		85772	3 x 3 x 1 1/4	1	1.809	
		85771	3 x 3 x 1 1/2	1	1.929	
		85770	3 x 3 x 2	1	2.083	
		85780	3 x 3 x 2 1/2	1	2.446	
		85620	4	1	4.179	
		85791	4 x 4 x 1 1/2	1	2.821	
		85790	4 x 4 x 2	1	2.962	
		85800	4 x 4 x 2 1/2	1	3.332	
		85810	4 x 4 x 3	1	3.604	
 ProPress Stainless XL-S Tee 304 Stainless Steel w/FKM Seal Smart Connect feature DISCOUNT 9 <u>model 6018XL</u>			P x P x P			
		85612	2 1/2	1	2.061	
		85955	2 1/2 x 2 x 1 1/2	1	1.534	
		85954	2 1/2 x 2 x 2	1	1.706	
		85934	2 1/2 x 2 1/2 x 1 1/2	1	1.578	
		85904	2 1/2 x 2 1/2 x 2	1	1.735	
		85617	3	1	2.691	
		85944	3 x 3 x 1 1/4	1	1.827	
		85935	3 x 3 x 1 1/2	1	1.951	
		85905	3 x 3 x 2	1	2.109	
		85914	3 x 3 x 2 1/2	1	2.468	
		85622	4	1	4.201	
		85945	4 x 4 x 1 1/2	1	2.821	
		85915	4 x 4 x 2	1	3.011	
		85924	4 x 4 x 2 1/2	1	3.421	
		85925	4 x 4 x 3	1	3.681	
 ProPress Stainless Reducing Tee - Female 304 Stainless Steel Smart Connect feature DISCOUNT 9 <u>model 0117.2</u>			P x P x F NPT			
		85820	3/4 x 3/4 x 1/2	5	0.285	
		85830	3/4 x 3/4 x 3/4	5	0.326	
		85840	1 x 1 x 1/2	5	0.354	
		85850	1 x 1 x 3/4	5	0.393	
		85860	1 1/4 x 1 1/4 x 1/2	1	0.442	
		85870	1 1/4 x 1 1/4 x 3/4	1	0.497	
		85880	1 1/4 x 1 1/4 x 1	1	0.656	
		85900	1 1/2 x 1 1/2 x 3/4	1	0.742	
		85890	1 1/2 x 1 1/2 x 1/2	1	0.705	
		85910	1 1/2 x 1 1/2 x 1	1	0.913	
		85920	2 x 2 x 1/2	1	0.988	
		85930	2 x 2 x 3/4	1	1.027	
		85940	2 x 2 x 1	1	1.202	
 ProPress Stainless Reducing Tee - Female 304 Stainless Steel w/FKM Seal Smart Connect feature DISCOUNT 9 <u>model 6017.2</u>			P x P x F NPT			
		85822	3/4 x 3/4 x 1/2	5	0.281	
		85832	3/4 x 3/4 x 3/4	5	0.323	
		85842	1 x 1 x 1/2	5	0.337	
		85852	1 x 1 x 3/4	5	0.379	
		85862	1 1/4 x 1 1/4 x 1/2	1	0.399	
		85872	1 1/4 x 1 1/4 x 3/4	1	0.455	
		85882	1 1/4 x 1 1/4 x 1	1	0.628	
		85892	1 1/2 x 1 1/2 x 1/2	1	0.666	
		85902	1 1/2 x 1 1/2 x 3/4	1	0.754	
		85912	1 1/2 x 1 1/2 x 1	1	0.884	
		85922	2 x 2 x 1/2	1	0.785	
		85932	2 x 2 x 3/4	1	0.822	
		85942	2 x 2 x 1	1	1.025	

		Stock Code	Dimension	Qty	Approx. wt./lb. Each	
	ProPress Stainless XL-S Reducing Tee - Female 304 Stainless Steel Smart Connect feature DISCOUNT 9 <u>model 0117.2XL</u>		P x P x F NPT			
		85950	2 1/2 x 2 1/2 x 3/4	1	1.384	
		85960	2 1/2 x 2 1/2 x 1	1	1.554	
		85970	3 x 3 x 3/4	1	1.741	
		85980	3 x 3 x 1	1	1.909	
		85990	4 x 4 x 3/4	1	2.535	
		86000	4 x 4 x 1	1	2.718	
	ProPress Stainless XL-S Reducing Tee - Female 304 Stainless Steel w/FKM Seal Smart Connect feature DISCOUNT 9 <u>model 6017.2XL</u>		P x P x F NPT			
		85952	2 1/2 x 2 1/2 x 3/4	1	1.393	
		85962	2 1/2 x 2 1/2 x 1	1	1.585	
		85972	3 x 3 x 3/4	1	1.75	
		85982	3 x 3 x 1	1	1.931	
		85992	4 x 4 x 3/4	1	2.557	
		86002	4 x 4 x 1	1	2.724	
Threaded Adapters, Couplings and Reducers						
	ProPress Stainless Adapter - Male 304 Stainless Steel Smart Connect feature DISCOUNT 9 <u>model 0111</u>		P x M NPT			
		85010	1/2 x 1/2	10	0.128	
		85015	1/2 x 3/4	10	0.169	
		85020	3/4 x 1/2	10	0.15	
		85025	3/4 x 3/4	10	0.195	
		85030	3/4 x 1	5	0.437	
		85035	1 x 3/4	5	0.201	
		85040	1 x 1	5	0.312	
		85045	1 1/4 x 1 1/4	1	0.584	
		85050	1 1/2 x 1 1/2	1	0.711	
		85055	2 x 2	1	1.048	
	ProPress Stainless Adapter - Male 304 Stainless Steel w/FKM Seal Smart Connect feature DISCOUNT 9 <u>model 6011</u>		P x M NPT			
		85012	1/2	10	0.133	
		85017	1/2 x 3/4	10	0.171	
		85022	3/4 x 1/2	10	0.152	
		85027	3/4	10	0.197	
		85032	3/4 x 1	5	0.434	
		85042	1	5	0.315	
		85037	1 x 3/4	5	0.203	
		85047	1 1/4	1	0.584	
		85052	1 1/2	1	0.685	
		85054	2	1	1.047	
	ProPress Stainless XL-S Adapter - Male 304 Stainless Steel Smart Connect feature DISCOUNT 9 <u>model 0111XL</u>		P x M NPT			
		85060	2 1/2	1	2.021	
		85065	3	1	2.821	
		85070	4	1	3.945	

	Stock Code	Dimension	Qty	Approx. wt./lb. Each	
 ProPress Stainless XL-S Adapter - Male 304 Stainless Steel w/FKM Seal Smart Connect feature DISCOUNT 9 <u>model 6011XL</u>		P x M NPT			
	85062	2 1/2	1	2.034	
	85067	3	1	2.843	
	85072	4	1	3.967	
 ProPress Stainless Adapter - Female 304 Stainless Steel Smart Connect feature DISCOUNT 9 <u>model 0112</u>		P x F NPT			
	85080	1/2 x 1/2	10	0.117	
	85085	3/4 x 1/2	10	0.158	
	85090	3/4 x 3/4	10	0.198	
	85092	1 x 1/2	5	0.258	
	85095	1 x 3/4	5	0.207	
	85100	1 x 1	5	0.393	
	85105	1 1/4 x 1 1/4	1	0.404	
	85110	1 1/2 x 1 1/4	1	0.497	
	85115	1 1/2 x 1 1/2	1	0.677	
	85075	2 x 1	1	1.19	
	85120	2 x 1 1/2	1	0.737	
	85125	2 x 2	1	0.807	
 ProPress Stainless Adapter - Female 304 Stainless Steel w/FKM Seal Smart Connect feature DISCOUNT 9 <u>model 6012</u>		P x F NPT			
	85082	1/2 x 1/2	10	0.121	
	85087	3/4 x 1/2	10	0.156	
	85096	3/4	10	0.198	
	85128	1	5	0.386	
	85094	1 x 1/2	5	0.261	
	85097	1 x 3/4	5	0.208	
	85107	1 1/4	1	0.417	
	85117	1 1/2	1	0.641	
	85127	2	1	0.807	
	85077	2 x 1	1	1.047	
	85122	2 x 1 1/2	1	0.719	
 ProPress Stainless Adapter 304 Stainless Steel Transition - Weld Smart Connect feature DISCOUNT 9 <u>model 0113.3</u>		P x BW (IPS)			
	86003	1/2 x 1/2	10	0.115	
	86008	3/4 x 3/4	1		
	86013	1 x 1	5		
	86023	1 1/2 x 1 1/2	1		
	86028	2 x 2	1		
 ProPress Stainless XL-S Adapter 304 Stainless Steel DISCOUNT 9 <u>model 0113.1XL</u>		P x BW (IPS)			
	85135	2 1/2 x 2 1/2	1	1.031	
	85145	3 x 3	1	1.30	
	85155	4 x 4	1	1.887	

		Stock Code	Dimension	Qty	Approx. wt./lb. Each	
	ProPress Stainless XL-S Adapter 304 Stainless Steel Transition - Groove DISCOUNT 9 <u>model 0113.2XL</u>	85166	P x G (IPS) 2 1/2 x 2 1/2	1	1.49	
		85177	3 x 3	1	1.856	
		85188	4 x 4	1	2.552	
Couplings						
	ProPress Stainless Coupling - w/Stop 304 Stainless Steel Smart Connect feature DISCOUNT 9 <u>model 0115</u>	85265	P x P 1/2	10	0.076	
		85270	3/4	10	0.13	
		85275	1	5	0.162	
		85280	1 1/4	1	0.246	
		85285	1 1/2	1	0.403	
		85290	2	1	0.564	
	ProPress Stainless Coupling - w/Stop 304 Stainless Steel w/FKM Seal Smart Connect feature DISCOUNT 9 <u>model 6015</u>	85267	P x P 1/2	10	0.076	
		85272	3/4	10	0.132	
		85277	1	5	0.164	
		85282	1 1/4	1	0.241	
		85287	1 1/2	1	0.42	
		85292	2	1	0.613	
	ProPress Stainless XL-S Coupling - w/Stop 304 Stainless Steel Smart Connect feature DISCOUNT 9 <u>model 0115XL</u>	85295	P x P 2 1/2	1	1.058	
		85300	3	1	1.378	
		85305	4	1	2.089	
	ProPress Stainless XL-S Coupling - w/Stop 304 Stainless Steel w/FKM Seal Smart Connect feature DISCOUNT 9 <u>model 6015XL</u>	85297	P x P 2 1/2	1	1.095	
		85302	3	1	1.396	
		85307	4	1	2.136	

	Stock Code	Dimension	Qty	Approx. wt./lb. Each	
 ProPress Stainless Coupling - No Stop 304 Stainless Steel Smart Connect feature DISCOUNT 9 <u>model 0115.5</u>		P x P			
	85310	1/2	10	0.076	
	85315	3/4	10	0.129	
	85320	1	5	0.165	
	85325	1 1/4	1	0.24	
	85330	1 1/2	1	0.41	
	85335	2	1	0.571	
 ProPress Stainless Coupling - No Stop 304 Stainless Steel w/FKM Seal Smart Connect feature DISCOUNT 9 <u>model 6015.5</u>		P x P			
	85312	1/2	10	0.076	
	85317	3/4	10	0.13	
	85322	1	5	0.166	
	85327	1 1/4	1	0.242	
	85332	1 1/2	1	0.39	
	85337	2	1	0.606	
 ProPress Stainless XL-S Coupling - No Stop 304 Stainless Steel Smart Connect feature DISCOUNT 9 <u>model 0115.5XL</u>		P x P			
	85340	2 1/2	1	1.058	
	85345	3	1	1.366	
	85350	4	1	2.10	
 ProPress Stainless XL-S Coupling - No Stop 304 Stainless Steel w/FKM Seal Smart Connect feature DISCOUNT 9 <u>model 6015.5XL</u>		P x P			
	85342	2 1/2	1	1.087	
	85347	3	1	1.411	
	85352	4	1	2.16	

		Stock Code	Dimension	Qty	Approx. wt./lb. Each	
Reducers						
	ProPress Stainless Reducer 304 Stainless Steel Smart Connect feature DISCOUNT 9 <u>model 0115.1</u>	FTG x P				
		85160	3/4 x 1/2	10	0.088	
		85165	1 x 1/2	10	0.12	
		85170	1 x 3/4	10	0.138	
		85175	1 1/4 x 1/2	1	0.186	
		85180	1 1/4 x 3/4	1	0.194	
		85185	1 1/4 x 1	1	0.21	
		85190	1 1/2 x 1/2	1	0.276	
		85195	1 1/2 x 3/4	1	0.293	
		85200	1 1/2 x 1	1	0.269	
		85205	1 1/2 x 1 1/4	1	0.297	
		85210	2 x 1/2	1	0.397	
		85215	2 x 3/4	1	0.591	
		85220	2 x 1	1	0.435	
		85225	2 x 1 1/4	1	0.39	
		85230	2 x 1 1/2	1	0.503	
	ProPress Stainless Reducer 304 Stainless Steel w/FKM Seal Smart Connect feature DISCOUNT 9 <u>model 6015.1</u>	FTG x P				
		85162	3/4 x 1/2	10	0.094	
		85167	1 x 1/2	10	0.121	
		85172	1 x 3/4	10	0.139	
		85173	1 1/4 x 1/2	1	0.165	
		85182	1 1/4 x 3/4	1	0.192	
		85187	1 1/4 x 1	1	0.216	
		85192	1 1/2 x 1/2	1	0.278	
		85197	1 1/2 x 3/4	1	0.295	
		85202	1 1/2 x 1	1	0.273	
		85212	2 x 1/2	1	0.361	
		85217	2 x 3/4	1	0.41	
		85222	2 x 1	1	0.419	
		85232	2 x 1 1/2	1	0.476	
	ProPress Stainless XL-S Reducer 304 Stainless Steel Smart Connect feature DISCOUNT 9 <u>model 0115.1XL</u>	FTG x P				
		85235	2 1/2 x 2	1	0.76	
		85240	3 x 2	1	0.968	
		85245	3 x 2 1/2	1	1.135	
		85250	4 x 2	1	1.439	
		85255	4 x 2 1/2	1	1.598	
		85260	4 x 3	1	1.686	
	ProPress Stainless XL-S Reducer 304 Stainless Steel w/FKM Seal Smart Connect feature DISCOUNT 9 <u>model 6015.1XL</u>	FTG x P				
		85237	2 1/2 x 2	1	0.765	
		85242	3 x 2	1	0.97	
		85247	3 x 2 1/2	1	1.153	
		85252	4 x 2	1	1.448	
		85257	4 x 2 1/2	1	1.607	
		85262	4 x 3	1	1.673	

	Stock Code	Dimension	Qty	Approx. wt./lb. Each	
Caps					
 ProPress Stainless Cap 304 Stainless Steel Smart Connect feature DISCOUNT 9 <u>model 0156</u>		P			
	85355	1/2	10	0.04	
	85360	3/4	10	0.078	
	85365	1	5	0.107	
	85370	1 1/4	1	0.156	
	85375	1 1/2	1	0.252	
	85380	2	1	0.354	
 ProPress Stainless Cap 304 Stainless Steel w/FKM Seal Smart Connect feature DISCOUNT 9 <u>model 6056</u>		P			
	85357	1/2	10	0.038	
	85362	3/4	10	0.079	
	86367	1	5	0.105	
	86372	1 1/4	1	0.161	
	86377	1 1/2	1	0.258	
	86382	2	1	0.356	
 ProPress Stainless XL-S Cap 304 Stainless Steel Smart Connect feature DISCOUNT 9 <u>model 0156.1XL</u>		P			
	85385	2 1/2	1	0.767	
	85390	3	1	0.996	
	85395	4	1	1.616	
 ProPress Stainless XL-S Cap 304 Stainless Steel w/FKM Seal Smart Connect feature DISCOUNT 9 <u>model 6056.1XL</u>		P			
	85387	2 1/2	1	0.787	
	85392	3	1	1.007	
	85397	4	1	1.627	

		Stock Code	Dimension	Qty	Approx. wt./lb. Each	
Unions and Flanges						
	ProPress Stainless Union 304 Stainless Steel Ground Joint Smart Connect feature DISCOUNT 9 <u>model 0160</u>	P x P				
		86005	1/2	5	0.309	
		86010	3/4	5	0.992	
		86015	1	5	0.804	
		86020	1 1/4	1	1.042	
		86025	1 1/2	1	1.955	
		86030	2	1	3.028	
	ProPress Stainless Union 304 Stainless Steel Ground Joint w/FKM Seal Smart Connect feature DISCOUNT 9 <u>model 6060</u>	P x P				
		86007	1/2	5	0.312	
		86012	3/4	5	0.475	
		86017	1	5	0.791	
		86022	1 1/4	1	1.047	
		86027	1 1/2	1	1.957	
		86032	2	1	3.045	
	ProPress Stainless Flange 304 Stainless Steel Smart Connect feature DISCOUNT 9 <u>model 0159</u>	Flange x P				
		86035	1/2	1	1.062	
		86040	3/4	1	1.552	
		86045	1	1	2.043	
		86050	1 1/4	1	2.508	
		86055	1 1/2	1	3.324	
		86060	2	1	5.138	
	ProPress Stainless XL-S Flange 304 Stainless Steel Smart Connect feature DISCOUNT 9 <u>model 0159XL</u>	Flange x P				
		86065	2 1/2	1	8.552	
		86070	3	1	9.978	
		86075	4	1	10.491	
	ProPress Stainless XL-S Adapter Flange 304 Stainless Steel w/FKM Seal Smart Connect feature DISCOUNT 9 <u>model 6059XL</u>	Flange x P				
		86067	2 1/2	1	8.541	
		86072	3	1	10.002	
		86077	4	1	14.238	

	Stock Code	Dimension	Qty	Approx. wt./lb. Each	
 Bolt Set Galvanized Steel For Two Piece Adapter Flange DISCOUNT 8 <u>model 2959.7</u> NOTE: 1" (28mm) to 3" (88.9mm) bolts - set of 4 4" bolts - set of 8	19748	1, 1 1/4, 1 1/2	1	0.871	
	19758	2, 2 1/2, 3	1	1.572	
	19763	4	1	3.141	
		Flange Dimension			
 Sealing Element EPDM (shiny black) For ProPress, ProPress 304 Stainless Steel, ProPress 316 Stainless Steel fittings DISCOUNT 8 <u>model 2989</u>	78242	1/2	10	0.001	
	78247	3/4	10	0.002	
	78252	1	10	0.002	
	78257	1 1/4	10	0.003	
	78262	1 1/2	10	0.007	
	78267	2	10	0.006	
 Sealing Element FKM (dull black) For ProPress, ProPress 304 Stainless Steel, ProPress 316 Stainless Steel fittings DISCOUNT 8 <u>model 2986</u>	17768	1/2	5	0.003	
	17778	3/4	5	0.004	
	17788	1	5	0.005	
	17803	1 1/4	5	0.006	
	17818	1 1/2	5	0.01	
	17823	2	5	0.012	
 Replacement Gasket EPDM Flat Gasket Replacement gasket for Di-electric Union DISCOUNT 8 <u>model 2963.9</u>	15559	1/2	10	0.004	
	15569	3/4 & 1	10	0.003	
	15549	1 1/4	10	0.005	
	15544	1 1/2	10	0.005	
	15564	2	10	0.009	
 Flange Gasket AFM 34 Asbestos-free DISCOUNT 8 <u>model 2959.9</u>	81130	1/2	10	0.016	
	81131	3/4	10	0.022	
	93417	1	10	0.029	
	93422	1 1/4	10	0.037	
	93427	1 1/2	10	0.047	
	93432	2	10	0.07	
	93437	2 1/2	10	0.094	
	93442	3	10	0.106	
	93447	4	10	0.17	

