| For Residential and Commercial Applications | | | |
|---|--|----------------------|--|
| Job Name | | Engineer / Architect | |
| Job Location | | Wholesaler | |
| Submittal Date | | Contractor | |

B1-**DL/ B2-**DL/ B3-**DL Speedi Plumb® PLUS Braided Toilet Connectors - Compression Inlet

Use: For use in potable water distribution systems in accessible locations only.

Design Features:

- Superior corrosion resistance to harsh chemicals found in common household cleaning and plumbing repair products
- More flexible than stainless steel, the braided polymer-coated fibers bend freely without kinking or crimping
- Tough inner core is reinforced to resist chlorine and chloramine leaching and deterioration
- Nitrile rubber washers provide a large pliable sealing surface and ensures a long lasting water tight connection
- 8-sided pneumatic crimp provides greater dependability for realible nut-to-hose connections

Operating Specifications:

Temperature: 40°-140° F, intermittent to 180° F

Pressure: 125 psi maximum

Tubing Diameter: 0.300" I.D. (0.550" O.D.)

| MATERIAL SPECIFICATIONS | | |
|-------------------------|---------------------------|--|
| Inner Hose | Reinforced PVC | |
| Braiding | PVC coated polyester yarn | |
| Barb | Compliant brass | |
| Ferrule | C37000 brass | |
| Nut | C36000 brass | |
| Washer | Nitrile rubber | |
| Compression Ring & Nut | C36000 brass | |

Part Listing:

| B1-6DL F | 3/8" Compression x 7/8" Ballcock x 6" Length |
|------------|---|
| B1-9DL F | 3/8" Compression x 7/8" Ballcock x 9" Length |
| B1-12DL F | 3/8" Compression x 7/8" Ballcock x 12" length |
| B1-12DLM F | 3/8" Compression x 7/8" Ballcock (metal nut) x 12" length |

B1-12DLU D Universal Connector - 3/8" Compression x 7/8" Ballcock x 12" length


with 7/16" & 1/2" slip-joint & 1/2" F.I.P. adapters


This specification and all information contained herein is the confidential and exclusive property of BrassCraft Manufacturing, and shall not be disclosed to others without the written consent of BrassCraft. This specification must be returned to BrassCraft if requested.

B1-**DL/ B2-**DL/ B3-**DL Speedi Plumb® PLUS Braided Toilet Connectors - Compression Inlet

Part Listing (con't):

| B1-16DL F | 3/8" Compression x 7/8" Ballcock x 16" length |
|------------|---|
| B1-20DL F | 3/8" Compression x 7/8" Ballcock x 20" length |
| B1-20DLM F | 3/8" Compression x 7/8" Ballcock x 30" length |
| B1-26DL F | 3/8" Compression x 7/8" Ballcock x 36" length |
| B2-12DL F | 7/16" Compression x 7/8" Ballcock x 12" length |
| B2-20DL F | 7/16" Compression x 7/8" Ballcock x 20" length |
| B3-9DL F | 1/2" Compression x 7/8" Ballcock x 9" length |
| B3-12DL F | 1/2" Compression x 7/8" Ballcock x 12" length |
| B3-12DLM F | 1/2" Compression x 7/8" Ballcock (metal nut) x 12" length |
| B3-20DL F | 1/2" Compression x 7/8" Ballcock x 20" length |





| PART DIMENSIONS (Inches) | | |
|--------------------------|-------------|--|
| Model | Dim. A | |
| B1-6DL | 6.0 / 7.0 | |
| B1-9DL | 9.0 / 10.0 | |
| B1-12DL | 12.0 / 13.0 | |
| B1-12DLM | 12.0 / 13.0 | |
| B1-12DLU | 12.0 / 13.0 | |

| PART DIMENSIONS (Inches) | | |
|---------------------------------|-------------|--|
| Model | Dim. A | |
| B1-16DL | 16.0 / 17.0 | |
| B1-20DL | 20.0 / 21.0 | |
| B1-20DLM | 20.0 / 21.0 | |
| B2-12DL | 12.0 / 13.0 | |
| B2-20DL | 20.0 / 21.0 | |

| PART DIMIENSIONS (Inches) | |
|---------------------------|-------------|
| Model | Dim. A |
| B3-9DL | 9.0 / 10.0 |
| B3-12DL | 12.0 / 13.0 |
| B3-12DLM | 12.0 / 13.0 |
| B3-20A | 20.0 / 21.0 |
| | |

This specification and all information contained herein is the confidential and exclusive property of BrassCraft Manufacturing, and shall not be disclosed to others without the written consent of BrassCraft. This specification must be returned to BrassCraft if requested.



B1-**DL/ B2-**DL/ B3-**DL Speedi Plumb® PLUS Braided Toilet Connectors - Compression Inlet

Listings & Certifications:

- IAPMO listed to ASME A112.18.6-2003 (File # 0452)
- CSA listed to ASME A112.18.6-2003 / CSA B125 (File # 204593)





