Saves Energy!

Programmable Line Voltage

PSPLV512

Heat Only Thermostat



For Use On:

- 1 Stage Heat Only: Single or Double Pole 120/240 VAC Systems up to 16 Amps
- Line Voltage (120/240 Volt)
 Hydronic (Hot Water) Systems
 With Motors Up To 1/4 HP

Not For Use On:

Conventional 24V Heating and and Cooling Systems

Electrical Rating:

1900W at 120Vac (Non-Inductive) 3800W at 240Vac (Non-Inductive)

Temperature Differential

+\- 1 °F Factory Preset; Adjustable

Batteries:

• Requires 2 AA Batteries - Included

UL Approved

Features:

- Preprogrammed 4 Periods per day
- 5/2 Programming
- Positive Off Switch
- °F / °C Selectable Display
- Temporary Temperature Override
- Vacation Hold

Dimensions:

- 4.7" T x 2.7" W x 2.4" D
- 1.4" D from wall surface

Wall Plate:

• 4.8" W x 5.0" H (Wallplate Not Included)

Carton Pack:

• 5 Pieces

UPC CODE:

• 0 21079 06512 7

