

## RP971A Ratio Relay

### SPECIFICATION DATA



### FEATURES

- Adjustable pilot start point pressures
- Two pilot pressure spans available
- Four sharp barb air connections
- Molded plastic construction with neoprene diaphragms and stainless steel valve seats
- 100 mesh stainless steel screens in main and branch ports
- Designed for in-line mounting but can be wall or panel mounted

### GENERAL

The RP971A Ratio Relay is a four port nonbleed pneumatic relay which produces a modulating pressure output proportional to pilot input changes. It is used to control pneumatic valve or damper actuators in sequence from a single thermostat.



## DESCRIPTION

The RP971A Ratio Relay is a four port nonbleed pneumatic relay which produces a modulating pressure output proportional to pilot input changes. It is used to control pneumatic valve or damper actuators in sequence from a single thermostat.

## SPECIFICATIONS

**Model:**

RP971A Ratio Relay

**Operating Range:**

0 to 18 psi (0 to 124 kPa)

**Maximum Safe Air Pressure:**

30 psi (205 kPa)

**Ambient Operating Limits:**

Temperature: 0 to 140F (-18 to 60C)

Humidity: 5 to 95%

**Operating Air Pressures:**

Pilot: 3 to 15 psi (21 to 103 kPa)

Main: 18 psi (124 kPa)

**Air Handling Capacity:**

0.039 scfm at 1 psi differential (18 ml/s at 5 kPa differential)

**Air Consumption:**

0.002 scfm (0.8 ml/s) maximum

**Start Point:**

Adjustable from 0 to 10 psi (0 to 69 kPa)

**Pilot Operating Span:**

3 or 5 psi (20 or 35 kPa), nonadjustable

**Mounting:**

In line, wall, or panel mounted

**Air Connections:**

Barb type for 1/4-in. (6-mm) O.D. plastic tubing for Port 1 and 5/32-in. (4-mm) O.D. plastic tubing for Ports 2, 3, and 4

**Construction:**

Molded plastic with neoprene diaphragm, stainless steel valve seats, and 100-mesh stainless steel filters in main and branch ports

**Accessories:**

801629T Cable Clamp (2 in. [51 mm] dia) for wall mounting if desired

**Dimensions:**

2 in. (51 mm) dia x 2-5/8 (67 mm) deep

**Home and Building Control**

Honeywell Inc.  
Honeywell Plaza  
P.O. Box 524  
Minneapolis MN 55408-0524

**Honeywell Latin American Division**

Miami Lakes Headquarters  
14505 Commerce Way Suite 500  
Miami Lakes FL 33016

**Home and Building Control**

Honeywell Limited-Honeywell Limitée  
155 Gordon Baker Road  
North York, Ontario  
M2H 2C9

**Honeywell Europe S.A.**

3 Avenue du Bourget  
B-1140 Brussels Belgium

**Honeywell Asia Pacific Inc.**

Room 3213-3225  
Sun Hung Kai Centre  
No. 30 Harbour Road  
Wanchai  
Hong Kong

---

**Honeywell**

