

1515

FLEXIBLE DUCT CLOSURE TAPE

VentureTape® 1515 is high strength, premium quality polyethylene (PE) coated cloth duct tape coated with an aggressive rubber pressure sensitive adhesive. Venture Tape 1515 provides easy application and superior performance and durability over a wide range of demanding temperatures and environments.

Product Construction



Features & Benefits

- UL File # MH16587, meets requirements of UL 181B-FX
- High performance flexible duct closure tape performs well over a wide temperature range
- Self wound product is hand tearable and applies easily
- Conforms well to corners and irregular surfaces
- Excels in high heat and humidity conditions
- In stock product available for immediate delivery

Test	Typical Value	Typical Value (Metric)	Test Method
Product Thickness	14.0 mils	0.36 mm	PSTC-133
Peel Adhesion ^Δ	75 oz/in	20.8 N/25 mm	PSTC-101
Shear Adhesion	>24 hrs @ 2.2 psi	>24 hrs @ 15.2 kPa	PSTC-107
Tensile Strength	38 lb/in	171.2 N/25 mm	PSTC-131
Elongation	21 %	21 %	PSTC-131
Service Temperature	0 to 180 °F	32 to 82 °C	

^Δ - 20 minute dwell

Typical values are not intended to be used for specification development. Technical data is believed to be true and accurate; Venture Tape recommends that the purchaser test for fitness of use in all applications.

Product Configurations

- Available in black and silver
- Standard roll width: 2 inch
- Standard length: 60 yards

Contact Venture Tape today for a complete list of products or a free sample

Toll Free North America 800-343-1076

From United Kingdom 0-800-962-957

From Australia 1-800-122-797

www.venturetape.com

VentureTape®

GTA - NHT, Inc.
Venture Tape
30 Commerce Rd., Rockland, MA 02370
Tel 781-331-5900; Fax 781-871-0065
800-343-1076 (U.S.A.), 800-544-1024 (Canada)
Toll Free Fax 877-264-5490
www.venturetape.com

GTA

TAPES & ADHESIVES
a 3M Company