



HDT2600

INSTALLATION PACKAGE

Includes universal humidistat, self-piercing saddle valve, bypass tubing, 24 volt transformer, summer shut-off damper, mounting template, mounting hardware and homeowner's manual/installation instructions.

HDT2600 DRUM TYPE BYPASS HUMIDIFIER

A Good Choice for Lower Efficiency Warm Air Heating Systems

FEATURES

- Unique snap-lock fittings and reversible components allow quick installation and maintenance.
- Uses minimal water and electricity.
- Durable thermoplastic cabinet resists rust, corrosion and warpage.
- Interior components designed for easy cleaning or replacement.
- Output capacity of 17.0 gallons per day (GPD) at 120°F.

SPECIFICATIONS

Overall Dimensions, HDT2600 10⁵/₁₆" H x 11¹¹/₁₆" D x 12³/₈" W
 Plenum Opening 6⁵/₈" H x 8¹/₂" W
 Bypass Opening 6" diameter
 Drum Motor 24 VAC, 3 watt, 1 RPM, bidirectional

PARTS AND ACCESSORIES See page 233 for parts and accessories



HFT2100/2700

INSTALLATION PACKAGE

Includes universal humidistat, self-piercing saddle valve, 24 volt transformer, mounting template, mounting hardware and homeowner's manual/installation instructions.

**HFT2100/2700 HIGH-CAPACITY BYPASS
FLOW-THRU HUMIDIFIER WITH SIDE ENTRY**

An Excellent Choice for Warm Air Heating Systems

FEATURES

- Designed to fit today's narrower plenums – as narrow as 10" (HFT2100) or 14" (HFT2700).
- Reversible side panels with unique snap-lock fittings permit easy-change left-side or right-side bypass installation.
- New, improved wicking and water distribution system allows for non-level plenums.
- Durable thermoplastic cabinet resists rust, corrosion and warpage.
- Low profile makes unit ideal where space is limited.

SPECIFICATIONS

Overall Dimensions, HFT2100 13¹/₂" H x 9⁵/₈" D x 12¹/₂" W
 Overall Dimensions, HFT2700 18⁵/₈" H x 9⁵/₈" D x 13³/₄" W
 Plenum Opening, HFT2100 10" H x 9" W
 Plenum Opening, HFT2700 16⁵/₈" H x 10⁵/₈" W
 Bypass Opening 6" diameter

PARTS AND ACCESSORIES See pages 234-235 for parts and accessories



HFT2900FP

INSTALLATION PACKAGE

Includes universal humidistat, self-piercing saddle valve, 24 volt transformer, mounting template, mounting hardware and homeowner's manual/installation instructions.

**HFT2900FP HIGH-CAPACITY
FAN-POWERED FLOW-THRU HUMIDIFIER**

A Premium Choice for Warm Air Heating Systems

FEATURES

- Designed to fit today's narrower plenums – as narrow as 14".
- Ideal for installations where the return air plenum is not easily accessible.
- New, improved wicking and water distribution system allows for non-level plenums.
- Durable thermoplastic cabinet resists rust, corrosion and warpage.
- Low profile makes unit ideal where space is limited.

SPECIFICATIONS

Overall Dimensions, HFT2900FP 18⁵/₈" H x 9⁵/₈" D x 13³/₄" W
 Plenum Opening 16⁵/₈" H x 13¹/₈" W

PARTS AND ACCESSORIES See page 236 for parts and accessories

Type	Model Number	Rated Output Gallons per Day	Evaporation Rate Gallons per Hour	Typical Application		
				Sq. Ft. Avg. House	Sq. Ft. Tight House	Sq. Ft. Loose House
Drum Bypass	HDT2600	17.0	0.71	2,575	4,045	1,845
Bypass Flow-Thru	HFT2100	14.0	0.58	2,121	3,333	1,627
Bypass Flow-Thru	HFT2700	18.0	0.75	2,725	4,285	1,955
Fan Powered Flow-Thru	HFT2900FP	19.0	0.79	2,880	4,525	2,065

Table calculations based on ARI 630