

Your Peace of Mind is Our Top Priority®



COMPANY

Zoeller Family of Water Solutions™

(502) 778-2731 • 1 (800) 928-PUMP

www.ZControlCloud.com

www.Zoeller.com

FM2945
0616
Supersedes
New



APak®

New and Improved Design!

- *Longer battery life*
- *Friendlier design*
- *More compact and easy to install*
- *CSA approved*



10-4011 APak® Standard
10-4013 APak® Z Control®



10-4012 APak® Standard
10-4014 APak® Z Control®

Features: Standard Models

- NEMA 1 enclosure
- High water LED and alarm
- Low battery LED and alarm
- Silence/Reset button
- 87 decibel Alarm
- AC only mode, DC only mode, AC/DC mode
- Input screw terminals allow for versatility
- Long battery life (2 AA not included). Up to 2 years in AC/DC mode, up to 1 year in DC only mode.
- Power supply with 6' cord included
- 10-4011 comes with reed sensor
- 10-4012 comes with mechanical float switch

Z Control® Enabled

Features:

Z Control® Models

- All the Standard features plus:
- 2nd Input for additional monitoring ability
- Dry contacts for connection to home security system, etc.
- Z Control Enabled!
 - Wifi equipped
 - Receive free text, email, and push alerts on:
 - Power outage
 - Low battery
 - Input 1 or 2 triggers
 - Loss of contact with Z Control®
 - Remotely Silence, Reset alarm.
 - Free Z Control App and Web interfaces
 - Free Z Control account
 - No monthly cost
 - Simple setup
 - Z Control connectivity LED
- 10-4013 comes with reed sensor
- 10-4014 comes with mechanical float switch



Notes:

Either the Standard or Wifi APak can be used to monitor nearly any switch or pair of dry contacts.

For sewage applications, the models with mechanical float switch are recommended (10-4012 and 10-4014). If a direct wired alarm is required use 10-2614, which is unchanged from our previous generation of alarms.



COMPANY

Zoeller Family of Water Solutions™

(502) 778-2731 • 1 (800) 928-PUMP
www.ZControlCloud.com
www.Zoeller.com

Your Peace of Mind is Our Top Priority®