


FD-2322 Low Profile Adjustable Floor Drain TAG



FD-2322 Low Profile Adjustable Floor Drain


Recommended for finished floor areas where membarne is not required. The drain is designed for foot traffic and light cart applications. Complete with cast iron body and adjustable nickel bronze strainer. 1/2"[13mm] (-P) trap primer connection provided with plug.

<u>Options:</u>	
CP	Chrome Plated
PB	Polished Brass
R6	6" Dia. Nickel Head Assy
R7	7" Dia. Nickel Head Assy
R8	8" Dia. Nickel Head Assy
-VP	Vandal Proof

\..4! - .. - .

Product	Connection 'A'	D
 FD-2322-NH2	2"[51mm] No-Hub	2-1/2"[64mm]
 FD-2322-NH3	3"[76mm] No Hub	2-1/2"[64mm]
FD-2322-NH4	4"[102mm] No-Hub	2-1/2"[64mm]
 FD-2322-PO2	2"[51mm] Push-On	3-1/3"[85mm]
 FD-2322-PO3	3"[76mm] Push-On	4-1/3"[110mm]
 FD-2322-IP2	2"[51mm] IPS	2-1/2"[64mm]
 FD-2322-IP3	3"[76mm] IPS	2"[51mm]

Typical installation



ZURN LIGHT COMMERCIAL PLUMBING PRODUCTS 2855 GIRTS ROAD , JAMESTOWN, NY 14701 PHONE: 716-665-1131 FAX: 716-665-3126 World Wide Web: <u>WWW.ZURN.COM</u>

Rev. Date: 6/19/03 Dwg. No. 80041 C.N. No. 90601 Product No. FD-2322