

## For Commercial & Residential Applications

Job Name \_\_\_\_\_

Contractor \_\_\_\_\_

Job Location \_\_\_\_\_

Approval \_\_\_\_\_

Engineer \_\_\_\_\_


Contractor's P.O. No. \_\_\_\_\_

Approval \_\_\_\_\_

Representative \_\_\_\_\_

# Metal S-Traps

- Furnished with diecast nuts and shallow flanges



MODEL	✓ TO SUBMIT	DESCRIPTION	DIMENSIONS								FINISH
			A		B		C		D		
			in.	mm.	in.	mm.	in.	mm.			
<b>Less cleanout</b>											
508 222		1 1/4" x 1 1/4" x 20 1/2"	6 1/2	165	20 1/2	521	4 1/2	114	22 GA.	Satin	
508 223		1 1/4" x 1 1/4" x 20 1/2"	6 1/2	165	20 1/2	521	4 1/2	114	22 GA.	Chrome	
512 221		1 1/2" x 1 1/2" x 20 1/2"	6 1/2	165	20 1/2	521	4 1/2	114	22 GA.	Rough Brass	
512 222		1 1/2" x 1 1/2" x 20 1/2"	6 1/2	165	20 1/2	521	4 1/2	114	22 GA.	Satin	
512 223		1 1/2" x 1 1/2" x 20 1/2"	6 1/2	165	20 1/2	521	4 1/2	114	22 GA.	Chrome	
508 203		1 1/4" x 1 1/4" x 20 1/2"	6 1/2	165	20 1/2	521	4 1/2	114	20 GA.	Chrome	
512 202		1 1/2" x 1 1/2" x 20 1/2"	6 1/2	165	20 1/2	521	4 1/2	114	20 GA.	Satin	
512 203		1 1/2" x 1 1/2" x 20 1/2"	6 1/2	165	20 1/2	521	4 1/2	114	20 GA.	Chrome	
508 173		1 1/4" x 1 1/4" x 20 1/2"	6 1/2	165	20 1/2	521	4 1/2	114	17 GA.	Chrome	
512 173		1 1/2" x 1 1/2" x 20 1/2"	6 1/2	165	20 1/2	521	4 1/2	114	17 GA.	Chrome	
<b>With cleanout</b>											
509 173		1 1/4" x 1 1/4" x 20 1/2"	6 1/2	165	20 1/2	521	4 1/2	114	17 GA.	Chrome	
513 173		1 1/2" x 1 1/2" x 20 1/2"	6 1/2	165	20 1/2	521	4 1/2	114	17 GA.	Chrome	



815 Chestnut Street • N. Andover, MA 01845  
 Tel: 978.688.1811 Fax: 978.794.1848  
 www.wattsbrass-tubular.com

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.