

For Commercial & Residential Applications

Job Name _____

Contractor _____

Job Location _____

Approval _____


Engineer _____

Contractor's P.O. No. _____

Approval _____

Representative _____

Metal Threaded Tubes



MODEL	✓ TO SUBMIT	DESCRIPTION	DIMENSIONS		FINISH
			A		
			<i>in.</i>	<i>mm.</i>	
718 203		1 1/4" x 4", threaded one end	4	102	20 GA. Chrome
719 203		1 1/4" x 6"	6	152	20 GA. Chrome
720 203		1 1/4" x 8"	8	203	20 GA. Chrome
722 201		1 1/4" x 12"	12	305	20 GA. Rough Brass
722 203		1 1/4" x 12"	12	305	20 GA. Chrome
723 201		1 1/2" x 4", threaded one end	4	102	20 GA. Rough Brass
724 201		1 1/2" x 6"	6	152	20 GA. Rough Brass
724 203		1 1/2" x 6"	6	152	20 GA. Chrome
725 201		1 1/2" x 8"	8	203	20 GA. Rough Brass
725 203		1 1/2" x 8"	8	203	20 GA. Chrome
727 201		1 1/2" x 12"	12	305	20 GA. Rough Brass
727 203		1 1/2" x 12"	12	305	20 GA. Chrome
728 201		1 1/2" x 18"	18	457	20 GA. Rough Brass
729 201		1 1/2" x 24"	24	610	20 GA. Rough Brass
735 201		1 3/8" x 12"	12	305	20 GA. Rough Brass
735 203		1 3/8" x 12"	12	305	20 GA. Chrome
722 171		1 1/4" x 12"	12	305	17 GA. Rough Brass
722 173		1 1/4" x 12"	12	305	17 GA. Chrome
727 171		1 1/2" x 12"	12	305	17 GA. Rough Brass
727 173		1 1/2" x 12"	12	305	17 GA. Chrome



815 Chestnut Street • N. Andover, MA 01845
 Tell: 978.688.1811 Fax: 978.794.1848
www.wattsbrass-tubular.com

Watts product specifications in U.S. customary units and metric are approximate and are provided for reference only. For precise measurements, please contact Watts Technical Service. Watts reserves the right to change or modify product design, construction, specifications, or materials without prior notice and without incurring any obligation to make such changes and modifications on Watts products previously or subsequently sold.