

SINK SPECIALTIES



"MAX" ADAPTER

W-R#	Size	Min	Box
0225030	3/8" X 3/8" X 3/8"	6	24
0225032	3/8" X 1/4" X 3/8"	6	24

- For add-on installation of water filters and ice makers. Takes an ordinary stop valve and makes it a three-way valve.



CHROME-PLATED STEEL FLAT ESCUTCHEON

W-R#	Size - IPS	OD	Min	Box
1610002	3/8"	2 1/2"	25	500
1610004	1/2"	2 1/2"	25	500
1610006	3/4"	2 1/2"	25	250
1610008	1"	2 7/8"	25	250
1610010	1 1/4"	2 7/8"	25	200
1610012	1 1/2"	3"	25	200
1610014	2"	3"	25	100

Nom.	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"
IPS	.84	1.05	1.32	1.66	1.90	2.38
Copper	5/8"(.63)	7/8"(.88)	1 1/8"(1.13)	1 3/8"(1.38)	1 5/8"(1.63)	2 1/8"(2.13)
Tubular				1 1/4"	1 1/2"	2"

W-R#	Size - Copper	OD	Min	Box
1611004	5/8"OD	2 1/2"	25	500
1611006	7/8"OD	2 1/2"	25	250
1611008	1 1/8"OD	2 7/8"	25	250
* 1611009	1 1/4"OD	2 7/8"	25	200
* 1611010	1 1/2"OD	3"	25	200
* 1611012	2"OD	3"	25	100

* Denotes tubular size



ROUGH BRASS FLAT ESCUTCHEON

- meets NYCHA specifications



W-R#	Size - IPS	OD	Min	Box
1618002	3/8"	2 1/2"	25	500
1618004	1/2"	2 1/2"	25	500
1618006	3/4"	2 1/2"	25	250
1618008	1"	2 7/8"	25	250
1618010	1 1/4"	2 7/8"	25	200
1618012	1 1/2"	3"	25	200
1618014	2"	3"	25	100

W-R#	Size - Copper	OD	Min	Box
1618502	5/8"OD	2 1/2"	25	500
1618504	7/8"OD	2 1/2"	25	250



WHITE PLASTIC SURE GRIP FLAT ESCUTCHEON

W-R#	Size (Copper)	Min	Box
1615020	5/8"OD	25	25
1615022	7/8"OD	25	25

SINK SPECIALTIES



**CHROME-PLATED
STEEL
BELL ESCUTCHEON**

W-R#	Size - IPS	OD	Min	Box
1612002	3/8"	2 3/8"	25	25
1612004	1/2"	2 3/8"	25	25

W-R#	Size - Copper	OD	Min	Box
1613006	5/8"OD	2 3/8"	25	25
* 1613009	1 1/4"OD	3"	1	25
* 1613010	1 1/2"OD	3"	1	25

* Denotes tubular size



**CHROME-PLATED
STEEL
BOX ESCUTCHEON**

W-R#	Size - IPS	OD	Min	Box
1614002	1 1/4"	3"	5	25
1614004	1 1/2"	3"	5	25

W-R#	Size - Copper	OD	Min	Box
1614012	1 3/8"OD	3"	5	25
* 1614006	1 1/4"OD	3"	5	25
* 1614008	1 1/2"OD	3"	5	25

* Denotes tubular size



**PLASTIC
SPLIT ESCUTCHEONS**

W-R#	Size (IPS)	Finish	Min
1731500	3/8" IP	Chrome	12
1731502	1/2" IP	Chrome	12
1731504	3/4" IP	Chrome	12
1731506	1" IP	Chrome	12
1731508	1 1/4" IP	Chrome	12
1731510	1 1/2" IP	Chrome	12
1731512	2" IP	Chrome	12
1731514	2 1/2" IP	Chrome	12
1731516	3" IP	Chrome	12
1731518	4" IP	Chrome	12
1731522	6" IP	Chrome	1

Nom.	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"
IPS	.84	1.05	1.32	1.66	1.90	2.38
Copper	5/8"(.63)	7/8"(.88)	1 1/8"(1.13)	1 3/8"(1.38)	1 5/8"(1.63)	2 1/8"(2.13)
Tubular				1 1/4	1 1/2	2

W-R#	Size (Copper)	Finish	Min
1731602	5/8"OD	Chrome	12
1731802	5/8"OD	White	12
1731604	7/8"OD	Chrome	12
1731606	1 1/8"OD	Chrome	12
1731608	1 3/8"OD	Chrome	12
1731610	1 5/8"OD	Chrome	12
1731612	2 1/8"OD	Chrome	12

SINK SPECIALTIES



**STEEL
FLOOR AND CEILING
PLATES, LESS SPRING**

W-R#	Size - IPS	OD	Min	Box
1728000	3/8"	2 1/2"	12	144
1728002	1/2"	2 3/4"	12	144
1728004	3/4"	2 3/4"	12	144
1728006	1"	3 1/2"	12	144
1728008	1 1/4"	3 1/2"	12	144
1728010	1 1/2"	3 1/2"	12	144
1728012	2"	4 1/4"	12	120

W-R#	Size - Copper	OD	Min	Box
1730002	5/8"OD	2 3/4"	12	144
1730004	7/8"OD	2 3/4"	12	144
1730006	1 1/8"OD	2 3/4"	12	144
1730008	1 3/8"OD	3 1/2"	12	144
1730010	1 5/8"OD	3 1/2"	12	144



**HEAVY-DUTY STEEL
FLOOR AND CEILING
PLATES, WITH SPRING**

W-R#	Size - IPS	OD	Min	Box
1729000	3/8"	2 1/4"	12	144
1729002	1/2"	2 1/2"	12	144
1729004	3/4"	2 3/4"	12	144
1729006	1"	3 1/4"	12	144
1729008	1 1/4"	3 1/2"	12	144
1729010	1 1/2"	3 7/8"	12	144
1729012	2"	4 1/2"	12	120
1729014	2 1/2"	5 3/8"	12	120
1729016	3"	5 7/8"	1	12
1729018	3 1/2"	6 5/8"	1	12
1729020	4"	7 1/8"	1	12
1729022	5"	9"	1	12
1729024	6"	10"	1	12

Nom.	1/2"	3/4"	1"	1 1/4"	1 1/2"	2"
IPS	.84	1.05	1.32	1.66	1.90	2.38
Copper	5/8"(.63)	7/8"(.88)	1 1/8"(1.13)	1 3/8"(1.38)	1 5/8"(1.63)	2 1/8"(2.13)
Tubular				1 1/4	1 1/2	2

W-R#	Size - Copper	OD	Min	Box
1731002	3/8"OD	2 3/8"	12	144
1731004	5/8"OD	2 3/8"	12	144
1731006	7/8"OD	2 3/4"	12	144
1731008	1 1/8"OD	3"	12	144
1731010	1 3/8"OD	3 1/4"	12	144
1731012	1 5/8"OD	3 5/8"	12	144
1731014	2 1/8"OD	4"	12	120
1731016	2 5/8"OD	4 7/8"	1	48
1731018	3 1/8"OD	5 1/8"	1	48