



High-quality, architecturally pleasing, innovative access doors for walls, ceilings, ducts, floors and roofs



FIRE-RATED UNINSULATED - for walls

FB-5060

Application

- For wall applications.
- Designed to maintain continuity in a 2 hour fire rated wall, when temperature is not a factor

Product Features

- Concealed hinge • Self-closing • Self-Latching
- Inside latch release
- Available with a removable door panel

FB-5060 Access Door Specifications:

Door / Door Frame: Steel or Stainless Steel: 16 gage door, 16 gage mounting frame. Flush to frame with reinforced edges, flange to be 1" wide

Hinge: Concealed

Fire Rating: UL — 1-1/2 hour "B" label. ULC — 2 hour "B" label. (optional)

Standard Latch: Universal self-latching bolt, operated by either a knurled knob or flush key. When master keying is required, doors can be prepared for rim or mortise cylinder locks.

Finish: Steel: 5 stage iron phosphate preparation with prime coat of White alkylid baking enamel. Stainless Steel: #4 satin polish.



AVAILABLE SIZES (Special sizes available upon request)

NOMINAL DOOR SIZE W X H		WEIGHT PER DOOR		
inches	mm	Latches	lbs.	kg.
8 X 8	203 X 203	1	5.5	2.5
10 X 10	254 X 254	1	6.7	2.9
12 X 12	305 X 305	1	8.3	3.8
14 X 14	355 X 355	1	9.5	4.3
16 X 16	406 X 406	1	11.5	5.2
18 X 18	457 X 457	1	14.3	6.5
22 X 30	560 X 762	1	32.5	14.5
22 X 36	560 X 914	2	28	12.7
24 X 24	610 X 610	1	20.3	9.2
24 X 36	610 X 914	2	28.5	12.9
24 X 48	610 X 1220	2	34	10.6
30 X 30	762 X 762	2	28.5	12.9
36 X 36	914 X 914	2	38	17.2
36 X 48	914 X 1220	2	47.5	21.5

Wall opening is W + 3/8" (9 mm)
For detailed specifications see submittal sheet

