



AUTOMATIC SPRINKLERS GL SERIES UPRIGHT • PENDENT VERTICAL SIDEWALL HORIZONTAL SIDEWALL CONVENTIONAL (OLD STYLE)

DESCRIPTION AND OPERATION

The Globe GL Series Sprinkler is a low profile yet durable design which utilizes a frangible glass ampule as the thermo-sensitive element. While the sprinkler provides an aesthetically pleasing appearance, it can be installed wherever standard spray sprinklers are specified. This sprinkler series is available in various styles, orifices, temperature ratings and finishes to meet varying design requirements.

The heart of Globe's GL Series sprinkler proven actuating assembly is a hermetically sealed frangible glass ampule that contains a precisely measured amount of fluid. When heat is absorbed, the liquid within the bulb expands increasing the internal pressure. At the prescribed temperature the internal pressure within the ampule exceeds the strength of the glass causing the glass to shatter. This results in water discharge which is distributed in an approved pattern depending upon the deflector style used.



UPRIGHT



CONVENTIONAL



PENDENT



VERTICAL SIDEWALL



HORIZONTAL SIDEWALL

TECHNICAL DATA

- See reverse side for Approvals and Specifications.
- Temperature Ratings - 135°F (57°C), 155°F (68°C), 175°F (79°C), 200°F (93°C), 286°F (141°C), 360°F (182°C)
- 500°F (260°C) Available Upon Request Without Approvals
- Water Working Pressure Rating - 175 psi (12 Bars)
- Factory tested hydrostatically to 500 psi (34 Bars)
- Maximum low temperature glass bulb rating is -67°F (-55°C)
- Frame - bronze • Deflector - brass • Screw - brass
- Bulb seat - copper • Spring - nickel alloy • Seal - teflon
- Bulb - glass with glycerin solution, 5mm size

• SPRINKLER TEMPERATURE RATING/CLASSIFICATION and COLOR CODING

CLASSIFICATION	AVAILABLE SPRINKLER TEMPERATURES		BULB COLOR	N.F.P.A. MAXIMUM CEILING TEMPERATURE	
ORDINARY	135°F/155°F	57°C/68°C	ORANGE/RED	100°F	38°C
INTERMEDIATE	175°F/200°F	79°C/93°C	YELLOW/GREEN	150°F	66°C
HIGH	286°F	141°C	BLUE	225°F	107°C
EXTRA HIGH	360°F	182°C	MAUVE	300°F	149°C
ULTRA HIGH	500°F	260°C	BLACK	475°F	246°C

AUTOMATIC SPRINKLERS GL SERIES

SPECIFICATIONS

NOMINAL "K" FACTOR		THREAD SIZE	LENGTH ¹	FINISHES
2.8	(39 metric)	1/2" NPT	2 1/4" (5.7 cm)	Factory Bronze Bright Chrome
4.2	(59 metric)	1/2" NPT	2 1/4" (5.7 cm)	Satin Chrome ²
5.6	(80 metric)	1/2" NPT	2 1/4" (5.7 cm)	White Polyester ³
7.8	(111 metric)	1/2" NPT	2 1/4" (5.7 cm)	Black Polyester ^{2,3}
8.1	(116 metric)	3/4" NPT	2 7/16" (6.2 cm)	Wax Coated ^{2,3,4} Lead Coated ^{2,3} Wax over Lead ^{2,3,4}

NOTE: METRIC CONVERSIONS ARE APPROXIMATE.

¹ HORIZONTAL SIDEWALL IS 2 9/16".

² FINISHES AVAILABLE ON SPECIAL ORDER.

³ AVAILABLE AS cULus LISTED CORROSION RESISTANT-WHEN SPECIFIED ON ORDER.

⁴ WAX COATING UL LISTED UP TO 200°F ONLY.

APPROVALS

STYLE	SIN MODEL	ORIFICE SIZE	135°F 57°C	155°F 68°C	175°F 79°C	200°F 93°C	286°F 141°C	360°F 182°C	* 500°F * 260°C	cULus	FM	LPC	CE	NYC - DOB MEA 101-92-E
UPRIGHT	GL2861	2.8	X	X	X	X	X	X	X	X	---	---	---	X
	GL4261	4.2	X	X	X	X	X	X	X	X	---	---	---	X
	GL5661	5.6	X	X	X	X	X	X	X	X	X	X	X	X
	GL8161	7.8†	X	X	X	X	X	X	X	X	---	---	---	X
	GL8164	8.1	X	X	X	X	X	X	X	X	X	X	X	X
PENDENT	GL2851	2.8	X	X	X	X	X	X	X	X	---	---	---	X
	GL4251	4.2	X	X	X	X	X	X	X	X	---	---	---	X
	GL5651	5.6	X	X	X	X	X	X	X	X	X	X	X	X
	GL8151	7.8†	X	X	X	X	X	X	X	X	X	---	---	X
	GL8156	8.1	X	X	X	X	X	X	X	X	X	X	X	X
VERTICAL SIDEWALL ‡	GL5675	5.6	X	X	X	X	X	X	X	X	X	---	---	X
	GL8176	8.1	X	X	X	X	X	X	X	X	---	---	---	X
HORIZONTAL SIDEWALL §	GL2870	2.8	X	X	X	X	X	X	X	X	---	---	---	X
	GL4270	4.2	X	X	X	X	X	X	X	X	---	---	---	X
	GL5670	5.6	X	X	X	X	X	X	X	X	X	---	---	X
	GL8171	8.1	X	X	X	X	X	X	X	X	---	---	---	---
CONVENTIONAL (OLD STYLE)	GL5668	5.6	X	X	X	X	X	X	X	---	---	X	X	---
	GL8169	8.1	X	X	X	X	X	X	X	---	---	X	X	---

*500°F/260°C AVAILABLE UPON REQUEST WITH NO APPROVALS.

† 1/2" NPT.

‡ VERTICAL SIDEWALL UL LISTED FOR LIGHT HAZARD ONLY.

§ HORIZONTAL SIDEWALL UL LISTED FOR DEFLECTOR 4" TO 12"

¶ PENDING VERTICAL SIDEWALL UL LISTED FOR 6' MIN. SPACING.

§ UPRIGHT VERTICAL SIDEWALL UL LISTED FOR 9' MIN. SPACING.

§ HORIZONTAL SIDEWALL UL LISTED FOR DEFLECTOR 4" TO 12" BELOW THE CEILING, FM APPROVED 4" TO 6".

ORDERING INFORMATION

SPECIFY

- Quantity • Model Number • Style
- Orifice • Thread Sizes • Temperature
- Finishes desired
- Quantity - Wrenches - P/N 325390 (1/2"); P/N 312366 (L.O.)

GLOBE® PRODUCT WARRANTY

Globe agrees to repair or replace any of its own manufactured products found to be defective in material or workmanship for a period of one year from date of shipment.

For specific details of our warranty, please refer to Price List Terms and Conditions of Sale (Our Price List).



4077 AIRPARK DRIVE, STANDISH, MICHIGAN 48658

989-846-4583

FAX 989-846-9231

1-800-248-0278

www.globesprinkler.com