



Item	Description	DEL	DEL	DEL
		30 102	40 102	50 102
1	Anode, Plug BAR, BUSS			
2	Left Hand	38022	38022	38022
3	Right Hand	38021	38021	38021
4	*Bushing, A-7 Circuit	98863	98863	98863
5	Collar, Pipe	20172-14	20172-14	20172-14
6	Cover, Front	38428	38428	38428
7	ELEMENT, HEATING	See Element Chart Below		
8	Gasket, Element	<u>42537</u>	<u>42537</u>	<u>42537</u>
9	Opening Insulation	43307	43307	43307
10	Fitting, Extension	43231-1	-----	-----
11	JUNCTION BOX			
	Except A-7	180398	180398	180398
	A-7 Circuit	68595	68595	68595
12	COVER, JUNCTION BOX			
	Except A-7	43441	43441	43441
	A-7 Circuit	2233	2233	2233
13	*Instruction Manual LABEL	41863	41863	41863
14	*Scald Warning	181138	181138	181138
15	*Temperature Warning	182734	182734	182734
16	PERSONNEL PROTECTOR			
	Except A-6 Lower & A-7 Upper	182117	182117	182117
	Lower A-6 Circuit	182117-1	182117-1	182117-1
	Upper A-7 Circuit	39909	39909	39909
17	Pipe Nipple PLUG	38469(1)	38469-5(2)	38469-5 (2)
18	Cap	42306-1	42306-1	42306-1
19	Element	42290	42290	42290
20	Pipe	-----	92650-1	92650-1
21	SWITCH, HIGH LIMIT			
	Upper A-6 & Lower A-7 Circuits	<u>23899-170</u>	<u>23899-170</u>	<u>23899-170</u>
	Upper A-7 Circuit	<u>38017</u>	<u>38017</u>	<u>38017</u>
	C-2 Circuit	<u>23899-170</u>	<u>23899-170</u>	<u>23899-170</u>
	TERMINAL BLOCK			
22	A-7 Circuit	68305	68305	68305
23	End A-7 Circuit	68305-1	68305-1	68305-1
	THERMOSTAT			
24	Upper A-6 Circuit	<u>23898-170</u>	<u>23898-170</u>	<u>23898-170</u>
24	Lower A-6 Circuit	<u>23897-170</u>	<u>23897-170</u>	<u>23897-170</u>
24	Lower A-7 Circuit	<u>23897-170</u>	<u>23897-170</u>	<u>23897-170</u>
24	C-2 Circuit	<u>23897-170</u>	<u>23897-170</u>	<u>23897-170</u>
25	Upper A-7 Circuit	<u>38008</u>	<u>38008</u>	<u>38008</u>
27	Bracket, Thermostat	<u>182707</u>	<u>182707</u>	<u>182707</u>
28	TUBE, INLET	160501-24	160501-24	160501-24
29	Spacer VALVE	42589	42589	42589
30	Drain	<u>26273-4</u>	<u>26273-4</u>	<u>26273-4</u>
	Relief	<u>76527</u>	<u>43151</u>	<u>43151</u>

SCREW-IN ELEMENT CHART

Wattage	120V	208V	240V	277V	480V
1000	23790-2	-----	23791-2	-----	-----
1500	23790-4	23775-4	23791-4	23782-4	-----
2000	23790-5	23775-5	23791-5	23782-5	-----
2500	23790-6	23775-6	23791-6	23782-6	23783-6
3000	23790-7	23775-7	23791-7	23782-7	23783-7
3500	-----	-----	23791-8	-----	-----
4000	-----	23775-9	23791-9	-----	23783-9
4500	-----	23775-10	23791-10	23782-10	23783-10
5000	-----	23775-11	23791-11	-----	23783-11
5500	-----	-----	23791-14	-----	-----
6000	-----	23775-12	23617-12	23782-12	23783-12

* Not Illustrated

Part numbers underlined are recommended stock items for emergency replacement.

Standard hardware items may be purchased locally.