











A.O. Smith Water Heaters

GAS

RESIDENTIAL WATER HEATER PARTS LIST
MODELS GPVX-50, 50Q, 50L
SERIES 100, 101



A.O. Smith Water Heater Parts Fulfillment
125 Southeast Parkway
Franklin, TN 37068
1-800-527-1953
www.hotwater.com

Item	Description	GPVX-50	GPVX-50
		GPVX-50Q	GPVX-50Q
		GPVX-50L	GPVX-50L
		100	101
1 Anode Aluminum - 6 Year	183523-029	183523-029
2 Baffle, Flue	185136-000	185136-000
3 Ring, Flue Restrictor	034894-000	034894-000
4 Blower Assembly	185331-000	185331-000
5 **Limit Switch	183380-004	183380-004
6 Pressure Switch	185110-005	185110-005
7 Adaptor, Exhaust	185215-000	185215-000
8 Hose Clamp - 4"	183545-001	183545-001
9 Blower Assembly Gasket	184956-000	184956-000
10 Burner Assembly - Natural Gas	185193-006	N/A
10 Burner Assembly - Propane Gas	N/A	185194-006
11 Burner Head with Door Gasket - Natural	183583-000	N/A
11 Burner Head with Door Gasket - Propane	N/A	183220-000
12 Igniter Assy, Hot Surface with Door Gasket	184923-000	184923-000
13 Orifice, Main Burner with Door Gasket - Natural	181508-026	N/A
13 Orifice, Main Burner with Door Gasket - Propane	N/A	181791-042
14 Burner Tube Assy with Door Gasket - Natural	184931-005	N/A
14 Burner Tube Assy with Door Gasket - Propane	N/A	184932-007
15 Inner Door with Door Gasket	183425-000	183425-000
16 Inner Door Gasket	183162-000	183162-000
17 Viewport Assembly	184470-000	184470-000
18 FV Sensor Bracket	185310-000	185310-000
19 FV Sensor	184952-000	184952-000
20 Combination Gas Valve - Natural	184960-002	N/A
20 Combination Gas Valve - Propane	N/A	184960-003
21 Outer Door	183458-000	183458-000
22 Envelope with Parts	183509-004	183509-004
23 Wall Plate, 2"	182787-000	182787-000
24 Wall Plate, 3"	181557-000	181557-000
25 Wall Plate, 4"	185403-000	185403-000
26 Vent Terminal Assembly 2"	183006-000	183006-000
27 Vent Terminal Screen 3"	181662-000	181662-000
28 Vent Terminal Screen 4"	196070-000	196070-000
29 Instruction Sheet - 3" & 4" Screens	185308-000	185308-000
30 Instruction Tag - 3" Screens	185287-000	185287-000
31 Instruction Tag - 4" Screens	185287-001	185287-001
32 Vent Terminal Restrictor - Ring 4"	N/A	N/A
33 Instruction Sheet - 3" & 4" Screens & Restrictor Ring	N/A	N/A
34 Pipe Insulation (optional)	181639-003	181639-003
35 T & P Insulation (optional)	183256-000	183256-000
36 Nipples - 5"	184715-000	184715-000
37 Spacer Inlet Tube	184011-000	184011-000
38 Inlet Tube, Diffuser	183766-029	183766-029
 (All Models Except: GPVX-50Q)		
38 Inlet Tube, Turbo	183901-032	183901-032
 (Only These Models: GPVX-50Q)		
39 Valve, Drain - Brass	026273-007	026273-007
39 Valve, Drain - Plastic	N/A	N/A
40 Valve, T & P Relief	043151-000	043151-000
41 Wire Harness	183506-001	183506-001
42 Dirt Leg Assembly	181206-001	181206-001
43 Air Intake Screen	183159-000	183159-000
44 Thermostat Shield (optional)	185424-000	185424-000
45 20" Dia. Aluminum Drain Pan with Side Drain (optional)	9002842	9002842
45 22" Dia. Aluminum Drain Pan with Side Drain (optional)	9002843	9002843
45 24" Dia. Aluminum Drain Pan with Side Drain (optional)	9002844	9002844
45 26" Dia. Aluminum Drain Pan with Side Drain (optional)	9002845	9002845

**Limit Switch located inside control box of blower assembly.