


RECIPROCATING BLADES CROSS REFERENCE CHART

| | TPI | LENGTH | | DESC | SHAPE | COMPETITIVE CROSS REFERENCE | | | | |
|---------------------|--------------|--------|--------|---|---|---|---------------------------------|------------------------|---|---|
| | | IN | MM | | | BOSCH® | DeWALT® | MILWAUKEE® | MK MORSE® | |
| DIAMOND™ | Grit | 8 | 203 | 800RDG |  | — | — | — | — | |
| | Gold™ | 10 | 6 | 152 | 610G |  | — | — | — | — |
| | | 10 | 6 | 152 | 6110G |  | — | — | — | — |
| | | 10 | 8 | 203 | 810G |  | — | — | — | — |
| | | 10 | 9 | 229 | 9110G |  | — | — | — | — |
| | | 14 | 6 | 152 | 614G |  | — | — | — | — |
| | | 14 | 6 | 152 | 6114G |  | — | — | — | — |
| | | 14 | 9 | 229 | 9114G |  | — | — | — | — |
| | | 18 | 6 | 152 | 618G |  | — | — | — | — |
| | | 18 | 6 | 152 | 6118G |  | — | — | — | — |
| 18 | | 9 | 229 | 9118G |  | — | — | — | — | |
| 24 | 6 | 152 | 624G |  | — | — | — | — | | |
| LAZER™ | 8 | 6 | 152 | 6108R |  | RSM6X2, RSM7X2 | — | 5700, 5701 | — | |
| | 8 | 9 | 229 | 9108R |  | RSM9X2 | — | 5705, 5706 | — | |
| | 8 | 12 | 305 | 12108R |  | RSM12X2 | — | 5710, 5711 | — | |
| | 10 | 6 | 152 | 6110R |  | S123XF, RPRM6, SAPP6 | — | 5712 | RB66210, RBFR66210W, RBMC64210 | |
| | 10 | 9 | 229 | 9110R |  | — | — | 5713 | RB1010, RBMC95010 | |
| | 10 | 12 | 305 | 12110R |  | RAP1210 | — | — | RB1210, RB126210, RBFR126210W, RBMC125010 | |
| | 14 | 6 | 152 | 6114R |  | RCM6X2, RCTM6X2 | — | — | RBFR66214W, RBMC64214 | |
| | 14 | 9 | 229 | 9114R |  | RCM9X2 | — | 5787, 5795 | RBFR96214W, RBMC95014 | |
| | 14 | 12 | 305 | 12114R |  | RCM12X2 | — | — | RB1214, RBFR126214W, RBMC125014, RBU10514 | |
| | 18 | 6 | 152 | 6118R |  | RCTM6X2 | — | 5784 | RB65018, RBMC64218 | |
| 18 | 9 | 229 | 9118R |  | — | — | 5788, 5798 | RBMC95018 | | |
| 18 | 12 | 305 | 12118R |  | — | — | 5789 | RBMC125018 | | |
| DEMOLITION | 6 | 6 | 152 | 6066R |  | RDN6V | DW4862 | 5021 | RB66206C | |
| | 6 | 9 | 229 | 966R |  | RDN9V | DW4863 | 5026 | RB96206 | |
| | 6 | 12 | 305 | 106R |  | RDN12V | DW4806, DW4806B, DW4845, DW4877 | 5027 | RB126206 | |
| | 10 | 9 | 229 | 960R |  | RDM6X2, RDM9X2 | — | — | RB96210, RBFR96210W | |
| | 10/14 | 6 | 152 | 650R |  | RD6V, RRD6V, SRD6, RAP6V | DW4864, DW4864B | — | RB61014, RB6501014, RB6501014T | |
| MASTER-GRIT® | Grit | 6 | 152 | 600RG |  | RCB6G | — | 1400, 1410, 1420, 1430 | RTCG4, RTCG6 | |
| | Grit | 8 | 203 | 800RG |  | RCB9G | — | — | RTCG8 | |

**NO
COMPETITIVE
EQUIVALENT**

RECIPROCATING BLADES CROSS REFERENCE CHART (CONTINUED)

| | TPI | LENGTH | | DESC | SHAPE | COMPETITIVE CROSS REFERENCE | | | |
|-------------------|-------|--------|------|---|---|--|--|------------------------|--|
| | | IN | MM | | | BOSCH® | DeWALT® | MILWAUKEE® | MK MORSE® |
| CARBIDE TIPPED | 3 | 8 | 203 | 8535RCT |  | — | — | — | RTCT6065 |
| | 6 | 6 | 152 | 6565RCT |  | — | — | — | RTCT6065 |
| | 6 | 6 | 152 | 6563RCT |  | — | — | — | RCFP66 |
| STANDARD BI-METAL | 4 | 6 | 152 | 634R |  | S234XF | DW4801 | — | RC603 |
| | 6 | 4 | 102 | 456RP |  | — | — | 5052 | RB606 |
| | 6 | 6 | 152 | 636RP |  | RDW66 | — | — | RB606P |
| | 6 | 6 | 152 | 656R |  | RDN6V, RHN66, RW66, RN66, RN96, RN126 | DW4802, DW4802B, DW4847, DW4848B, DW4876 | 5031, 5035 | RB63506, RB65006, RB65058, RC606 |
| | 6 | 6 | 152 | 676RC |  | — | DW4816 | 5041 | RB65006C |
| | 6 | 6 | 152 | 606R |  | — | DW4850 | 5012, 5015 | RB606ST, RB658, RC606ST |
| | 6 | 9 | 229 | 956R |  | RPRW8, RDN9V, RSN9V, RHN96, RW96 | DW4803, DW4803B, DW4848 | 5016, 5036 | RB93506, RB95006, RC905, RC906 |
| | 6 | 12 | 305 | 156R |  | RHN126, RW126 | DW4804, DW4804B, DW4849 | 5017, 5037 | RB123506, RB125006, RB125058ST, RB125058, RC1206 |
| | 10 | 6 | 152 | 610R |  | RPRAP6, RAP610 | DW4806, DW4806B, DW4845, DW4877 | 4091, 5090, 5091, 5092 | RB610, RB65010, RBMC610, RC610 |
| | 10 | 8 | 203 | 810R |  | RPRAP8, RAP810, RAP910 | DW4865B | 5093, 5175 | RB810, RB8501014, RBMC810 |
| | 10/14 | 8 | 203 | 850R |  | RD9V, RRD9V, SRD9, RAP9V | DW4865 | 5193 | RB81014, RB8501014 |
| | 10/14 | 12 | 305 | 110R |  | RD12V, RRD12V, SRD12, RFM10V, SHMF10, RAP12V | DW4838 | 5094, 5194 | RB121014, RB12501014, RB12501014ST, RB12501014 |
| | 14 | 3-5/8 | 92 | 314RC |  | — | DW4814 | 5161, 5162 | — |
| | 14 | 4 | 102 | 414R |  | — | DW4807, DW4807B | 5181 | RB414, RH414 |
| | 14 | 6 | 152 | 614R |  | RM614 | DW4808, DW4808B | 5182, 5282 | RB614, RB65014, RBMC614, RH614 |
| | 14 | 8 | 203 | 814R |  | RM914 | — | 5187 | RB814, RBMC814 |
| | 18 | 3-5/8 | 92 | 318RC |  | RSM418 | — | 5163 | RB318S, RH318S, RH324S |
| | 18 | 4 | 102 | 418R |  | RS418 | DW4810 | 5183 | RB418, RH318, RH418 |
| | 18 | 6 | 152 | 618R |  | RS618, RM618 | DW4811, DW4811B, DW4878 | 5184, 5284 | RB618, RBMC618, RH618 |
| | 18 | 8 | 203 | 818R |  | RM918 | DW4921 | 5188 | RB814, RB818, RBMC818 |
| | 18 | 12 | 305 | 118R |  | RM1218 | — | 5189 | RB1018, RB1218, RBMC1218 |
| | 24 | 4 | 102 | 424R |  | S518A, S518AF, S518AF-100, S518EF, S518G | DW4812 | 5185 | RB424, RH424 |
| | 24 | 6 | 152 | 624R |  | RM624 | DW4815 | 5186, 5286 | RB624, RBMC624, RH624 |
| 24 | 8 | 203 | 824R |  | RM924 | — | — | — | |