

Residential PowerStor Series[®] Single-Wall Indirect Water Heater



Photo is of
SW-2-65-L

The PowerStor Series[®] Single-Wall Models feature:

- **Heat Exchanger**—Single-Wall 1½" O.D. glass coated (Vitraglas[®]) carbon steel coil. The coil has a heat transfer area of 14.2 sq. ft. and a stored water volume of 2.7 Gal. Maximum supply temperature from the boiler must not exceed 240° F.
- **Factory Installed Hydrojet[®] Total Performance System**—Cold water inlet sediment reducing device helps prevent sediment build up in tank. Increases first hour delivery of hot water while minimizing temperature build up in tank.
- **Vitraglas[®] Lining**—Bradford White water heater tanks are protected from the corrosive effects of hot water by an exclusive ceramic porcelain-like coating. The Bradford White high silica Vitraglas[®] lining provides a tough interior surface for our hot water tanks.
- **Immersed Adjustable Honeywell Aquastat**—Fast acting immersion aquastat for automatic temperature control (adjustable from 80°F to 160°F).
- **Supply and Return Connections**—1" NPT female connections are located on the front for both the boiler collector supply and return.
- **2" Non-CFC Foam Insulation**—Covers the side and top of tank, reducing the amount of heat loss. This results in less energy consumption, improved operation efficiencies and jacket rigidity.
- **Potable Water Connections**—¾" NPT (1" NPT for 120 gallon model) factory installed true dielectric fittings extend water heater life and eases installation.
- **Three Protective Aluminum Anode Rods**—Provide added protection against corrosion for long trouble-free service.
- **Steel Tank**—Heavy gauge steel automatically formed, rolled and welded to assure a continuous seam for glass lining.
- **T&P Relief Valve**—Included.
- **Low Restriction Brass Drain Valve.**
- **I=B=R Certified**—These water heaters are rated by the Institute of Boiler and Radiation Manufacturers (I=B=R) to provide accurate performance data within the standards of the certification. The I=B=R rating is issued by the Hydronics Institute Division of AHRI and provide a recognized standard for proper comparison of hydronic appliances.



Limited Lifetime Tank and Heat Exchanger Warranties / 6-Year Limited Warranty on Component Parts.

For more information on warranty, please visit www.bradfordwhite.com

For products installed in USA, Canada and Puerto Rico. Some states do not allow limitations on warranties. See complete copy of the warranty included with the heater.


Residential PowerStor Single-Wall Indirect Water Heater

Single Wall Models

Meet or exceed ASHRAE 90.1b (current standard)

Model Number	Capacity		A Floor to Heater Top in.	B Jacket Dia. in.	C Floor to T&P Conn. in.	D Floor to Water Conn. in.	E Floor to Exchanger Outlet in.	F Floor to Exchanger Inlet in.	G Floor to Aquastat in.	Approx. Shipping Weight lbs.
	U. S. Gal.	Imp. Gal.								
SW-2-30-L	30	25	33 ³ / ₈	22	28 ¹ / ₄	34 ³ / ₈	5 ³ / ₈	27 ¹ / ₂	11 ¹ / ₂	164
SW-2-40R-L	38	32	41 ¹ / ₈	22	34 ³ / ₈	41 ¹ / ₈	5 ³ / ₈	27 ¹ / ₂	11 ¹ / ₂	185
SW-2-50R-L	48	40	46 ¹ / ₄	22	40 ¹ / ₈	47	5 ³ / ₈	27 ¹ / ₂	11 ¹ / ₂	195
SW-2-65-L	60	50	59 ¹ / ₄	22	53 ¹ / ₈	60	5 ³ / ₈	27 ¹ / ₂	11 ¹ / ₂	225
SW-2-80-L	75	62	59	24	52 ⁷ / ₈	59 ³ / ₄	5 ³ / ₈	27 ¹ / ₂	11 ¹ / ₂	250
SW-2-120-L	116	97	62 ¹ / ₂	28 ¹ / ₄	55 ³ / ₄	63 ¹ / ₄	6 ³ / ₈	28 ¹ / ₂	11 ¹ / ₂	370

Model Number	Capacity		A Floor to Heater Top mm.	B Jacket Dia. mm.	C Floor to T&P Conn. mm.	D Floor to Water Conn. mm.	E Floor to Exchanger Outlet mm.	F Floor to Exchanger Inlet mm.	G Floor to Aquastat mm.	Approx. Shipping Weight kg.
	Liters									
SW-2-30-L	114		854	559	718	873	137	699	292	74
SW-2-40R-L	143		1045	559	873	1064	137	699	292	85
SW-2-50R-L	182		1175	559	1019	1194	137	699	292	89
SW-2-65-L	227		1505	559	1349	1524	137	699	292	102
SW-2-80-L	284		1499	610	1343	1518	137	699	292	114
SW-2-120-L	439		1588	718	1416	1607	162	720	292	167



Heat Exchanger Head Loss					
GPM	2	5	8	10	12
Ft. of Hd. Loss	0.01	0.09	0.22	0.80	0.50

DOE Water Heater Performance

Model Number	Maximum First Hour Rating (Gal.) @		Continuous Draw Rating (Gal./Min.) @		Approximate Boiler Output Needed for Ratings (BTU/Hr.)
	140°F	115°F	140°F	115°F	
SW-2-30-L	279	429	4.2	6.7	220,000
SW-2-40R-L	288	438	4.2	6.7	220,000
SW-2-50R-L	297	447	4.2	6.7	220,000
SW-2-65-L	306	456	4.2	6.7	220,000
SW-2-80-L	321	470	4.2	6.7	220,000
SW-2-120-L	357	507	4.2	6.7	220,000

Based on 200°F boiler water temperature and 50°F potable water inlet.

I=B=R Water Heater Ratings

Model Number	First Hour Delivery @ 135°F (Gal.)	Continuous Draw Rating @ 135°F (Gal./Hr.)	Standby Heat Loss Rating (°F/Hr.)	Minimum Output Rate of Heat Source (BTU/Hr.)	Minimum Heat Source Flow Rate (Gal./Min.)
SW-2-30-L	255	235	1.2	157,000	13.7
SW-2-40R-L	260	235	1.1	157,000	13.7
SW-2-50R-L	265	235	0.9	157,000	13.7
SW-2-65-L	275	235	0.7	157,000	13.7
SW-2-80-L	295	235	0.6	157,000	13.7
SW-2-120-L	325	235	0.4	157,000	13.7

These certified ratings were obtained with a heat source output rate and flow rate as specified and a 180°F boiler water supply temperature. Other results will be obtained under different conditions.

General: All units are certified at 300 PSI (2068 kPa) test pressure

and 150 PSI (1034 kPa) working pressure. Potable water connections are 3/4" (19mm) NPT on 8" (203mm) centers. The 120 gallon model has 1" (25 mm) NPT potable water connections on 8" (203 mm) centers.

Dimensions and specifications subject to change without notice in accordance with our policy of continuous product improvement.

Suitable for Water (Potable) Heating and Space Heating.

Toxic chemicals, such as those used for boiler treatment, shall NEVER be introduced into the potable side of this system. The potable side may NEVER be connected to any existing heating system or component(s) previously used with a non-potable water heating appliance. The heat exchanger side of the unit may be used in space heating applications.



For U.S. and Canada field service, contact your professional installer or local Bradford White sales representative.

Sales 800-523-2931 • Fax 215-641-1670 / Technical Support 800-334-3393 • Fax 269-795-1089 • Warranty 800-531-2111 • Fax 269-795-1089

International: Telephone 215-641-9400 • Telefax 215-641-9750 / www.bradfordwhite.com

BRADFORD WHITE-CANADA INC. Sales / Technical Support 866-690-0961 / 905-238-0100 • Fax 905-238-0105 / www.bradfordwhite.com

Built to be the Best™

©2012, Bradford White Corporation. All rights reserved.