

Mastik Duct Sealing Tape



1580

Venture Tape 1580 Printed is a UL181B-FX listed foil tape approved for use on flexible and sheet metal ducts.

- **Provides an instant bond on most surfaces including sheet metal, flex duct, and duct wrap**
- **May also be used on FSK systems**
- **Hand tearable allows for easy installation**
- **Also excels in high heat and humidity conditions**

UL181B-FX

PRESSURE SENSITIVE TAPES FOR
USE WITH FLEXIBLE AIR DUCTS



www.venturetape.com

VentureTape®



Venture Tape Corp.
30 Commerce Rd. Rockland, MA 02370
Tel 781 331-5900, Fax 781 871-0065, E-mail sales@venturetape.com

1580 Printed

UL181B-FX LISTED MASTIK TAPE

Venture Tape 1580P is a printed 2.0-mil (50µm) annealed aluminum foil coated with a heavy application of mastik adhesive. The malleable foil applies easily to both fibrous and sheet metal ducts and conforms to irregular surfaces. Venture Tape 1580P meets UL181B-FX requirements and excels in demanding temperature and humidity applications and provides superior performance and durability over a wide range of environmental conditions.

TECHNICAL PRODUCT SPECIFICATIONS

Specification	Typical Value	Typical Value (Metric)	Test Method
Material Thickness (Total)	17.0 mils	431.8 µm	PSTC-133
Adhesive Peel Strength	112 oz/in	31.2 N/25mm	PSTC-101
Adhesive Shear Strength	>168 hours	>168 hours	PSTC-107
Tensile Strength	20 lb/in width	89 N/25mm	PSTC-131
Elongation	5%	5%	PSTC-131
Application Temperature Range	35°F to 120°F	2°C to 49°C	
Minimum Continuous Use Temperature	-20°F	-29°C	
Maximum Continuous Use Temperature	200°F	93°C	

PRODUCT FEATURES & SPECIFICATION APPROVALS

- UL181-FX Listed 
- Provides an instant, water resistant bond on most surfaces including sheet metal, duct board, flex duct, and duct wrap vapor barriers
- May also be used on FSK systems
- Hand tearable and conformable allows easy and reliable installations
- Excels in high heat and humidity conditions
- In stock product available for immediate delivery
- Standard roll sizes: 2" x 100 ft. and 3" x 100 ft.

Contact Venture Tape today for a complete list of products or a free sample

Toll Free North America 800-343-1076
From United Kingdom 0-800-962-957
From Australia 1-800-122-797
www.venturetape.com
www.boma.it

USA

Venture Tape Corp.
30 Commerce Road
Rockland, MA 02370
781-331-5900
FAX 781-871-0065

Europe - Venture Tape

Venture Tape Europe Corp.
Units 5 – 6, Faraday Close,
Drayton Fields, Daventry,
Northamptonshire, England NN11 8RD
(0) 1327 876555
FAX (0) 1327 876444

Europe - BOMA

BOMA s.r.l.
Via Aquileia 22/30
34070 Villesse (GO)
Italy
0481 96431 1
FAX 0481 91440

Australasia

Venture Tape Australasia, Pty., Ltd.
11B Production Drive
Campbellfield, Victoria 3061
Australia
(03) 9357 6025
FAX (03) 9357 6045



VentureTape®