



A.O. Smith Water Heater Parts Fulfillment  
 125 Southeast Parkway • Franklin, TN 37068  
 www.hotwater.com • 1-800-433-2545

## RESIDENTIAL GAS SERVICE PARTS LIST


### MODELS:

GCVL 30 200/201, XCVL 30 200/201		
GCVL 40 200/201, XCVL 40 200/201	GCV 40 200/201, XCV 40 200/201, GCVH 40L 200/201	GVR 40 200/201, XVR 40 200/201, XGV 40 200/201, XGV 40L 200/201
GVRL 40 200/201, XVRL 40 200/201, GVRL 40 202/203, XVRL 40 202/203	GCV 50 200/201, XCV 50 200/201	GVR 50 200/201, XVR 50 200/201, XGV 50 200/201, XGV 50L 200/201

Actual water heater may have one of the following SMRs, so it will vary from list accordingly:

- S19 - Magnesium Anode
  - S24 - No Name Plate
  - S41 - KA 90 Anode
  - S45 - Outlet Anode, Top T&P
  - S83 - Outlet Magnesium Anode, Top T&P
  - T25 - Magnesium Anode, Canadian Model
- Circulating Loop model ("L") after capacity same as standard except receive outlet magnesium & primary magnesium anode.

ANODE LOCATION  
 OR  
 TOP T&P LOCATION



ACTUAL APPEARANCE OF PARTS  
 MAY VARY FROM ILLUSTRATION.

Item	Description	GCVL 40	GCV 40	GVR 40	GVR 40	GCV 50	GVR 50	GVR 40	GCVL 30
		XCVL 40 200/201	XCV 40 GCVH 40L 200/201	XVR 40 XGV 40 XGV 40L 200/201	XVRL 40 XVRL 40 200/201	XCV 50 200/201	XGV 50 XGV 50L 200/201	XVRL 40 202/203	XCVL 30 200/201
1	Inlet Tube	9003668005	9006690005	9006690005	9003668005	9006688005	9006688005	9002545005	9006949005
	Inlet Tube Dynaclean II Conservationist XGV	-----	-----	9006798005	-----	-----	9006653005	-----	-----
2	Anode Aluminum	9003892005	9003892005	9003892005	9003892005	9003892005	9003892005	9003892005	9003892005
	Anode Magnesium	9001829005	9001829005	9001829005	9001829005	9001829005	9001829005	9001829005	9001829005
	Anode KA90	9006299005	9006299005	9006299005	9006299005	9006299005	9006299005	9006299005	9006299005
3	Outlet Anode (Alum.) W/Heat Trap	9006291005	9006291005	9006291005	9006291005	9006291005	9006291005	9006291005	9006291005
	Outlet Anode (Mag.) W/Heat Trap	9003938005	9003938005	9003938005	9003938005	9003938005	9003938005	9003938005	9003938005
4	T&P Valve (Top or side)	9000071015	9000071015	9000728015	9000728015	9000071015	9000728015	9000728015	9000071015
5	Drain Valve	9004330015	9004330015	9001870015	9001870015	9004330015	9001870015	9001870015	9004330015
6	Gas Control Valve/Thermostat W/ lead wires - Nat.	9006655005	9006655005	9006656005	9006656005	9006655005	9006656005	9006656005	9006655005
	Gas Control Valve/Thermostat W/ lead wires - LP	9006657005	9006657005	9006658005	9006658005	9006657005	9006658005	9006658005	9006657005
7*	Pilot Assembly Kit (Nat. Gas)	9006666015	9006666015	9006666015	9006666015	9006666015	9006666015	9006666015	9006666015
	Pilot Assembly Kit (LP Gas)	9006668015	9006667015	9006667015	9006668015	9006667015	9006667015	9006668015	9006667015
8*	Burner Head Assembly (Nat. Gas)	9006136005	9006136005	9006136005	9006136005	9006136005	9006136005	9006136005	9006136005
	Burner Head Assembly (LP Gas)	9006651005	9006603005	9006603005	9006651005	9006603005	9006603005	9006651005	9006603005
9*	Manifold Door/Burner Assembly, Complete (Nat. Gas)	9006619005	9006620005	9006620005	9006619005	9006621005	9006621005	9006620005	9006807005
	Manifold Door/Burner Assembly, Complete (LP Gas)	9006691005	9006618005	9006618005	9006691005	9006622005	9006622005	9006691005	9006618005
10*	Piezoelectric Igniter Button	9006143015	9006143015	9006143015	9006143015	9006143015	9006143015	9006143015	9006143015
11*	Thermocouple	9000056015	9000056015	9000056015	9000056015	9000056015	9000056015	9000056015	9000056015

\* Not shown in illustration.

