



## Application Selection Guide




# RedLINK™ Wireless Systems

It's no doubt that you're looking for ways to make more money for your business. Whether that's lowering labor costs or selling more content per home — or both — Honeywell Wireless and Prestige™ Comfort Systems are the answer. From the versatility of the Wireless FocusPRO® thermostat to profitable add-ons like the Portable Comfort Control, you'll gain sales opportunities while virtually eliminating installation risk. Our full suite of RedLINK™-enabled wireless system kits and accessories make it easy to meet homeowners' comfort needs — solving everyday problems and offering them more comfort solutions and wireless ways to control their equipment from anywhere in the home.



This complete lineup of wireless-enabled systems and components make it easy to solve what-used-to-be problems and meet your customers' comfort needs, with everything that you need to easily:

- Relocate a Thermostat
- Upgrade to Multi-Stage Equipment
- Add Cooling
- Display Outdoor Temperature and Humidity
- Offer Temperature Control On-Demand
- Easily Zone a Home Without Running Thermostat Wires
- Control All Zones From a Single Control
- Wirelessly Control Humidity



REDLINK™  
ENGINEERED  
FOR YOU



## Wireless Technology

# Exclusive Honeywell Technology Makes It Possible

### INTRODUCING REDLINK™

With wireless security systems installed in more than 100 million homes protecting people and property around the clock, Honeywell is a leader in wireless technology. Now Honeywell brings you RedLINK™ — the first wireless technology engineered specifically for HVAC applications.

### REALIZE THE POSSIBILITIES

RedLINK Wireless Technology eliminates the need to run wires in many applications and enables homeowners to have advanced comfort control anywhere in the home.

### WORKS EVERY TIME

The RedLINK signal has been tested and proven to work through concrete, brick and other building materials in homes up to 6,500 square feet with multiple levels. It works every time in every home.

### ZERO INTERFERENCE

RedLINK's ability to "hop frequencies" means that the signal is secure. It won't affect or be effected by other wireless devices in the home such as baby monitors and cordless phones — or with neighboring systems.

### TRUST

Backed by proven Honeywell technology, internal safeguards continuously self-check the signal — so it's never lost.

RedLINK is Reliability.

# Prestige™ Comfort Systems

## ELEGANT SIMPLICITY

For the industry's best contractors that want to set themselves apart, there's Prestige™ Comfort Systems. Prestige is the world's first high-definition, full-color thermostat that redefines how a thermostat can look and what a thermostat can do. There's simply nothing else like it.



## The Cool Factor

LIKE NOTHING YOU'VE EVER SEEN

- **Simple Touchscreen Technology** — no hidden doors or complex buttons
- **High-Definition, Color Display\*** — visual clarity of the display is 3 times better than typical thermostats
- **Graphics** — uses a graphical user interface to display information in a way that's easy to understand
- **User Friendly** — consumers rated up to 10 times easier to use\*\* than other thermostats
- **Tri-Lingual** — English, Spanish and French installation and display options
- **Temperature Control On-Demand** — sense and remotely adjust temperature from anywhere in the home
- **Added Information** — outdoor temperature and humidity displayed on screen

*\*Available in HD-High Definition (color) or SD-Standard Definition (black/white).*

*\*\*Source: Prestige Focus Group Study, August 2006, Worrell Research*

## The Brains

MORE THAN JUST A PRETTY FACE



While Prestige thermostats are wired, they are enabled with RedLINK™ Wireless Technology inside — you can offer endless possibilities for controlling and monitoring comfort with Honeywell system enhancements like the Portable Comfort Control, Wireless Outdoor Sensor and TrueSTEAM™ Humidification System.



# The Simplicity

## INSTALLS IN MINUTES, PROGRAMS ITSELF

Prestige's patented, interview-based setup screens use natural language to ask questions like "How many stages of heating are you running?" to guide installers through setup with no need for an installation manual. The same interview process is used for homeowner setup. After answering the questions, it programs itself — so they don't have to.

And if you do have a question, simply press the HELP button. The on-board manual gives definitions and directions for every screen.



User-Friendly Questions



Simple Setup



On-Screen Help

# The Convenience

## DOWNLOAD AND GO

After installing Prestige for a specific type of equipment, simply download the settings to a standard USB drive and transfer them to all future jobs where you use Prestige with the same type of equipment. It's that easy. The same USB drive can be used to upload your full-color business logo on the screen for customization of service reminders, giving homeowners on-screen access to you.



## WIRELESS HUMIDITY CONTROL



Increase homeowner satisfaction with Prestige by controlling both temperature and humidity with one control to reduce wall clutter. And because it communicates wirelessly to TrueSTEAM™ humidifiers, you'll have faster installation without pulling new wires to the thermostat.







# Prestige™ Comfort Systems Appli

With the perfect combination of engineering, high-resolution graphics and simple setup, Prestige redefines what a thermostat




## Selection Guide

		Solutions				Schedule Options				Application					Power Method	
Kit Includes:		Displays Outdoor Temperature and Humidity	Controls Humidification and Dehumidification	Temperature Control on Demand	Adjust All RedLINK-Enabled Thermostats from a Single Control	Program Options	ENERGY STAR®	Fixed and Adjustable Temporary Override	Permanent and Vacation Holds	Stages	Gas, Oil or Electric	Heat Pump	Forced Warm Air	Hot Water	Steam/Gravity	
<b>Prestige™ Comfort Systems</b>																
 Prestige HD Comfort System Kit YTHX9321R5003	Prestige HD, Portable Comfort Control and Wireless Outdoor Sensor	•	•	•	•	7-Day	•	•	•	Up to 3H/2C Heat Pump or 2H/2C Conventional	•	•	•	•	•	Prestige—Hardwired Portable Comfort Control and Wireless Outdoor Sensor — Battery
 Prestige HD Thermostat Kit YTHX9321R5012	Prestige HD and Wireless Outdoor Sensor	•	•	•*	•*	7-Day	•	•	•	Up to 3H/2C Heat Pump or 2H/2C Conventional	•	•	•	•	•	Prestige—Hardwired Wireless Outdoor Sensor — Battery
 Prestige SD Comfort Kit YTHX9321R1000	Prestige SD, Portable Comfort Control and Wireless Outdoor Sensor	•	•	•	•	7-Day	•	•	•	Up to 3H/2C Heat Pump or 2H/2C Conventional	•	•	•	•	•	Prestige—Hardwired Portable Comfort Control and Wireless Outdoor Sensor — Battery
 Prestige SD Thermostat Kit YTHX9321R1011	Prestige SD and Wireless Outdoor Sensor	•	•	•*	•*	7-Day	•	•	•	Up to 3H/2C Heat Pump or 2H/2C Conventional	•	•	•	•	•	Prestige—Hardwired Wireless Outdoor Sensor — Battery

\* REM5000R1001 required

# cations

can do.



Features & Functions														Display Information						Limited Warranty	Wiring Terminals		
Touchscreen User Interface	On-Screen Help	Real-Time Clock	Permanent Memory Retention	Auto or Manual Changeover	Interview-Based Programming	USB Port for Uploading Logo and Preset Installer Setup	Adaptive Intelligent Recovery™/Early Start™	Temperature Setpoint Limits	Keypad Lockout	Programmable Fan	Advanced Dual-Fuel Heat Pump Operation	Language Options	Remote Locator	Display Size (Viewable sq. in.)	High-Definition (HD) Color Display	Standard-Definition (SD) Display	Backlighting — Continuous or On-Demand	Simultaneous Display of Room and Set Temperatures	Filter, Humidifier Pad and UV Lamp Replacement Reminder	Dealer Logo On-Screen			
•	•	•	•	•	•	•	•	•	•	•	•	•	•	Prestige—8 Portable Comfort Control—7	•		•	•	•	•	•	Prestige—5 years Portable Comfort Control and Wireless Outdoor Sensor—1 year	C, R, Rc, W-0/B, W2-Aux/E, Y, Y2, G, L, K, HUM, HUM, DHM, DHM
•	•	•	•	•	•	•	•	•	•	•	•	•*	•	8	•		•	•	•	•	•	Prestige—5 years Wireless Outdoor Sensor—1 year	C, R, Rc, W-0/B, W2-Aux/E, Y, Y2, G, L, K, HUM, HUM, DHM, DHM
•	•	•	•	•	•	•	•	•	•	•	•	•	•	Prestige—8 Portable Comfort Control—7		•	•	•	•	•	•	Prestige—5 years Portable Comfort Control and Wireless Outdoor Sensor—1 year	C, R, Rc, W-0/B, W2-Aux/E, Y, Y2, G, L, K, HUM, HUM, DHM, DHM
•	•	•	•	•	•	•	•	•	•	•	•	•*	•	8		•	•	•	•	•	•	Prestige—5 years Wireless Outdoor Sensor—1 year	C, R, Rc, W-0/B, W2-Aux/E, Y, Y2, G, L, K, HUM, HUM, DHM, DHM



# Wireless FocusPRO® Systems

## The Problem Solver

Thanks to RedLINK™, the world's best-selling thermostat — Honeywell's FocusPRO — is now also wireless so it can go anywhere and solve any problem. Since there's no need to run new wires, there's no longer risk in bidding jobs. It all adds up to more jobs done more quickly, which adds up to more profits for you.



### RELOCATE A THERMOSTAT

In most homes, thermostats are located in areas where people don't spend the majority of their time. Now, with Wireless FocusPRO® — you can install the thermostat anywhere.

### UPGRADE TO MULTI-STAGE EQUIPMENT OR ADD COOLING

Put an end to pulling and snaking wires. Because all the wiring with our Wireless FocusPRO is done at an Equipment Interface Module by the equipment, adding multi-stage systems or cooling is a breeze.

### DISPLAY OUTDOOR TEMPERATURE AND HUMIDITY

It's often not feasible to run new wires outdoors. Our RedLINK-enabled Wireless Outdoor Sensor is the perfect solution — and displays outdoor temperature and humidity on Wireless FocusPRO thermostats.

### TEMPERATURE CONTROL ON DEMAND

Part of the Wireless FocusPRO system is the Portable Comfort Control. It senses temperature wherever it goes giving homeowners the freedom to make adjustments from any place in the home. Plus — with the added information of outdoor temperature and humidity on the Portable Comfort Control — your customers can make informed decisions on saving energy. If it's cooler outside than inside, homeowners can turn their system off to save energy.



# Wireless Zoning Systems

## The Game Changer

The RedLINK story gets even sweeter when it comes to zoning. When used with our RedLINK-enabled TrueZONE® panels, our Wireless Adapter allows you to easily — and wirelessly — add zoning to a home or add more zones to an existing system. Most zoning jobs can be done in one day and bidding risk is virtually eliminated.



### ADD A ZONE — ONE WIRED, ONE WIRELESS

Every home has one room or area that is too hot or cold. Solve that problem today with a RedLINK-enabled TrueZONE panel and Wireless Adapter Kit. TrueZONE panels support both wired and wireless thermostats — the choice is yours. Go one wired and one wireless or upgrade all to the Wireless FocusPRO.

### FOUR ZONES MADE EFFORTLESS AND WIRELESS

When homeowners want zoning, they typically identify more than two zones. With a TrueZONE HZ432 panel and the Wireless Adapter Kit, add up to four zones (per panel) without running thermostat wires.



### ONE CONTROL FOR EVERY ZONE

Add the Portable Comfort Control to give homeowners the control to change the temperature in any zone from anywhere in the house. For example, watch TV downstairs, but warm the upstairs bedroom before going to bed. Name each zone on the Portable Comfort Control with one of 60+ options — upstairs, master bedroom, office — even wine cellar and home theatre.





Homeowners can toggle between zones and adjust the temperature from anywhere in the home.

# Wireless FocusPRO® Systems Ap

Wireless FocusPRO thermostats are the same FocusPROs you already know and love — now wireless — and now able to communicate with other RedLINK™-enabled devices for a complete system approach that installs in the same amount of time.



## Selection Guide

		Solutions					Schedule Options			User Interface	Application			
Kit Includes:		Relocate Thermostat Without Running New Wires	Upgrade to Multi-stage or Add Cooling Without Running New Thermostat Wires	Displays Outdoor Temperature and Humidity	Temperature Control on Demand	Adjust All RedLINK-Enabled Thermostats from a Single Control	Program Options	ENERGY STAR®	Temporary Override	Permanent Hold	Stages	Gas, Oil or Electric	Heat Pump	
<b>Wireless FocusPRO® Systems (Non-Zoned)</b>														
 Programmable Wireless FocusPRO System Kit YTH6320R1015	Programmable FocusPRO, Equipment Interface Module, Portable Comfort Control, Wireless Outdoor Sensor and Return Air Sensor	•	•	•	•	•	5-1-1 / 5-2 Day	•	•	•	FocusPRO— Soft Keys Portable Comfort Control— Touchscreen	Up to 3H/2C Heat Pump or 2H/2C Conventional	•	•
 Programmable Wireless FocusPRO Kit YTH6320R1001	Programmable FocusPRO, Equipment Interface Module and Return Air Sensor	•	•	•*	•**	•**	5-1-1 / 5-2 Day	•	•	•	Soft Keys	Up to 3H/2C Heat Pump or 2H/2C Conventional	•	•
 Non-Programmable Wireless FocusPRO System Kit YTH5320R1017	Non-Programmable FocusPRO, Equipment Interface Module, Portable Comfort Control, Wireless Outdoor Sensor and Return Air Sensor	•	•	•	•	•					FocusPRO— Soft Keys Portable Comfort Control— Touchscreen	Up to 3H/2C Heat Pump or 2H/2C Conventional	•	•
 Non-Programmable Wireless FocusPRO Kit YTH5320R1000	Non-Programmable FocusPRO, Equipment Interface Module and Return Air Sensor	•	•	•*	•**	•**					Soft Keys	Up to 3H/2C Heat Pump or 2H/2C Conventional	•	•

\*C7089R1013 required    \*\* REM5000R1001 required

# Application



			Power Method	Features and Functions					Display Information				Limited Warranty	Wiring Terminals	
Forced Warm Air	Hot Water	Steam/Gravity		Permanent Memory Retention	Selectable Auto or Manual Changeover	Adaptive Intelligent Recovery™ / Early Start™	Temperature Setpoint Limits	Remote Locator	Backup Control	Display Size (Viewable sq. in.)	On-Demand Backlighting	Simultaneous Display of Room and Set Temperatures	Private Labeling Available		
•	•	•	Equipment Interface Module — Hardwired FocusPRO, Portable Comfort Control and Wireless Outdoor Sensor — Battery	•	•	•	•	•	•	FocusPRO — 5.09 Portable Comfort Control — 7	•	•	•	FocusPRO and Equipment Interface Module — 5 years Portable Comfort Control and Wireless Outdoor Sensor — 1 year	Equipment Interface Module C, R, Rc, Rh, W-0/B, W2-Aux/E, Y, Y2, G, L, RAS, RAS
•	•	•	FocusPRO — Battery Equipment Interface Module — Hardwired	•	•	•	•	•	•**	5.09	•	•*	•	FocusPRO and Equipment Interface Module — 5 years	Equipment Interface Module C, R, Rc, Rh, W-0/B, W2-Aux/E, Y, Y2, G, L, RAS, RAS
•	•	•	Equipment Interface Module — Hardwired FocusPRO, Portable Comfort Control and Wireless Outdoor Sensor — Battery	•	•	•	•	•	•	FocusPRO — 5.09 Portable Comfort Control — 7	•	•	•	FocusPRO and Equipment Interface Module — 5 years Portable Comfort Control and Wireless Outdoor Sensor — 1 year	Equipment Interface Module C, R, Rc, Rh, W-0/B, W2-Aux/E, Y, Y2, G, L, RAS, RAS
•	•	•	FocusPRO — Battery Equipment Interface Module — Hardwired	•	•	•	•	•	•**	5.09	•	•*	•	FocusPRO and Equipment Interface Module — 5 years	Equipment Interface Module C, R, Rc, Rh, W-0/B, W2-Aux/E, Y, Y2, G, L, RAS, RAS






# Wireless Zoning Systems Applic

Nothing beats zoning for the ultimate blend of comfort and energy savings. Honeywell TrueZONE® panels introduced effortless zoning installation and setup, and now Honeywell wireless zoning systems make zoning easier than ever.



## Selection Guide

	Kit Includes:	Solutions						Schedule Options			User Interface		Application
		Relocate Thermostat Without Running New Wires	Upgrade to Multi-stage or Add Cooling Without Running New Thermostat Wires	Add to a TrueZONE® System Without Running New Thermostat Wires	Displays Outdoor Temperature and Humidity	Add Dual Fuel Control Without Running Wires To Outdoor Sensor	Program Options	ENERGY STAR®	Temporary Override	Permanent Hold	Stages		
<b>Wireless Zoning Systems</b>													
 HZ432 Wireless Zoning Kit with Prestige YHZ432R5108	HZ432 TrueZONE Panel, Wireless Adapter, Discharge Air Temperature Sensor, AT140 Transformer, Prestige HD, Programmable FocusPRO, Portable Comfort Control and Wireless Outdoor Sensor	•	•	•	•	•	Prestige - 7 Day, FocusPRO - 5-1-1/5-2 Day	•	•	•	Prestige & Portable Comfort Control - Touchscreen, FocusPRO - Soft Keys	Up to 3H/2C Heat Pump or 3H/2C Conventional Through Zone Panel	
 HZ432 Wireless Zoning Kit YHZ432R1108	HZ432 TrueZONE Panel, Wireless Adapter, Discharge Air Temperature Sensor, AT140 Transformer, 2 Programmable FocusPRO's, Portable Comfort Control and Wireless Outdoor Sensor	•	•	•	•	•	5-1-1/ 5-2 Day	•	•	•	Portable Comfort Control - Touchscreen, FocusPRO - Soft Keys	Up to 3H/2C Heat Pump or 3H/2C Conventional Through Zone Panel	
 HZ322 Wireless Zoning Kit with Prestige YHZ322R5108	HZ322 TrueZONE Panel, Wireless Adapter, Discharge Air Temperature Sensor, AT140 Transformer, Prestige HD, Programmable FocusPRO's, Portable Comfort Control and Wireless Outdoor Sensor	•	•	•	•	•	Prestige - 7 Day, FocusPRO - 5-1-1/5-2 Day	•	•	•	Prestige & Portable Comfort Control - Touchscreen, FocusPRO - Soft Keys	Up to 3H/2C Heat Pump or 2H/2C Conventional	
 HZ322 Wireless Zoning Kit YHZ322R1108	HZ322 TrueZONE Panel, Wireless Adapter, Discharge Air Temperature Sensor, AT140 Transformer, 2 Programmable FocusPRO, Portable Comfort Control and Wireless Outdoor Sensor	•	•	•	•	•	5-1-1/ 5-2 Day	•	•	•	Portable Comfort Control - Touchscreen, FocusPRO - Soft Keys	Up to 3H/2C Heat Pump or 2H/2C Conventional	
<b>Wireless Zoning Adapter Kits</b>													
 Programmable Wireless Zoning Adapter Kit YTH6320R1023	Programmable FocusPRO and Wireless Adapter	•	•	•	•	•	5-1-1/ 5-2/Day	•	•	•	Soft Keys	Up to 3H/2C Heat Pump or 2H/2C Conventional	
 Non-Programmable Wireless Zoning Adapter Kit YTH5320R1025	Non-Programmable FocusPRO and Wireless Adapter	•	•	•	•	•					Soft Keys	Up to 3H/2C Heat Pump or 2H/2C Conventional	

\* C7089R1013 required

\*\* REM5000R1001 required

# ation



Power Method			Features and Functions					Display Information			Limited Warranty	Wiring Terminals	
Gas, Oil or Electric	Heat Pump	Forced Warm Air	Permanent Memory Retention	Selectable Auto or Manual Changeover	Adaptive Intelligent Recovery™/Early Start™	Temperature Setpoint Limits	Remote Locator	Display Size (Viewable sq. in.)	On-Demand Backlighting	Simultaneous Display of Room and Set Temperatures	Private Labeling Available		
•	•	•	•	•	•	•	•	Prestige - 8, Wireless FocusPRO - 5.09, Portable Comfort Control - 7	•	•	FocusPRO only	TrueZONE, Prestige, FocusPRO, & Wireless Adapter - 5 Years, Portable Comfort Control and Wireless Outdoor Sensor - 1 Year	Prestige - C, R, Rc, W-0/B, W2-Aux/E, Y Y2, G, L, K, HUM, HUM, DHM, DHM Wireless Adapter - A, B, C, D
•	•	•	•	•	•	•	•	Wireless FocusPRO - 5.09, Portable Comfort Control - 7	•	•	•	TrueZONE, FocusPRO, & Wireless Adapter - 5 Years, Portable Comfort Control and Wireless Outdoor Sensor - 1 Year	Wireless Adapter - A, B, C, D
•	•	•	•	•	•	•	•	Prestige - 8, Wireless FocusPRO - 5.09, Portable Comfort Control - 7	•	•	FocusPRO only	TrueZONE, Prestige, FocusPRO, & Wireless Adapter - 5 Years, Portable Comfort Control and Wireless Outdoor Sensor - 1 Year	Prestige - C, R, Rc, W-0/B, W2-Aux/E, Y Y2, G, L, K, HUM, HUM, DHM, DHM Wireless Adapter - A, B, C, D
•	•	•	•	•	•	•	•	Wireless FocusPRO - 5.09, Portable Comfort Control - 7	•	•	•	TrueZONE, FocusPRO, & Wireless Adapter - 5 Years, Portable Comfort Control and Wireless Outdoor Sensor - 1 Year	Wireless Adapter - A, B, C, D
•	•	•	•	•	•	•	•	FocusPRO — Battery Wireless Adapter - Hardwired	•	•	•	5 years	Wireless Adapter - A, B, C, D
•	•	•	•	•	•	•	•	FocusPRO — Battery Wireless Adapter - Hardwired	•	•	•	5 years	Wireless Adapter - A, B, C, D

# Wireless TrueSTEAM™ Humidification

## The Ultimate In Humidification Comfort & Control

Through the power of RedLINK, select models of TrueSTEAM Humidifiers are now wireless-enabled. The new models feature all the advantages of TrueSTEAM operation including 1:1 Humidification Delivery Rate, up to 90% less water waste, and remote installation flexibility - plus the benefits of wireless installation and advanced humidity control.



## Plug & Play

Finally – universal installation regardless of equipment brand or type. Because TrueSTEAM is now wireless, there’s no need to decipher complex wiring from the humidifier to the furnace board. Simply wire TrueSTEAM to the Wireless Adapter and press ‘Connect’. The adapter then communicates wirelessly with Prestige to control humidity, fan airflow and temperature.

	Model	Type	Features and								
			Gallons Per Day (GPD)	GDP Requires Plenum Air Temperature Of 120° F	Maximum Gallons Of Water Used Per Day (Does not include flush cycle)	Square Footage Covered (up to)	RedLINK™ Enabled	Humidity On Demand	Humidity When Furnace Is On	Frost Protection	Remote Mount Capability
<b>Steam Humidification</b>											
	HM512WTHX9 TrueSTEAM™, Prestige™, Wireless Adapter, Wireless Outdoor Sensor	Steam	12	NO	12	3,000+	•	•	•	•*	•
	HM512W1005	Steam	12	NO	12	3,000+	•	•	•	•*	•
	HM509W1005	Steam	9	NO	9	2,500	•	•	•	•*	•
	HM506W1005	Steam	6	NO	6	2,000	•	•	•	•*	•

\*Requires outdoor sensor for automatic Frost Protection.



# Humidification System



## Homeowner Friendly

Prestige eliminates wall clutter by controlling both temperature and humidity. Homeowners will appreciate having only one control on their wall just as much as they'll like using the sliding humidity scale on the Prestige Comfort System.

The sliding scale shows both actual and desired humidity on the same screen and relates Relative Humidity (RH) % into a comfort range so that homeowners easily understand how to control humidity in their home.



Functions					Control Options		Service Contract Parts	
Includes Quick Connect Water Filter	High And Low Water Cutoff Protection	LED User Interface	Auto Flushing And End-Of-Season Shutdown	UV Corrosion Protection	Warranty (years)	Prestige™ HD	Also includes Wireless Adapter and Wireless Outdoor Sensor	In-Line Quick Connect Water Filter
•	•	•	•	•	TrueSTEAM™, Prestige™, & Wirelss Adapter - 5 Wireless Outdoor Sensor-1	•	•	50028044-001
•	•	•	•	•	5			50028044-001
•	•	•	•	•	5			50028044-001
•	•	•	•	•	5			50028044-001

# Individual System Components

		Solutions								Schedule Options				User Interface		Application			
	Model	Relocate Thermostat Without Running New Wires	Upgrade to Multi-stage or Add Cooling Without Running New Thermostat Wires	Add to a TrueZONE® System Without Running New Thermostat Wires	Displays Outdoor Temperature and Humidity	Controls Humidification	Controls Dehumidification	Temperature Control on Demand	Adjust RedLINK-Enabled Thermostats from a Single Control	Program Options	ENERGY STAR®	Temporary Override	Permanent Hold	Vacation Hold	Touchscreen	Soft Keys	Stages	Gas, Oil or Electric	
<b>Prestige™ Thermostats</b>																			
	THX9321R5000				•*	•	•	•**	•**	7-Day	•	Fixed and Adjustable	•	•	•		Up to 3H/2C Heat Pump or 2H/2C Conventional	•	
Prestige HD Thermostat																			
	THX9321R1008				•*	•	•	•**	•**	7-Day	•	Fixed and Adjustable	•	•	•		Up to 3H/2C Heat Pump or 2H/2C Conventional	•	
Prestige SD Thermostat																			
<b>Wireless FocusPRO® Thermostats</b>																			
	TH6320R1004	•	•	•	•*			•**	•**	5-1-1 / 5-2 Day	•	•	•		•		Up to 3H/2C Heat Pump or 2H/2C Conventional	•	
5-1-1 Programmable Thermostat																			
	TH5320R1002	•	•	•	•*			•**	•**						•		Up to 3H/2C Heat Pump or 2H/2C Conventional	•	
Non-Programmable Thermostat																			
<b>System Components</b>																			
	REM5000R1001				•*			•	•			Fixed and Adjustable	•	•					
Portable Comfort Control																			
	C7089R1013																		
Wireless Outdoor Sensor																			
	THM5320R1000	•	•														Up to 3H/2C Heat Pump or 2H/2C Conventional	•	
Equipment Interface Module																			
	THM4000R1000			•															
Wireless Adapter																			

\*C7089R1013 required  
\*\* REM5000R1001 required

# Selection Guide

Power Method				Features & Functions														Display Information						Limited Warranty	Wiring Terminals			
Heat Pump	Forced Warm Air	Hot Water	Steam/Gravity	On-Screen Help	Real-Time Clock	Permanent Memory Retention	Selectable Auto or Manual Changeover	Interview-Based Programming	USB Port for Uploading Logo and Preset Installer Setup	Adaptive Intelligent Recovery™/Early Start™	Temperature Setpoint Limits	Keypad Lockout	Programmable Fan	Advanced Dual-Fuel Heat Pump Operation	Language Options	Remote Locator	Audible Feedback	Display Size (Viewable sq. in.)	High Definition (HD) Color Display	Standard Definition (SD) Display	On-Demand Backlighting	Continuous Backlighting	Simultaneous Display of Room and Set Temperatures	Filter, Humidifier Pad and UV Lamp Replacement Reminder	Dealer Logo On-Screen	Private Labeling Available		
•	•	•	•	Hardwired	•	•	•	•	•	•	•	•	•	•	•	•	•	8	•	•	•	•	•	•	•	•	5 years	C, R, Rc, W-O/B, W2-Aux/E, Y, Y2, G, L, K, HUM, HUM, DHM, DHM
•	•	•	•	Hardwired	•	•	•	•	•	•	•	•	•	•	•	•	•	8	•	•	•	•	•	•	•	•	5 years	C, R, Rc, W-O/B, W2-Aux/E, Y, Y2, G, L, K, HUM, HUM, DHM, DHM
•	•	•	•	Battery		•	•			•	•					•	5.09			•		•			•	5 years		
•	•	•	•	Battery		•	•				•					•	5.09			•		•			•	5 years		
				Battery		•	•				•					•	7			•		•				1 year		
				Battery																						1 year		
•	•	•	•	Hardwired																						5 years	C, R, Rc, Rh, W-O/B, W2-Aux/E, Y, Y2, G, L, RAS, RAS	
				Hardwired																						5 years	A, B, C, D	



# We've Done the Math

## With RedLINK™, You Can Do More With Less.



See How you can decrease your installation costs while increasing your profits. We've done the math for you in the example below by comparing a Conventional (Wired) Zoning System to a RedLINK (Wireless) Zoning System.

### Step 1. Determine The Products Needed For The Job

#### Conventional (Wired) 2-Zone System:

- (1) HZ322 TrueZONE® Panel
- (2) Programmable FocusPRO® Thermostats
- (1) Discharge Air Temperature Sensor and Transformer
- (1) Bypass Damper
- (2) Regular Dampers
- Thermostat Wire - (100 ft.)

#### RedLINK™ (Wireless) 2-Zone System:

- (1) HZ322 TrueZONE® Panel
- (2) Wireless Programmable FocusPRO® Thermostats
- (1) Discharge Air Temperature Sensor and Transformer
- (1) Wireless Adapter
- (1) Portable Comfort Control
- (1) Wireless Outdoor Sensor
- (1) Bypass Damper
- (2) Regular Dampers
- (1) Wireless Adapter
- Thermostat Wire - (25 ft.)

### Step 2. Add Up Product Costs\*

(1) HZ322 TrueZONE Panel	\$140
(2) Programmable FocusPRO TH6220 Thermostats @ \$65 each	\$130
(1) Discharge Air Temperature Sensor and Transformer	\$36
(1) Bypass Damper	\$100
(2) Regular Dampers @ \$120	\$240
Thermostat Wire - (\$0.50/ft. x 100 ft)	\$50
<b>TOTAL</b>	<b>\$696</b>

(1) HZ322 TrueZONE Panel	\$140
YTH6320R1023 Kit Includes: (1) Wireless Programmable FocusPRO TH6320 (1) Wireless Adapter	\$130
(1) Wireless Programmable FocusPRO Thermostat	\$110
(1) Discharge Air Temperature Sensor and Transformer	\$36
(1) Bypass Damper	\$100
(2) Regular Dampers @ \$120 each	\$240
Thermostat Wire - (\$0.50/ft. x 25 ft.)	\$13
<b>TOTAL</b>	<b>\$769</b>

### Step 3. Determine Labor Costs\*

How many installers will be needed, how many hours, and their hourly rate

Labor Cost	
Installers needed	2
Installer Labor Rate	\$85
Hours Estimated	16
<b>TOTAL</b>	<b>\$1,360</b>

Labor Cost	
Installers needed	1
Installer Labor Rate	\$85
Hours Estimated	6
<b>TOTAL</b>	<b>\$510</b>

the RedLINK Advantage: **Less Labor is Required with RedLINK.**

## Step 4. Establish Your Profit

Determine your net profit by subtracting what the job costs you from the job sell-price.

SELL PRICE	\$3,000	SELL PRICE	\$3,000
— YOUR COST (Product & Labor)	\$2,056	— YOUR COST (Product & Labor)	\$1,279
<b>= NET PROFIT</b>	<b>\$944</b>	<b>= NET PROFIT</b>	<b>\$1,721</b>

the RedLINK Advantage: **Less Labor = More Profit.**

## Step 5. Consider RedLINK Accessory Add-Ons

For an additional 5 minutes of labor, you can further increase profits and homeowner satisfaction with these RedLINK accessories.

	You Charge		Your Cost		Your Profit
Portable Comfort Control	\$200	-	\$110	=	\$90
Wireless Outdoor Sensor	\$100	-	\$52	=	\$48
	<b>TOTAL</b>				<b>\$138</b>

the RedLINK Advantage:  
**Increased Profits.**  
**Little or No Additional Time.**

## Step 6. Establish Productivity

Based on averaging your profit per labor hour, see how RedLINK adds up to more jobs done more quickly - which adds up to more profits for you.

### Conventional (Wired) 2-Zone System:

<b>Job Profit</b>	<b>\$944</b>
÷ <b>Job Hours</b>	<b>16</b>
<b>= Total Profit</b>	<b>\$59</b> per labor hour

### RedLINK (Wireless) 2-Zone System:

<b>Job Profit</b>	<b>\$1,859</b>
÷ <b>Job Hours</b>	<b>6</b>
<b>= Total Profit</b>	<b>\$310</b> per labor hour

the RedLINK Advantage: **Achieve More Profit Per Labor Hour by Using RedLINK.**

\*Estimates taken from sampling of 10 Contractor PRO® members.

# Focus On What's Really Important



Our full suite of RedLINK™-enabled wireless system kits and accessories allows you to do more for your customers, all while making more money for your business. They'll be satisfied with a more comfortable home — not to mention the cleaner installation because you won't have to drill, patch and paint holes in their walls. You'll save both time and money with the ease of wireless installation and you'll be able to make more calls and take on more projects.

**It all adds up to a better bottom line, and it's all exclusively from Honeywell.**

## Learn More

For more information about Wireless Comfort and Zoning Systems with Honeywell's RedLINK technology, ask your Honeywell representative or use the contact information listed below.

Call toll-free **1-800-328-5111**,  
e-mail **info@honeywell.com** or  
visit **forwardthinking.honeywell.com**.

## Automation and Control Solutions

Honeywell

1985 Douglas Drive North  
Golden Valley, MN 55422-3992  
[www.honeywell.com](http://www.honeywell.com)

50-1194 RL  
April 2009  
© 2009 Honeywell International Inc.

# Honeywell