SPEC SHEET #S1073 April 2002

Pro Port[™] Plumbers Access Door



HERCULES®

specifications

DESCRIPTION

Easy installation. Secure directly to wall surface with caulking or adhesive, or use nails or screws to attach to framing. Lightweight, durable and maintenance-free heavy-duty plastic construction fits flush with wall. Use to provide quick, easy access behind walls or ceiling for new or existing plumbing or wiring. Eliminates costly wall and ceiling repairs. Hinged door can be removed and replaced if desired. Textured surface can easily be painted or wallpapered.

SIZES AND PACKING			
STOCK NO.	SIZE	PACKING	WEIGHT/CASE
43-008	8" x 8"	12	9.5 lbs.
43-014	14" x 14"	12	24.3 lbs.

Pro Port[™] Plumbers Access Door

APPROVALS AND LISTINGS

Not Applicable.

SPECIFIC USES

Swing door allows access to valves, piping, or wiring.

SPECIFIC APPLICATIONS*

Designed to facilitate future access to wall interiors or as a substitute for a more difficult wall surface repair.

PHYSICAL PROPERTIES

Not applicable.

WARNINGS OR CAUTIONS

Read all cautions and directions carefully before using this product.

DIRECTIONS FOR USE

REMOVING DOOR FROM HINGE

- 1) Open door by inserting screwdriver or coin in slots and prying open.
- 2) Hold unit vertically and open door 90 degrees.
- **3)** Grip top of door near the hinge sides and gently pull door loose.

INSTALLING LOOSE DOOR

- Hold loose door in 90 degree open position in relationship to the frame and place lower pivot pin of door into pivot slot in frame.
- 2) Position other pivot pin at top of door against top pivot slot and gently push door in.

INSTALLATION INSTRUCTIONS

- 1) Cut an opening in wall or ceiling 1/4" larger than door size.
- 2) Apply caulking or adhesive to back of frame.
- **3)** Before installation rotate frame to be sure hinge is in the proper position.
- **4)** Be sure frame is level and plumb. Then press frame and door into opening to assure tight seal.



MATERIAL SAFETY INFORMATION

For Delivery by Fax	Call 1-800-942-4636
Internet	See MSDS section of www.herchem.com
Mail	Contact Hercules at address below or any Hercules representative

This product is defined as an "article" and is not classified as hazardous in accordance with OSHA 1910.1200.

* For special applications which may not be covered on this or other Hercules literature, please contact Hercules Technical Services Department by phone at 1-800-221-9330 or send a fax to 1-800-333-3456.



Hercules Chemical Company, Inc.

111 South Street, Passaic, NJ 07055-9100 Phone: 800-221-9330 • Fax: 800-333-3456 e-mail: info@herchem.com

http://www.herchem.com

