

INSTALLATION INSTRUCTIONS

Series AGD-Y

Air Gap Drain

Sizes: $\frac{3}{4}$ " – 2" (20 – 50mm)

Installation Instructions

Kit Part No's: 905082, 905133, 905531

- 1) For FEBCO Series 825Y $\frac{3}{4}$ " to $1\frac{1}{4}$ " (20 – 32mm) assemblies.
Attach funnel to relief valve, under discharge shield, using $\frac{1}{2}$ " long bolt.
- 2) For FEBCO Series 825Y $1\frac{1}{2}$ " and 2" (40 – 50mm) assemblies.
Depressurize valve and remove lower cover bolt (through bossed area on backside of relief valve). Install $1\frac{1}{2}$ " long bolt through cover and tighten. Attach extension spacer to funnel using $\frac{1}{2}$ " long bolt and nut. Position funnel over protruding bolt and retain with nut.
- 3) Thread drain piping into the 1" (25mm) IPS connection in the drain. Do not use relief valve/air gap drain to support any drain piping weight. Support the drain piping by other appropriate means.
- 4) The air gap drain is designed to drain away minimal discharge from the relief valve port. It is not intended to drain all discharge possible from the relief valve port. The unit should be installed near a floor drain sized to adequately handle maximum relief port discharge if installed in an indoor installation. Write or call for FEBCO information chart RVDR (relief valve discharge rates).

NOTE: THIS FUNNEL CANNOT BE INSTALLED ON $\frac{3}{4}$ ", 1" OR $1\frac{1}{4}$ " (20, 25 or 32mm) ASSEMBLIES PRIOR TO S/N A1275.

Note: The gap drain is not designed to catch the maximum discharge possible from the relief valve. The installation of FEBCO air gap with the drain line terminating above a floor drain will handle any normal discharge or nuisance spitting through the relief valve. However, floor drain size may need to be designed to prevent water damage caused by a catastrophic failure condition. Do not reduce the size of the drain line from the air gap fitting.



CALIFORNIA PROPOSITION 65 WARNING

WARNING: This product contains chemicals known to the State of California to cause cancer and birth defects or other reproductive harm. (California law requires this warning to be given to customers in the State of California.)

For more information: www.watts.com/prop65

Limited Warranty: FEBCO warrants each product to be free from defects in material and workmanship under normal usage for a period of one year from the date of original shipment. In the event of such defects within the warranty period, the Company will, at its option, replace or recondition the product without charge.

THE WARRANTY SET FORTH HEREIN IS GIVEN EXPRESSLY AND IS THE ONLY WARRANTY GIVEN BY THE COMPANY WITH RESPECT TO THE PRODUCT. THE COMPANY MAKES NO OTHER WARRANTIES, EXPRESS OR IMPLIED. THE COMPANY HEREBY SPECIFICALLY DISCLAIMS ALL OTHER WARRANTIES, EXPRESS OR IMPLIED, INCLUDING BUT NOT LIMITED TO THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE.

The remedy described in the first paragraph of this warranty shall constitute the sole and exclusive remedy for breach of warranty, and the Company shall not be responsible for any incidental, special or consequential damages, including without limitation, lost profits or the cost of repairing or replacing other property which is damaged if this product does not work properly, other costs resulting from labor charges, delays, vandalism, negligence, fouling caused by foreign material, damage from adverse water conditions, chemical, or any other circumstances over which the Company has no control. This warranty shall be invalidated by any abuse, misuse, misapplication, improper installation or improper maintenance or alteration of the product.

Some States do not allow limitations on how long an implied warranty lasts, and some States do not allow the exclusion or limitation of incidental or consequential damages. Therefore the above limitations may not apply to you. This Limited Warranty gives you specific legal rights, and you may have other rights that vary from State to State. You should consult applicable state laws to determine your rights. **SO FAR AS IS CONSISTENT WITH APPLICABLE STATE LAW, ANY IMPLIED WARRANTIES THAT MAY NOT BE DISCLAIMED, INCLUDING THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE, ARE LIMITED IN DURATION TO ONE YEAR FROM THE DATE OF ORIGINAL SHIPMENT.**



A Division of Watts Water Technologies, Inc.

USA: 4381 N. Brawley • Ste. 102 • Fresno, CA • 93722 • Tel. (559) 441-5300 • Fax: (559) 441-5301 • www.FEBCOonline.com
Canada: 5435 North Service Rd. • Burlington, ONT. • L7L 5H7 • Tel. (905) 332-4090 • Fax: (905) 332-7068 • www.FEBCOonline.ca